


SUPER SIX 6" Jamb Saw





10-46


The 10-46 Jamb Saw is a powerful and versatile tool, capable of meeting a wide variety of undercutting needs. With a big 6-3/16" carbide tipped blade, this saw easily cuts door jambs, baseboards, cabinet toe kicks, inside corners and most hanging doors. The blade height adjusts from flush to the floor to 1-1/2" to allow proper heights for all floor coverings, from sheet vinyl up to thick ceramic and wood. As an additional feature, the cutting depth guide is also adjustable to prevent cutting through plaster or wall board when trimming cove base.

The Roberts Jamb Saw, lowering the cost of commercial carpet installations.



SUPER SIX 6" Jamb Saw





Saw Specifications:

Voltage: 120V-60Hz

AMPS: 7.5 (industrial grade)

RPM: (No load) 7,000

Arbor: 5/8"

Blade Adapter: 20mm

Kit Includes:

- 10-46 Power Saw Unit
- 6-3/16", carbide tooth "cupped arbor" saw blade
- Spanner wrench for blade retainer
- Spare parts
- Instruction manual
- Custom molded carrying case
- Steel depth guide

10-46

Part	Description	Part	Description
10-46-01	Handle	10-46-12	Return Spring (100 bulk pack) (not shown)
10-46-02	Spanner Wrench		
10-46-03	Depth Gauge	10-46-14	Snap Ring
10-46-04	Return Spring (3 pack)	10-46-16	Blade Retainer Nut
10-46-05	Screws, Spacers, Spring (2 pack)	10-46-17	Arbor Spacer
10-46-07	Handle Bolt & Lock Washer	10-46-18	Motor Unit
10-46-08	Mounting Body	10-46-19	Mounting Screws (4 pack)
10-46-09	Height Adjustment Skirt	10-46-20	Replacement Switch
10-46-10	Screw Knob,	10-46-21	Carbon Brushes (2)
	Washer for Depth Gauge	10-47	6-3/16" (158mm) Cupped Arbor,
10-46-11	Safety Guard		Carbide Tip Saw Blade

Roberts Consolidated Industries, Inc. • Boca Raton, FL 33487 • (800) 423 6545 • www.gep.com