




GENERAL PURPOSE ACCESS DOOR

WITH DRYWALL FLANGE

2VE72 - 2VE73 - 2VE74 - 2VE75 - 16M207

INSTALLATION




DIMENSIONS AND APPEARANCE

LEED ready: This product contributes to LEED® credits.

| PRODUCT CODE | DOOR SIZE | | NUMBER OF LOCKS | WEIGHT | |
|--------------|-------------------|-------------|-----------------|--------|-----|
| | W x H inches (MM) | | | LBS | KG |
| 2VE75 | 8 x 8 | (203 x 203) | 1 | 3 | 1.4 |
| 2VE72 | 12 x 12 | (304 x 304) | 1 | 5 | 2.3 |
| 16M207 | 16 x 16 | (406 x 406) | 1 | 8 | 3.6 |
| 2VE73 | 18 x 18 | (457 x 457) | 1 | 10 | 4.5 |
| 2VE74 | 24 x 24 | (609 x 609) | 1 | 15 | 6.8 |

Rough wall opening is door size + 1/4" or + 6mm



DESCRIPTION AND MATERIAL SPECIFICATION

Material: 16 gauge cold rolled steel
Hinge: hidden pin hinge
 continuous piano type on doors
 over 24" (height or width)

Lock / latch: screwdriver operated cam latch
Finish: high quality white powder coat primer
Packaging: individually wrapped, 1 per box
GYP: drywall corner beads flange



**FOR CUSTOM SIZES AND DIFFERENT LOCKING OPTIONS,
 PLEASE CALL YOUR LOCAL GRAINGER BRANCH.**