








	TRADES CART		CONTRACTORS CART		MOBILE WORK CENTER		TRADEMASTER®		TRADEMASTER®		TRADEMASTER®		LADDER CART	
														
	SMALL	LARGE	SMALL	LARGE	SMALL	LARGE	SMALL	LARGE	SMALL	LARGE	SMALL	LARGE	SMALL	LARGE
<b>CART SIZE</b>	38" (L) X 19.25" (W) X 33.4" (H)	—	52.5" (L) X 38.6" (W) X 37.9" (H)	—	32.63" (L) X 19.9" (W) X 33.5" (H)	—	40.6" (L) X 18.4" (W) X 33.4" (H)	—	41.6" (L) X 18.25" (W) X 38.4" (H)	49" (L) X 26.25" (W) X 38.25" (H)	49" (L) X 26.25" (W) X 38.0" (H)	58.6" (L) X 26.4" (W) X 33.25" (H)	—	31.5" (L) X 27" (W) X 42" (H)
<b>AVAILABLE COLORS</b>	BLACK/RED		BLACK/RED		BLACK/RED		BLACK/RED		BLACK/RED		BLACK/RED		BLACK/RED	
<b>HANDLE TYPE</b>	FLAT-HANDLE		VARIABLE GRIP-HEIGHT HANDLE		FLAT-HANDLE		VARIABLE GRIP-HEIGHT HANDLE		VARIABLE GRIP-HEIGHT HANDLE		VARIABLE GRIP-HEIGHT HANDLE		FLAT-HANDLE	
<b>SHELF TYPE</b>	FLAT-SHELF		FLAT-SHELF		FLAT-SHELF		POCKET-SHELF WITH OPEN-FRONT		POCKET-SHELF WITH OPEN-FRONT		POCKET-SHELF WITH OPEN-FRONT		FLAT-SHELF	
<b>CASTER SIZE</b>	5"		5"		4"		5"		5"		5"		5"	
<b>MAX. WEIGHT-CAPACITY</b>	330 LBS.		500 LBS.		250 LBS.		500 LBS.		500-750 LBS.		750 LBS.		500 LBS.	
<b>MATERIAL</b>	STRUCTURAL FOAM		STRUCTURAL FOAM		STRUCTURAL FOAM		STRUCTURAL FOAM		STRUCTURAL FOAM		STRUCTURAL FOAM		STRUCTURAL FOAM POWDER-COATED STEEL	
<b>STORAGE CONFIGURATION</b>	2-DRAWERS CABINET OPTIONAL		SINGLE FULL EXTENSION DRAWERS HINGED-TOP STORAGE COMPARTMENT		5-DRAWERS		4-DRAWERS		2-CABINET DOORS		4-DRAWERS + CABINET DOOR		CABINET DOORS FASTENER CADDY (TOP SHELF)	
<b>ASSEMBLY</b>	ASSEMBLY REQUIRED		SHIPS 90% ASSEMBLED		ASSEMBLY REQUIRED		SHIPS 90% ASSEMBLED		SHIPS 90% ASSEMBLED		SHIPS 90% ASSEMBLED		ASSEMBLY REQUIRED	
<b>MOLDED-IN PERIMETER</b>					•		•		•		•			
<b>EASY-REACH TOOL/ACCESSORY STORAGE COMPARTMENT</b>			•		•		•		•		•		•	
<b>CUP HOLDER</b>			•				•		•		•			
<b>3-OUTLET POWER STRIP</b>							•		•		•			
<b>CENTRAL LOCKING SYSTEM</b>	•		•		•		•		•		•		•	
<b>ACCESSORIES</b>														
<b>REFUSE BIN (8 GALLON)</b>					•		•		•		•			
<b>UTILITY BIN (4 GAL.)</b>					•		•		•		•			
<b>CORD/STEP LADDER HOOKS</b>			•				•		•		•			

		STANDARD CASTERS	CASTER OPTIONS
<b>CASTER TREAD MATERIAL</b>		TPR (THERMOPLASTIC RUBBER)	PNEUMATIC
<b>CASTER SIZE</b>		5"	8"
<b>CASTER TYPE (QTY.)</b>		2 SWIVEL; 2 FIXED	—
<b>FLOOR SURFACES</b>	<b>EXCELLENT</b>	ASPHALT, BRICK, CARPET, CONCRETE, LINOLEUM/TILE, TERRAZZO, AND WOOD	ASPHALT, BRICK, CARPET, CONCRETE, LINOLEUM/TILE, TERRAZZO, STEEL (RIBBED AND SMOOTH), AND WOOD
	<b>GOOD</b>	STEEL (RIBBED AND SMOOTH)	—
	<b>FAIR</b>	—	—
<b>OPERATING CONDITIONS</b>	<b>EXCELLENT</b>	METAL SCRAPS (SMALL OR LARGE)	—
	<b>GOOD</b>	WATER, STEAM, OR ANIMAL FATS	MILD OR HARSH CHEMICALS, METAL SCRAPS (SMALL OR LARGE), WATER, STEAM, OR ANIMAL FATS
	<b>FAIR</b>	MILD OR HARSH CHEMICALS, OIL & GREASE	OIL & GREASE
<b>REPLACEMENT ITEM #</b>		SWIVEL: FG4532L20000 RIGID: FG4532L10000	—
<b>ADDITIONAL INFORMATION</b>		TPR CASTERS ABSORB SHOCK AND PROVIDE FLOOR SURFACE PROTECTION AND QUIET OPERATION. CHEMICAL AND WATER RESISTANT.	PNEUMATIC CASTERS PROVIDE A CUSHIONED AND QUIET RIDE FOR FRAGILE LOADS. ALSO IDEAL FOR ROUGH, UNEVEN SURFACES BOTH IN INDOOR AND OUTDOOR USE.

# MOBILE WORKSTATIONS SELECTION GUIDE

To see our complete range of material handling solutions visit our online catalog at [rubbermaidcommercial.com](http://rubbermaidcommercial.com)

RCP-386  
#141734  
©2015 Rubbermaid Commercial Products LLC  
8900 Northpointe Executive Drive, Huntersville, NC 28078

