



Ultra-Containment Berm®

COLLAPSIBLE WALL MODEL

SPECIFICATIONS

KEY FEATURES AND BENEFITS

- Rugged PVC sidewall assemblies for sidewall support. Simply swivel the "feet" of the PVC supports to lower or raise the sidewalls in just seconds!
- Rugged materials provide years of service and excellent chemical compatibility.



SIDEWALLS:

- Heavy-duty PVC frames provide structure and support.
- "Feet" are swiveled at each frame to either position the sidewalls up or down.
- Manual set-up / take-down required.



COMPLIANCE:

- EPA 40 CFR 264.175 Containment of Containers Containing Free Liquid.
- SPCC - Spill Prevention, Control and Countermeasure Act

STANDARD SIZES AVAILABLE

	Size	Capacity	Weight
Part# 8405	4' x 6' x 1'(1.2 m x 1.8 m x .3 m)	179 gallons (678 L)	43 lbs. (19.5 kg)
Part# 8403	6' x 6' x 1'(1.8 m x 1.8 m x .3 m)	269 gallons (1,018 L)	46 lbs. (21 kg)
Part# 8400	10' x 10' x 1'(3 m x 3 m x .3 m)	748 gallons (2,831 L)	70 lbs. (32 kg)
Part# 8404	12' x 60' x 1' (3.7 m x 18.3 m x .3 m)	5,385 gallons (20,384 L)	323 lbs. (147 kg)
Part# 8401	15' x 50' x 1'(4.6 m x 15.2 m x .3 m)	5,610 gallons (21,236 L)	319 lbs. (145 kg)
Part# 8402	15' x 66' x 1'(4.6 m x 20.1 m x .3 m)	7,405 gallons (28,028 L)	420 lbs. (191 kg)
Custom Sizes Available.			

SEE BACK FOR MATERIAL SPECIFICATIONS

MATERIAL SPECIFICATIONS (Specs shown are for Copolymer-2000. Other materials available.)

Reinforced	Standard	Metric
Base Fabric Type	Polyester	
Base Fabric Weight (nominal)	3.0 oz/yd ²	102 g/m ²
Finished Coated Weight - ASTM D751	28.0 ± 2 oz/yd ²	950 ± 70 g/m ²
Thickness - ASTM D751	30 mils nominal	0.76 mm nominal
Trapezoid Tear - ASTM D4533	30/30 lb _f nominal	133/133 N nominal
Grab Tensile - ASTM D751 Grab Method	250/200 lb _f min.	1112/890 N min.
Hydrostatic Resistance - ASTM D751, Procedure A	300 psi min.	2.06 MPa min.
Adhesion - ASTM D751 Dielectric Seam	10 lb _f /in min.	9.0 daN/5 cm min.
Cold Crack - ASTM D2136 1/8 in mandrel, 4 hr.	Pass @ -25° F	Pass @ -32° C
Puncture Resistance - ASTM D4833	50 lb _f typical	225 N typical
Dead Load - ASTM D751	2 in seam, 4 hr, 1 in strip 100 lb _f @ 70° F 50 lb _f @ 160° F	5 cm seam, 4 hr, 2.5 cm strip 445 N @ 21° C 220 N @ 70° C