

## WARN® XD9000

### Long time best selling winch

Long-time best seller. A durable 9,000 lb. winch with a compact body and separate control pack that allows you to use it in tight spaces. Comes with 100' of 5/16" wire rope. Backed by the Warn Limited Lifetime Warranty.

- Low-profile design and separate control box allows for a wide range of mounting options
  - Exclusive brake design provides superior control while winching
  - Durable 3-stage planetary geartrain for smooth, reliable, operation
- Series-wound, high-speed motor provides fast line speed and strong pulls
  - Chip-resistant, powder-coated finish
  - Remote control with 12' (3.7m) lead.
- Durable 5/16" (8mm) diameter galvanized steel wire rope.

#### XD9000 SPECS

**Part number:** 28500 (12V)

**Part Number:** 88500 (12V, CE, International sales only)

**Part number:** 265012 (24V) *Contact WARN Customer Service for Availability*

**Winch model:** XD9000

**Rated line pull:** 9,000 lbs., (4080 kgs.) single-line

**Motor:** Series Wound: 12V 4.6 hp, 24V 2.5 hp

**Electrical controls:** Contactor

**Remote Control:** Remote switch, 12' (3.7m) lead

**Gear Train:** 3-Stage Planetary

**Gear ratio:** 156:1

**Clutch (freespooling):** Sliding Ring Gear

**Brake:** Automatic mechanical cone

**Drum diameter/Length:** 2.5"/9.0" (6.4cm/23cm)

**Weight:** 78 lbs. (35kgs.)

**Wire rope:** 100', 5/16" dia. (30m, 8mm)

**Fairlead:** Roller

**Recommended Battery:** 650 CCA minimum for winching

**Battery leads:** 2 gauge, 72" (1.83m)

**Finish:** Argent gray powder coat


#### 12V DC PERFORMANCE SPECS

Line Pull Lbs.(Kgs.)	Line Speed FT./min(M/min.)	Motor Current	Pull by layer layer/Lbs(Kgs.)
0	38 (11.58)	56 amps	1/9000 (4082)
2000 (910)	15 (6.8)	161 amps	2/8190 (3715)
4000 (1810)	10.3 (3.14)	252 amps	3/7500 (3402)
6000 (2720)	7.5 (2.29)	332 amps	4/7010 (3180)
8000 (3630)	5.1 (1.55)	423 amps	
9000 (4080)	3.9 (1.19)	478 amps	

### 24V DC PERFORMANCE SPECS

Line Pull Lbs.(Kgs.)	Line Speed FT./min(M/min.)	Motor Current	Pull by layer layer/Lbs(Kgs.)
0	22.5 (6.86)	46 amps	1/9000 (4082)
2000 (910)	14.5 (4.42)	93 amps	2/8190 (3715)
4000 (1810)	11 (3.35)	131 amps	3/7500 (3402)
6000(2720)	9.1(2.77)	169 amps	4/7010(3180)
8000 (3630)	7.9 (2.41)	207 amps	5/6570 (2980)
9000 (4080)	7.4 (2.26)	226 amps	

Above performance specs are based on first layer of drum



**Winch Dimensions:** 21.8" L. x 6.3" D. x 7.6" H.  
(555mm L. x 160mm D. x 193mm H.)

**Mounting Bolt Pattern:** 10.0" x 4.5" (254mm x 114.3mm)