























Slide Sledge® Multi-Head™ Hammer Product line-up

	1/2" Diameter Pin Driver #4XGT2 Recommended for pins and bolts greater than 1/2" up to 7/8" in diameter		Tie Rod/Ball Joint Separator Forks 11/16" 15/16" #4XGU3 #4XGU4 1 1/8" 1 7/16" #4XGU5 #4XGP4		Utility Wedge Tip #4XGR6 All purpose impact tool designed to separate parts and straighten steel with maximum force
	7/8" Diameter Pin Driver #4XGT3 Recommended for pins greater than 7/8" up to 1 1/4" in diameter		Bucket Tooth Pin Removers 3/8" Diameter #4XGP8 1/2" Diameter #4XGP7 3/4" Diameter #4XGP6		Bushing/Bearing/Seal Plate Driver #4XGR1 Use the extreme power of the Slide Sledge® Multi-Head™ to drive heavy duty plates without the cocking motion of a hammer and handle. <i>(plates not included)</i>
	1 1/4" Diameter Pin Driver #4XGT4 Recommended for pins greater than 1 1/4" up to 2" in diameter		Bucket Tooth Pin Removers 3/8" Diameter #4XGT9 1/2" Diameter #4XGT8 3/4" Diameter #4XGU1		Race/Bearing/Seal Adapter #4XGP9 Install races, bearings, and seals with this adapter driver tip. Add drive plates to the end of the adapter in various combinations Fits plates with a common 9/16" center hole, up to 3/4" high. <i>(plates not included)</i>
	2" Diameter Pin Driver #4XGT5 Recommended for pins greater than 2" up to 2.5" in diameter		Hammer Union Tip #31LZ11 Tip offers a flush fit and impact on all tabs or wings of pipe.		Bushing Driver Adapter #4XGR2 Proper installation of bushings will be accomplished easily and quickly with this adapter driver tip. Fits drivers with a common 3/4" center hole, up to 7/8" high. <i>(drivers not included)</i>
	2 1/2" Diameter Pin Driver #4XGT6 Recommended for pins greater than 2.5" up to 3" in diameter		Continuous Miner Tip #213661* Ideal for removing all teeth on continuous mining equipment		Tire Bead Breaker Large #4XGR4 Large bead breaker has a head width of 2 7/8" Small #4XGR3 Small bead breaker has a head width of 2 1/4"
	3" Diameter Pin Driver #4XGT7 Recommended for pins greater than 3" up to 4" in diameter		Curved Chisel Tip #4XGP5 1 3/8" tip ideal for chopping away hardened debris & shearing metal bolts, pins and rivets up to 3/8" grade 8		Strike Wrench, Large #31LZ09 Inside dimension 2.1 inch Small #31LZ10 Inside dimension 1.6 inch
	Tie Rod/Ball Joint Separator 3 Tip Set #4XGP3 Slide Sledge® separator adapter and 11/16", 15/16", 1 1/8" forks		Scarifier Tooth Tip #4XGR5 Removes scarifier teeth on most motor graders. The fork design allows the tech. to split the trenching arm where the scarifier tooth is forced fit		
	Tie Rod/Ball Joint Separator Adapter #4XGU2 Attach all Slide Sledge® separator forks and most common forks available today				
	5 lb Handle Weight #4XGR7 Increases the Slide Sledge® striking force by 5 lbs, works with any of the four tools by threading onto tool handle				

Stake & Ground Rod Drivers
 Large Cup #31LZ04
 Small Cup #31LZ05
 Stake Cup #31LZ06
 Hook Cup #31LZ07
 7/8" Punch Tip #31LZ08

Multi-Head™ Hammers
#4XGU6¹ 9 lb | 30" Multi-Head™ Hammer
#4XGN8² Compact 30" length great for fitting into tight areas
#4XGU7¹ 13 lb | 46" Multi-Head™ Hammer
#4XGN9² Ideal for most standard applications
#4XGU8¹ 14 lb | 30" Multi-Head™ BMF Hammer
#4XGP1² Larger diameter BMF series coupled with compact 30" length allow tool to fit into tight areas while delivering *Biggest Maximum Force*
#4XGU9¹ 21 lb | 46" Multi-Head™ BMF Hammer
#4XGP2² Longer length and greater weight delivers *Biggest Maximum Force* for your toughest applications

¹ includes #4XGT5 Pin Driver
² includes #4XGT5, #4XGT6, #4XGT7, #4XGT2, #4XGT3, #4XGT4 Pin Drivers

Covered by one or more US patents. Additional patents pending.

#25120* - 38" Heavy Nylon Tool Bags
 #25121* - 52" With interior pockets



* Items available through Grainger Sourcing only

For more information, please contact your Grainger Representative or visit Grainger.com

AVAILABLE THROUGH
GRAINGER
 FOR THE ONES WHO GET IT DONE



Slide Sledge
 MULTI-HEAD HAMMER

SAFER FASTER EASIER

PETERSEN BRANDS

Slide Sledge **SAFER, FASTER AND EASIER THAN A SLEDGE HAMMER**

MULTI-HEAD HAMMER

Affordably customize your Slide Sledge for **JOB-SPECIFIC APPLICATIONS** with our comprehensive list of changeable tips.

The linear motion of Slide Sledge focuses power for **PRECISION IMPACT** without the worry of dangerous sledge hammer misses and glancing blows. With the power and accuracy of Slide Sledge, driving pins and other tough maintenance jobs are safer, faster and easier.

The powerful Slide Sledge Multi-Head Hammer reduces dangerous, time-consuming, hammer and chisel jobs to a **ONE MAN, ONE TOOL** operation.

15,000 PSI OF FOCUSED LINEAR MOTION FOR PRECISE DELIVERY OF IMPACT



SAFETY FIRST
Eliminates Hand-holding of Chisel or Punch

MORE ACCURATE
Linear Impact instead of Wasteful Arcing Motion

LESS DOWNTIME
Powerful & Precise Impact with No Miss-hits

EXTREMELY POWERFUL
Easily Deliver Over 15,000 psi Impact

INCREASED PRODUCTIVITY
One Man Now Does Job of Two

VERSATILE
Quick-change "Application Specific" Tips



MULTI-HEAD VERSATILITY FOR ALL APPLICATIONS

