



Spill Berm Chemical Application Guide

For more information visit www.BradyID.com/spc.

The Information below is the result of laboratory test and is intended only as a guide. No performance warranty is intended or implied. Exposure time, temperature and size of the area of the exposure usually varies considerably in application; therefore, this table is given and accepted at the user's risk. Material samples can be provided for testing in simulated conditions prior to actual service application.

Exposure Ratings

Exposure	Rating	Exposure	Rating	Exposure	Rating
Acetic Acid (5%)	B	Ethylene Glycol	A	Phenol Formaldehyde	B
Ammonium Phosphate	T	Fertilizer Solution	A	Phosphoric Acid (5%)	A
Ammonium Sulfate	NT	#2, #6 Fuel Oils	A	Raw Linseed Oil	A
Amyl Acetate	NT	Gasoline	B	SAE-30 Oil	A
Animal Oil	A	Glycerin	A	Salt Water (25%)	B
ASTM Fuel A (100% Iso-Octane)	A	Hydraulic Fluid (Mineral)	A	Skydrol	X
Diesel Fuel	A	Hydrocarbon Type II 40% Aromatic	NT	Sodium Acetate Solution	T
ASTM Oil #2,#3	A	Urea Formaldehyde	A	Sodium Bisulfite Solution	T
Benzene	NT	Hydrochloric Acid (5%)	A	I,I,I - Trichloroethane	(*)
Butyl Alcohol	NT	Hydrofluoric Acid (5%)	A	Sodium Hydroxide (25%)	A
Calcium Chloride Solutions	T	Hydrofluosilicic Acid (30%)	A	Sodium Phosphate	T
Crude Oil	A	Zinc Chloride (25%)	T	Sulfuric Acid (50%)	A
Calcium Hydroxide	T	Isopropyl Alcohol	T	50% Tanic Acid	A
20% Chlorine Solution	A	JP-4,5,8,Jet Fuels	A	Toluene (Toluol)	X
Clorox	A	Kerosene	A	Transformer Oil	A
Conc. Ammonium Hydroxide	A	Magnesium Chloride	T	Turpentine	A
Corn Oil	A	Methanol (Methyl Al.)	A	Vegetable Oil	A
Ethanol (Ethyl Al.)	A	Mineral Spirits	A	Water (200 F)	A
Magnesium Hydroxide	T	Naphtha	A	Xylene (Xylol)	X

RATING:

- A** = Fluid has little or no effect
- B** = Fluid has minor to moderate effect
- T** = No data, likely to be acceptable
- (*)** = Limited stability, passed 10 days resistance
- X** = No data not likely to be acceptable
- NT** = Not tested

The shown ratings are based upon visual and physical examination of samples after 14 days of immersion at room temperature. Results represent ability of material to retain its performance properties when in contact with the indicated chemical. SPC makes no guarantee of results and assumes no obligation or liability whatsoever in connection with this information.

Catalog #	Description	Size	Qty
SB-1010	Standard Portable Spill Berm	10'H x 10'W x 12"D	1/Each
SB-1212	Standard Portable Spill Berm	12'H x 12'W x 12"D	1/Each
SB-1226	Sandard Portable Spill Berm	12'H x 26'W x 12"D	1/Each
SB-1236	Standard Portable Spill Berm	12'H x 36'W x 12"D	1/Each
SB-1454	Standard Portable Spill Berm	14'H x 54'W x 12"D	1/Each
SB-SL44	Lightweight Portable Spill Berm	4'L x 4'W x 8"H	1/Each
SB-SL46	Lightweight Portable Spill Berm	4'L x 6'W x 8"H	1/Each
SB-SL48	Lightweight Portable Spill Berm	4'L x 8'W x 8"H	1/Each