



DUAL DIMENSIONS: INCHES
MILLIMETERS

DEVICE	TYPE OF OPERATOR	CLASS 2510 TYPE	DIMENSIONS (IN.)		
			A	B	C
TYPE F	TOGGLE	FSJ1P, 2P	1.44	3.50	5.25
	KEY	FSJ3P, 4P	1.44	3.50	5.25
TYPE K	TOGGLE	KSJ1A, 1B KSJ2B, 2C	1.75	3.50	5.25
	KEY	KSJ3A, 3B KSJ4B, 4C	1.75	3.50	5.25

CATALOG NUMBER: 2510 FSI, KSI
 RATINGS: 1 HP FOR F, 10 HP FOR K
 UL FILE/CCN: E42243, CCN NLRV
 CSA FILE/CLASS: LR25490 CLASS 3211 05
 WEIGHT: 2 LBS
 WIRE SIZE: F=POWER #10 / K=VARIES PER MOTOR SIZE/CONSULT NEC
 TERMINAL TORQUE: 20 LBS IN.

NEMA FRACTIONAL HORSEPOWER
 MANUAL STARTERS
 2510_FSJ_KSJ_JUMBO FLUSH



DWG# 25100018
 NO.