




ACCESS DOOR WITH HIDDEN FLANGE

FOR ALL SURFACE TYPES

16M209 - 16M210 - 16M211 - 16M212 - 16M213 - 16M214

INSTALLATION

> EXCLUSIVE <
ACCESS DOOR



A LABOR SAVING
alternative to doors
with DRYWALL FLANGES


“No need to mud or plaster”

DIMENSIONS AND APPEARANCE

PRODUCT CODE	DOOR SIZE W x H inches (MM)	NUMBER OF LOCKS	WEIGHT	
			LBS	KG
16M209	8 1/4 x 8 1/4 (210 x 210)	1	3	1.4
16M210	12 x 12 (304 x 304)	1	6	2.7
16M211	14 x 14 (355 x 355)	1	7	3.2
16M212	16 x 16 (406 x 406)	1	9	4.1
16M213	18 x 18 (457 x 457)	3	10	4.5
16M214	24 x 24 (609 x 609)	4	17	7.7

Rough wall opening is door size + 1/4" or + 6mm

LEED ready: This product contributes to LEED® credits.



DESCRIPTION AND MATERIAL SPECIFICATION

Material: 16 gauge cold rolled steel

Hinge: concealed, exclusive hinge design

Lock / latch: screwdriver operated cam latch

Finish: high quality white powder coat primer

Packaging: individually wrapped, 1 per box



FOR CUSTOM SIZES AND DIFFERENT LOCKING OPTIONS,

PLEASE CALL YOUR LOCAL GRAINGER BRANCH.