


Series	PH	Shut Off	No
Sleeve Material	Steel	Valve Design	Poppet
Connection Type	FNPT	Seal Material	Buna
Coupler Body Size	1-1/2"	Max. Pressure	5000 psi
Coupler Flow Rate	3.8 gpm	Coupler Finish	Zinc Plated
Coupler Thread Size	1-1/2"-11-1/2	Locking Mechanism	Ball
Coupler Interchange Type	PH	Coupler Body Material	Steel



#### NOTES:

1. SEAL TYPE: Buna N
2. ITEM: Hydraulic Coupler Body
3. BEARING MATERIAL: 440 Stainless Steel
4. OPERATING TEMP. RANGE: -40° to 200°F
5. QUICK COUPLER TYPE: Hydraulic Coupler Body

**GRAINGER**

100 Grainger Parkway, Lake Forest, Illinois 60045-5201  
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000  
[www.grainger.com](http://www.grainger.com)

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE 0.73

COMPONENT	Hydraulic Quick Couplers		
20LF72  Coupler Body, 1-1/2-11-1/2, Body, Steel	UNIT		
	INCH		
	SHEET		
	1 of 1		