



NOTES:

1. MAX. RPM: 7000
2. TYPE: Hytrel Spider
3. ITEM: Hytrel® Spider
4. TORQUE: 315/415 In.-Lbs.
5. COUPLING SIZE: L099/L100
6. HP RATING@ 100 RPM: 1.36/1.80
7. COUPLING WEIGHT: 0.075Lb
8. MAX. TORQUE: 860/1134 In.-Lbs.
9. HP RATING@ 3600 RPM: 49.12/64.78
10. MAX. ANGULAR MISALIGNMENT: 1.5°
11. SHAFT DIA. RANGE: 7/16 to 1-3/8 In
12. APPLICATION: Close Coupling L-Type
13. SERVICEABLE TEMP. RANGE: -59.8°F to 69.8°F
14. ACCOMMODATES: 1/2 ° Angular and 0.015" of Parallel Misalignment

COMPONENT	Jaw Coupling Spider	
<h1>29HZ15</h1> Jaw Coupling Insert, L099 / L100, Hytrel	UNIT	INCH
	SHEET	1 of 1



100 Grainger Parkway, Lake Forest, Illinois 60045-5201
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE 1.07