

CLIMBING EQUIPMENT



#1 IN LADDERS™




# LEADING THE WAY IN

Once your feet leave the ground, you're in our world. From ladders to fall protection, Werner offers you a full line of climbing equipment that's engineered to provide maximum stability, safety and comfort at every height. Our products are designed to be used anywhere from the home to the most demanding job sites.

We continually strive to improve manufacturing techniques through ongoing testing and facility investment. Recognized for their durability, quality and safety, Werner products are developed based on application, industry research, product testing and customer insight to ensure the highest quality standards that meet the needs of our end users.



**LOCKTOP™**



**EDGE 360™**

Werner remains the market leader today by continually enhancing and improving its product offering. Recently, the Werner 6200 Series Stepladders were redesigned for better performance and productivity, which included an upgraded ladder top and enhanced bracing for overall durability. Our number one professional grade ladder series was upgraded specifically for professional contractors and continues to be a dependable tool on jobsites everywhere.

As part of our commitment to our customers, Werner is also focused on introducing new products and accessories to help users work more safely and efficiently. This commitment can be seen in cutting-edge product innovations that are unique and first to the industry, including the recent launch of the Podium, a new category of ladders. Podiums offer extra-large standing platforms allowing users to face any direction while working. The extended guardrail wraps around the user providing a feeling of safety while working and also secures tools and accessories at the top of the ladder, where they are needed. Based on the success of this new family of Podiums, the category will continue to expand with additional sizes, materials and casters for easy mobility.



***Work Facing Any Direction***



# CLIMBING SOLUTIONS

Recently, in the Extension Ladder category, Werner introduced two new innovations. Our Compact Extension Ladders were created to transport and store more easily than traditional two section ladders. The new Lightweight Performance Extension Ladders, designed for commercial and telecom professionals, are up to 12% lighter than standard extension ladders and will help minimize the risk of injury from lifting or transporting heavier ladders. As a result of our industry research, these new ladders will improve mobility, safety and worker efficiency, a tremendous value to trade professionals everywhere.

Both product research and development have been a huge point of differentiation for Werner over the years. To maintain our position as a world leader, Werner will continue to focus on global growth that brings the most progressive manufacturing facilities, products and people to our organization.

Through international expansion and continued investment in research, design, new products and marketing, we look forward to providing you with the finest climbing experience possible.




**#1 IN LADDERS™**





THE #1 BRAND IN PROFESSIONAL CLIMBING EQUIPMENT



# CHOOSING THE RIGHT LADDER FOR THE JOB

**1** Sectional ladders are designed for use by electrical, telephone and cable utilities. They provide versatility in applications where transit, storage or access requires short sections to be coupled together.



**2** Truck rack to transport ladders, lumber on top of vehicle to jobsite.

**3** Van racks used primarily in the paint industry to transport ladders safely to jobsite.

**4** Single one-section non-extendable ladders provide easy access to mid-range heights.



**5** Steel rolling scaffold has 1000 lbs. load capacity. Sets up with 1 person. Add additional sections for more height. No tools required. Easily moves from one room to another for maximum productivity.



**6** Twin step stools are ideal for using with planks.



**7** Special purpose work stands are great for wallboard installers and general contractors.



**8** Extension ladders are available in a wide assortment of types and sizes. They can handle an extremely wide range of tasks at varying elevations and are the most popular on construction and job sites.



**9** Complete pump jack system designed for siding applications. Adjusts to easily work at the height specific to the job. Allows workers to work from side to side safely at various heights.



**10** Create productive climbing equipment systems with extension ladders, ladder jacks and aluminum stages.



**11** Lightweight, sturdy and compact step stools are handy for many applications. Unlike regular stepladders, you can stand on the top platform.



**12** Fall protection self retracting lifeline(SRL), harness and anchor used on i-beam application.



**13** Fall protection harness and positioning lanyard used at elevated heights for protection against falls. Ideal application on rebar.



**14** Stockr's Ladder®s combine a twin stepladder with a revolutionary warehouse type ladder with a large platform.



**15** Stepladders are the most popular of all ladder styles. These ladders are often used for applications at low or medium heights. Ladder tops and pail shelves can hold tools, small parts and paint buckets.



**16** Podium ladders are ideal for working at fixed heights. The extra large platform allows you to work facing any direction. The extended guard rail wraps around the user and holds tools and equipment.



**17** Tripod ladders with 3 legs go where traditional ladders cannot. The back rail fits easily into tight corners and other confined spaces. Often used by electricians for installing wire between framing studs.



**18** Compact fiberglass extension ladder has a 3-piece design with all the same features as a traditional extension ladder. The smaller, compact design allows it to fit through tight spaces and maneuver more easily on jobsites. Easily fits on top of or in work vehicles.



**19** The telescoping multi-ladder can be used as a stepladder, extension ladder, stairway ladder or two scaffold bases. 4 ladders in 1 with multiple heights.



**20** The extension trestle ladder has an adjustable center trestle system. Often used in pairs with either a 12" or 14" wide stage or plank to work inside industrial buildings and by sign hangers to work for long periods of time at fixed heights.



**21** Manhole ladder used to access manholes in roadways. Hoop style end caps for removing ladder from manhole easily.





# THE #1 BRAND IN PROFESSIONAL CLIMBING EQUIPMENT


## CHOOSING THE RIGHT LADDER FOR THE JOB

### STEP 1 SELECT HEIGHT (SIZE)

STEPLADDERS	
Ladder Height	Maximum Reach*
4'	8'
6'	10'
7'	11'
8'	12'
10'	14'
12'	16'
14'	18'
16'	20'

Average Heights

EXTENSION LADDERS		
Ladder Height	Maximum Reach*	Height To Gutter or Top Support Point††
16'	15'	9' max.
20'	19'	9' to 13'
24'	23'	13' to 17'
28'	27'	17' to 21'
32'	31'	21' to 25'
36'	34'	25' to 28'
40'	37'	28' to 31'



\*Assumes a 5'6" person with a vertical 12" reach.

†† Support points for extension ladders reflect section overlap, ladder angle, or 3' extension above roof line.

### STEP 2 SELECT PERFORMANCE (DUTY RATING)

WERNER PERFORMANCE SYSTEM<sup>®</sup>

**Color Match for Ladder Performance.**

★ <b>200 lbs.</b>	★★ <b>225 lbs.</b>	★★★ <b>250 lbs.</b>	★★★★ <b>300 lbs.</b>	★★★★★ <b>375 lbs.</b>
----------------------	-----------------------	------------------------	-------------------------	--------------------------

200 lbs.*	Economical design for lightweight use	Type III
225 lbs.*	Basic design for simple projects	Type II
250 lbs.*	Designed to handle most projects and jobs	Type I
300 lbs.*	Rugged performance designed with the pro in mind	Type IA
375 lbs.*	Maximum performance and durability for the toughest jobs	Type IAA

Includes User and Materials

### STEP 3 SELECT MATERIAL

**FIBERGLASS**

For working around electricity  
Non-conductive side rails

**ALUMINUM**

Not for use around electricity  
Lightweight



# CHOOSING THE RIGHT LADDER FOR THE JOB

## PRODUCT CERTIFICATIONS

Werner ladders are manufactured and tested to the strictest quality standards. All Werner ladders meet or exceed American National Standards Institute (ANSI) and Occupational Safety and Health Administration (OSHA) requirements, where applicable.



### OCCUPATIONAL SAFETY AND HEALTH ADMINISTRATION CODE

All Type II, I, IA and IAA fiberglass, aluminum and wood ladders, ladder jacks and extension planks meet or exceed code. OSHA CODE applies to ladders used in the workplace. Werner Co. recommends Type II or heavier duty rated ladders for these applications.



### AMERICAN NATIONAL STANDARDS INSTITUTE

### PRODUCT LINES MEET OR EXCEED ANSI CODE

Fiberglass Ladders .... A14.5 (2007)  
Aluminum Ladders ..... A14.2 (2007)  
Ladder Jacks ..... A10.8 (2001)  
Extension Planks ..... A10.8 (2001)  
Scaffolding ..... A10.8 (2001)  
Stages ..... A10.8 (2001)  
Work Platforms ..... A10.8 (2001)  
Attic Ladders..... A14.9 (2010)



## CLIMBING PRO<sup>SM</sup>

SAFETY TRAINING

This online training program is designed to help you provide state-of-the-art training. Climbing Pro offers an interactive way to educate users how to safely climb.

- New and improved courses
- Monitoring and measurement tools for reporting to key customers

[www.wernerclimbingpro.com](http://www.wernerclimbingpro.com)

### Online Courses

- Knowledge check points throughout courses
- Stop and restart as you need, keeps track of where you left off
- Multimedia and interactive simulations
- Ongoing updates for additional courses



**THE #1 BRAND IN PROFESSIONAL  
CLIMBING EQUIPMENT**

**TABLE OF CONTENTS**

<b>SERIES/MODEL</b>	<b>PAGE</b>
<b>FIBERGLASS STEPLADDERS</b>	<b>1</b>
7400 SERIES	1
T7400 SERIES	2
P7400 SERIES	2
PT7400/PT7400-4C SERIES	3
E7400 SERIES	3
OBEL00 SERIES	4
OBCN00 SERIES	4
7300 SERIES	5
6200 SERIES	6
T6200 SERIES	6
P6200 SERIES	7
FTP6200 SERIES	7
SSF00 SERIES	8
TW6200 SERIES	8
6202 MODEL	8
T6202 MODEL	8
6100 SERIES	9
6002 MODEL	9
6000 & 6000S SERIES	10
T6000 SERIES	10
PT6000/PT6000-4C SERIES	11
5900 & 5900S SERIES	11
FIBERGLASS STEPLADDER COMPARISON CHART	12
<b>FIBERGLASS PODIUMS</b>	<b>13</b>
PD7300/PD7300-4C SERIES	14
PD6200/PD6200-4C SERIES	14
<b>FIBERGLASS EXTENSION LADDERS</b>	<b>15</b>
D7100-2LV SERIES	15
D7100-2 SERIES	15
7100-2/7100-1 SERIES	16
D8200-2EQ SERIES	16
D7200-2 SERIES	17
D6400-2 SERIES	17
D6200-2/D6200-1 SERIES	18
D6200-3 SERIES	18
D6000-2 SERIES	19
D5900-2 SERIES	19
FIBERGLASS EXT. LADDER COMPARISON CHART	20

<b>SERIES/MODEL</b>	<b>PAGE</b>
<b>FIBERGLASS SPECIALTY LADDERS</b>	<b>21</b>
7800 SERIES	21
M7100-1 SERIES	21
S7900 SERIES	22
9500-2/9500-1 SERIES	22
SPF00-1/TPF00-1 SERIES	23
S7700 SERIES	23
<b>ALUMINUM STEPLADDERS</b>	<b>24</b>
400 SERIES	24
T400 SERIES	24
P400 SERIES	25
370 SERIES	25
T370 SERIES	26
P370 SERIES	26
PT370 SERIES	27
SH378 MODEL	27
SSA00 SERIES	28
TW370-30 SERIES	28
150B MODEL	28
T372 MODEL	28
360 SERIES	29
350 SERIES	29
260 SERIES	30
244 MODEL	30
ALUMINUM STEPLADDER COMPARISON CHART	31
<b>ALUMINUM EXTENSION LADDERS</b>	<b>32</b>
500-1 SERIES	32
D500-2	32
D1500-2/D1500-1 SERIES	33
560-3 MODEL	33
D1800-2EQ SERIES	34
D1700-2EQ SERIES	34
D1300-2 SERIES	34
D1200-2 SERIES	35
D1200-3 SERIES	35
D1100-2 SERIES	36
D716-2 MODEL	36
ALUMINUM EXT. LADDER COMPARISON CHART	37



## TABLE OF CONTENTS

SERIES/MODEL	PAGE
<b>MULTILADDERS</b>	<b>38</b>
MT SERIES	38
M1 SERIES	38
<b>ATTIC LADDERS</b>	<b>39</b>
AH SERIES	39
AA1510 MODEL	39
WH SERIES	40
W SERIES	40
ATTIC LADDER COMPARISON CHART	41
<b>PORTABLE SCAFFOLDING</b>	<b>42</b>
AP-SERIES	42
PS-48 MODEL	43
SRS-72 MODEL	43
<b>WORK PLATFORMS</b>	<b>44</b>
PA200 SERIES	44
5600 SERIES	44
5500 SERIES	44
5300 SERIES	44
<b>PUMP JACKS</b>	<b>45</b>
ALUMINUM PUMP JACK SYSTEM	45
STEEL PUMP JACK SYSTEM	46
<b>SCAFFOLDING &amp; STAGES</b>	<b>47</b>
ALUMINUM TASK-MASTER® STAGES	47
GUARD RAIL SYSTEMS	48
ALUMINUM SCAFFOLD TOWERS	50
SCAFFOLD SECTIONS	51
SCAFFOLD COMPONENTS	52
SCAFFOLD/OUTRIGGER COMPONENT COMPARISON CHART	53
<b>RAMPS, RACKS &amp; MERCHANDISING</b>	<b>54</b>
R522 MODEL - FOLDING ARCHED RAMPS	54
R402 MODEL - ARCHED RAMPS	54
R301 MODEL - STRAIGHT RAMPS	55
R102 MODEL - STRAIGHT RAMP KIT	55
TR401-S MODEL - TRUCK RACK	56
VR401-W MODEL - VAN RACK	57
MERCHANDISING MODULAR LADDER DISPLAYS & FIXTURES	57

SERIES/MODEL	PAGE
<b>ACCESSORIES</b>	<b>58</b>
HOW TO ORDER	58
FACTORY INSTALLED ACCESSORY KITS	
LOCK-IN ACCESSORIES (AC27-P, AC27-L, AC50-JB-3)	59
LOCK-IN ACCESSORIES (AC52-UB, AC54-JC, AC56-UH, AC58-TL)	60
STEPLADDER ACCESSORIES (AC11, PK76, 76, 21, 22, AC24, 40)	61
EXTENSION LADDER ACCESSORIES (LADDER JACKS, AC18MT, AC19, AC22, ROOF BRACKETS, AC20, AC78)	62
EXTENSION LADDER ACCESSORIES (AC96, PK70-1/APK70, PK70-2, PK70-3, PK80/APK80, A61, A62)	63
EXTENSION LADDER ACCESSORIES (64-2,66-1/A66-1, 71/A71, 72/A72, 74/A74, A78)	64
EXTENSION LADDER ACCESSORIES (81/A81, A82, A83, 86/A86, 89, 91, 92/A92)	65
EXTENSION & ATTIC LADDER ACCESSORIES (94, 97P, AC59, 36-82)	66
<b>INDEX</b>	<b>67-68</b>



# THE BEST TOPS IN THE INDUSTRY



Next generation ladder top holds an arsenal of tools



Customize your ladder top with the Lock-In Accessory System



Sturdy paint can hanger decreases chances of spilling



Keeps tools within easy reach with the HolsterTop®



Convenient pail shelf provides additional work surface

## 7400SERIES

★★★★★ **375lbs.** LOAD CAPACITY **TYPE IAA** DUTY RATING

STYLE: Stepladder



\* Energy Diffusing Geometry

- Every rivet backed up by metal plate or washer to protect rails

### SPECIFICATIONS

Model No.	Size	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
7403	3'	19-3/4"	24-3/8"	2.5	13.5
7404	4'	21-1/2"	30-1/2"	3.5	16.5
7405	5'	23-1/4"	36-3/4"	4.6	20.0
7406	6'	25"	42-7/8"	5.8	23.5
7407	7'	26-3/4"	49"	7.1	28.0
7408	8'	28-1/2"	55-1/4"	8.5	32.0
7410	10'	32"	67-1/2"	11.4	40.5
7412	12'	35-1/2"	79-7/8"	14.8	49.5

### DIMENSIONS

Top:	7-1/4" x 14-7/8"	Steps:	3" wide
Front Rails:	3-1/8" wide	Rear Rails:	1-7/8" wide
Front Flange:	1-3/16" wide	Rear Flange:	1-3/16" wide

# WERNER®

# T7400SERIES

★★★★★ **375lbs.** LOAD CAPACITY **TYPE IAA**  
**PER SIDE** DUTY RATING

**STYLE: Multi-Use Twin Stepladder††**



- \* Energy Diffusing Geometry
- Every rivet backed up by metal plate or washer to protect rails

**SPECIFICATIONS** NOTE: Type IAA duty rating is for stepladders up to 12 ft.

Model No.	Size	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
T7404	4'	21-1/2"	36-1/8"	4.5	21.5
T7405	5'	23-1/2"	43-1/8"	5.8	29.0
T7406	6'	25"	50-1/8"	7.3	30.0
T7408	8'	28-1/2"	64-1/8"	10.5	40.5
T7410	10'	32"	78-1/4"	14.2	51.5
T7412	12'	35-1/2"	92-1/4"	18.3	63.5

★★★★★ **300lbs.** LOAD CAPACITY **TYPE IA**  
**PER SIDE** DUTY RATING

T7414	14'	39"	106-1/4"	22.8	86.0
T7416	16'	42-1/2"	120-1/4"	27.7	103.5
T7418	18'	46"	136-1/8"	33.1	126.0
T7420	20'	49-1/2"	150-1/8"	38.8	149.0

††Designed for one or two person jobs. Note: When used as a double stepladder, the maximum load per side, including person and materials, shall not exceed the duty rating of ladder.

**DIMENSIONS**

Top:	8-1/4" x 14-1/2"	Steps:	3" wide
Rails:	3-1/8" wide	Flange:	1-3/16" wide

# P7400SERIES

★★★★★ **375lbs.** LOAD CAPACITY **TYPE IAA**  
**PER SIDE** DUTY RATING

**STYLE: Platform Ladder**



- \* Energy Diffusing Geometry
- Every rivet backed up by metal plate or washer to protect rails
- Internal aluminum spreaders on 8' and 10' models

**SPECIFICATIONS** NOTE: Type IAA duty rating is for platforms ranging in size from 3' to 8'

Model No.	Height (Size) to Platform	Rail Length	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
P7403	3'	5'	25-1/4"	35-7/8"	5.1	22.0
P7404	4'	6'	27"	42"	6.4	26.0
P7406	6'	8'	30-1/2"	54-3/8"	9.1	34.0
P7408	8'	10'	34"	66-5/8"	12.2	44.5

★★★★★ **300lbs.** LOAD CAPACITY **TYPE IA**  
**PER SIDE** DUTY RATING

P7410	10'	12'	37-1/2"	79"	15.6	54.5
P7412	12'	14'	42"	91-1/4"	19.3	68.5

††Designed for one or two person jobs. Note: When used as a double stepladder, the maximum load per side, including person and materials, shall not exceed the duty rating of ladder.

**DIMENSIONS**

Platform:	14-5/8" x 15"	Steps:	3" wide
Front Rails:	3-1/8" wide	Rear Rails:	1-7/8" wide
Front Flange:	1-3/16" wide	Rear Flange:	1-3/16" wide



## PT7400/PT7400-4C SERIES

★★★★ **300 lbs.** LOAD CAPACITY **TYPE IA**  
**PER SIDE** DUTY RATING

**STYLE: Stockr's Ladder®††**



- Easy to handle and folds to a 12" width for storage
- Unique combination of one person, two person†† and platform ladder use
- Internal Pinch-Proof™ aluminum spreaders on 8' and 10' models
- Requires less floor space than heavy steel rolling ladders

### SPECIFICATIONS

Model No.	Height (Size) to Platform	Rail Length	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.	Model No. with Casters	Approx. Shipping Wt. Lbs.
PT7404	4'	6'	25-1/4"	50"	8.4	31.0	PT7404-4C	37.0
PT7406	6'	8'	28-3/4"	64"	12.7	41.5	PT7406-4C	53.0
PT7408	8'	10'	32-1/4"	78-1/4"	17.8	54.5	PT7408-4C	60.5
PT7410	10'	12'	35-3/4"	92-1/4"	23.7	66.0	PT7410-4C	72.5

††Designed for one or two person jobs. Note: When used as a double stepladder, the maximum load per side, including person and materials, shall not exceed the duty rating of ladder.


### DIMENSIONS

Platform:	12-3/4" x 22"	Steps:	3" wide
Rails:	3-1/8" wide	Flange:	1-3/16" wide

## E7400 SERIES

★★★★ **300 lbs.** LOAD CAPACITY **TYPE IA**  
**PER SIDE** DUTY RATING

**STYLE: Extension Trestle Ladder††**



### SPECIFICATIONS

Model No.	Stepladder Size	Base Section Bottom Width	Approx. Spread	Approx. Extended Ladder Height	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
E7408	8'	32-3/4"	67-3/4"	12'	16.6	74.0
E7410	10'	36-1/4"	81-7/8"	15'	22.2	95.5
E7412	12'	39-3/4"	95-7/8"	19'	28.3	113.5
E7414	14'	43-1/4"	109-3/4"	22'	35.1	135.5
E7416	16'	46-3/4"	123-3/4"	26'	42.4	158.0

††Designed for one or two person jobs. Note: When used as a double stepladder, the maximum load per side, including person and materials, shall not exceed the duty rating of ladder.

### DIMENSIONS

Extended Ladder	Stepladder
Rails: 3-3/8" wide	Rails: 3-3/16" wide (8'-12') 3-5/16" wide (14'-16')
Rungs: 1-1/4"	Steps: 3" wide
Flange: 1-3/16" wide	Flange: 1-3/16" wide

# OBEL00SERIES

★★★★★ **375lbs.** LOAD CAPACITY TYPE IAA DUTY RATING

**STYLE: Old Blue® Series Electrician's Jobstation™**



**COMPATIBLE**  
SEE PAGES 59-60


Customized HolsterTop® with Lock-In Accessory System secures tools from falling. 3 ToolLassos included.



Convenient conduit cutting system



HolsterTop® customized for electricians



Built-in wire spool holders for both large and small spools

\* Energy Diffusing Geometry

• Every rivet backed up by metal plate or washer to protect rails

© The blue and yellow ladder is an exclusive registered trademark of Werner Co.

## SPECIFICATIONS

Model No.	Size	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
OBEL04	4'	19-7/8"	29"	3.0	16.0
OBEL06	6'	23-3/8"	41-1/4"	5.3	24.0
OBEL08	8'	26-7/8"	53-5/8"	8.1	32.0
OBEL10	10'	30-3/8"	65-7/8"	12.5	41.0
OBEL12	12'	33-7/8"	78-1/4"	15.0	51.5

## DIMENSIONS

Top:	5-3/4" x 13"	Steps:	3" wide
Front Rails:	3-1/8" wide	Rear Rails:	1-7/8" wide
Front Flange:	1-3/16" wide	Rear Flange:	1-3/16" wide

# OBCN00SERIES

★★★★★ **375lbs.** LOAD CAPACITY TYPE IAA DUTY RATING

**STYLE: Old Blue® Series Contractor's Jobstation™**




**COMPATIBLE**  
SEE PAGES 59-60

Customized HolsterTop® with Lock-In Accessory System secures tools from falling. 3 ToolLassos included.



MagnaGrip™ heavy duty magnet secures hardware



HolsterTop® customized for contractors



Multi-Use hook for hanging tools and buckets

\* Energy Diffusing Geometry

• Every rivet backed up by metal part or washer to protect rails

© The blue and yellow ladder is an exclusive registered trademark of Werner Co.

## SPECIFICATIONS

Model No.	Size	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
OBCN06	6'	23-3/8"	41-1/4"	5.3	23.0
OBCN08	8'	26-7/8"	53-5/8"	8.1	31.0

## DIMENSIONS

Top:	5-3/4" x 13"	Steps:	3" wide
Front Rails:	3-1/8" wide	Rear Rails:	1-7/8" wide
Front Flange:	1-3/16" wide	Rear Flange:	1-3/16" wide





# The Best Just Got Better.

Trusted by professionals for their durability, our core line has been upgraded with new, advanced features to maximize your productivity.

## LOCKTOP™ NEXT GENERATION LADDER TOP



### HOLDS AN ARSENAL OF TOOLS



## EDGE 360™

### PROTECTION FROM EVERY ANGLE



#### INTEGRATED RAIL SHIELD

Protects rail during vehicle off-loading and maneuvering on the jobsite



#### EDGE BRACING

Supports rail and step



#### OVER-SIZED FEET & FOOT PADS

Stability while you work

## 7300SERIES

★★★★★ **375lbs.** LOAD CAPACITY **TYPE IAA** DUTY RATING

### STYLE: Stepladder



- \* EDGE360™ features Intergrated Rail Shields, Energy Diffusing Geometry, and Oversized Foot Pads
- Every rivet backed up by metal plate or washer to protect rails

#### SPECIFICATIONS

Model No.	Size	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.	Model No. with Pail Shelf	Approx. Shipping Wt. Lbs.
7303	3'	19-3/4"	23-1/2"	2.5	13.0	7303S	16.5
7304	4'	21-1/2"	29-3/4"	3.5	16.0	7304S	19.5
7305	5'	23-1/4"	35-7/8"	4.6	19.5	7305S	23.0
7306	6'	25"	42"	5.8	22.5	7306S	26.0
7308	8'	28-1/2"	54-3/4"	8.5	31.0	7308S	34.0
7310	10'	32"	66-5/8"	11.4	40.5	7310S	43.5
7312	12'	35-1/2"	79"	14.8	50.0	7312S	53.0

#### DIMENSIONS

Top:	7-1/4" x 14-7/8"	Steps:	3" wide
Front Rails:	3-1/8" wide	Rear Rails:	1-7/8" wide
Front Flange:	1-3/16" wide	Rear Flange:	1-3/16" wide

## 6200SERIES

★★★★ 300lbs.

LOAD CAPACITY

TYPE IA  
DUTY RATING

STYLE: Stepladder



COMPATIBLE  
SEE PAGES 59-60

**LOCKTOP™**

Next generation ladder top holds an arsenal of tools

4 rivets attach top to each front rail

Back-up plates reinforce all top connectors

Full set of rear horizontals spaced one per foot

Double riveted, slip-resistant Traction-Tred® steps

Heavy duty internal spreaders

All steps and two rear horizontals are knee-braced

Model 6206

EDGE360™ bracing system protects from every angle

- EDGE360™ features Intergrated Rail Shields, Energy Diffusing Geometry, and Oversized Foot Pads
- Every rivet backed up by metal plate or washer to protect rails
- Optional yellow molded pail shelf kit, model no. 76-2

### SPECIFICATIONS

Model No.	Size	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
6203	3'	18-1/8"	23-1/8"	2.0	13.0
6204	4'	19-7/8"	29"	3.0	16.0
6205	5'	21-5/8"	35-1/8"	4.1	19.0
6206	6'	23-3/8"	41-1/4"	5.3	22.0
6207	7'	25-1/8"	47-1/2"	6.6	26.0
6208	8'	26-7/8"	53-5/8"	8.1	30.0
6210	10'	30-3/8"	65-7/8"	12.5	39.0
6212	12'	33-7/8"	78-1/4"	15.0	48.0

### DIMENSIONS

Top:	5-3/4" x 13"	Steps:	3" wide
Front Rails:	3-1/8" wide	Rear Rails:	1-7/8" wide
Front Flange:	1-3/16" wide	Rear Flange:	1-3/16" wide

## T6200SERIES

★★★★ 300lbs.

LOAD CAPACITY

PER SIDE

TYPE IA  
DUTY RATING

STYLE: Twin Stepladder††

**LOCKTOP™**

Next generation dual ladder top holds an arsenal of tools

4 rivets attach top to each rail

Heavy duty internal spreaders

Double riveted, slip-resistant Traction-Tred® steps

All steps are knee-braced

Model T6206

EDGE360™ bracing system protects from every angle

- EDGE360™ features Intergrated Rail Shields, Energy Diffusing Geometry, and Oversized Foot Pads
- Every rivet backed up by metal plate or washer to protect rails

### SPECIFICATIONS

Model No.	Size	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
T6203	3'	18-1/8"	29"	3.1	16.0
T6204	4'	19-7/8"	36-1/8"	4.6	19.0
T6205	5'	21-5/8"	43-1/8"	6.2	23.0
T6206	6'	23-3/8"	50-1/8"	8.0	27.0
T6208	8'	26-7/8"	64-1/8"	12.3	37.0
T6210	10'	30-3/8"	78-1/8"	17.3	54.5
T6212	12'	33-7/8"	92-1/8"	23.2	68.5

††Designed for one or two person jobs. Note: When used as a double stepladder, the maximum load per side, including person and materials, shall not exceed the duty rating of ladder.

### DIMENSIONS

Top:	8-1/2" x 13"	Steps:	3" wide
Rails:	3-1/8" wide	Flange:	1-3/16" wide



## P6200 SERIES

★★★★ **300lbs.** LOAD CAPACITY

**TYPE IA**  
DUTY RATING

**STYLE: Platform Ladder**



- EDGE360™ features Intergrated Rail Shields, Energy Diffusing Geometry, and Oversized Foot Pads
- Every rivet backed up by metal plate or washer to protect rails
- Internal aluminum spreaders on 8' and 10' models

### SPECIFICATIONS

Model No.	Height (Size) to Platform	Rail Length	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
P6202	2'	4'	23-3/8"	29-3/4"	4.2	17.0
P6204	4'	6'	26-7/8"	42"	7.2	24.0
P6206	6'	8'	30-3/8"	54-3/4"	10.9	32.0
P6208	8'	10'	33-7/8"	66-5/8"	15.2	44.5
P6210	10'	12'	37-3/8"	79"	20.1	55.0

### DIMENSIONS

Platform:	14-5/8" x 15"	Steps:	3" wide
Front Rails:	3-1/8" wide	Rear Rails:	1-7/8" wide
Front Flange:	1-3/16" wide	Rear Flange:	1-3/16" wide

## FTP6200 SERIES

★★★★ **300lbs.** LOAD CAPACITY

**TYPE IA**  
DUTY RATING

**STYLE: Tripod Stepladder**



Single rear rail allows FTP Series to rest where other ladders can't



Convenient spreader handle design improves setup and transportability



Makes working in tight spaces easy

- Every rivet backed up by metal plate or washer to protect rails
- Internal aluminum spreaders on 8' and 10' models

### SPECIFICATIONS

Model No.	Size	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
FTP6204	4'	31"	30-1/2"	3.7	17.0
FTP6206	6'	36"	43-3/4"	6.8	23.0
FTP6208	8'	40"	57"	10.1	31.0
FTP6210	10'	51"	71"	17.6	42.0
FTP6212	12'	54"	77-3/4"	22.6	51.0

### DIMENSIONS

Top:	5-3/4" x 13"	Steps:	3" wide
Front Rails:	3-1/8" wide	Rear Rail:	1-1/2" square (4' to 8'), 2" square (10' and 12')
Flange:	1-3/16" wide		



## SSF00SERIES

★★★★★ **375lbs.** LOAD CAPACITY **TYPE IAA** DUTY RATING

**STYLE: Step Stand**



### SPECIFICATIONS

Model No.	Size	Maximum Standing Height	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
SSF02	2'	20"	17"	21"	2.6	15.0
SSF03	3'	30"	18-3/4"	27-1/2"	4.0	19.5


### DIMENSIONS

Top:	9" x 14"	Steps:	6" wide
Front Rails:	6" wide	Rear Rails:	1-7/8" wide
Front Flange:	1-1/8" wide	Rear Flange:	1-3/16" wide

## TW6200SERIES

★★★★★ **300lbs.** LOAD CAPACITY **PER SIDE** **TYPE IA** DUTY RATING

**STYLE: Portable Work Stand<sup>††</sup>**



### SPECIFICATIONS

Model No.	Size	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
TW6202	2'	31-1/4"	22-1/4"	3.0	17.0
TW6203	3'	32-3/4"	29-3/4"	4.7	24.0

<sup>††</sup> Designed for one or two person jobs. Note: When used as a double stepladder, the maximum load per side, including person and materials, shall not exceed the duty rating of ladder.

### DIMENSIONS

Top:	8" x 28"	Steps:	3" wide
Rails:	3-1/4" wide	Flange:	1-3/16" wide

## 6202MODEL

★★★★★ **300lbs.** LOAD CAPACITY **TYPE IA** DUTY RATING

**STYLE: Step Stool**



### SPECIFICATIONS

Model No.	Size	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
6202	2'	17-1/4"	19-1/2"	1.4	9.0


### DIMENSIONS

Top:	5-5/8" x 12-3/8"	Steps:	3" wide
Front Rails:	3-1/8" wide	Rear Rails:	1-3/4" wide
Front Flange:	1-3/16" wide	Rear Flange:	1-3/16" wide, 5/8" wide front

## T6202MODEL

★★★★★ **300lbs.** LOAD CAPACITY **PER SIDE** **TYPE IA** DUTY RATING

**STYLE: Twin Step Stool<sup>††</sup>**



### SPECIFICATIONS

Model No.	Size	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
T6202	2'	21-1/8"	23"	2.1	11.5

<sup>††</sup> Designed for one or two person jobs. Note: When used as a double stepladder, the maximum load per side, including person and materials, shall not exceed the duty rating of ladder.

### DIMENSIONS

Steps:	3" wide
Rails:	3-1/8" wide
Flange:	1-3/16" wide

Note: Planks or platforms shall be secured to the step stools. The ends of each plank or platform shall extend beyond the outside edge of each step stool by a minimum of 4 inches and a maximum of 10 inches.



## 6100 SERIES

★★★★ **300lbs.** LOAD CAPACITY **TYPE IA** DUTY RATING

**STYLE: Stepladder**



**COMPATIBLE**  
SEE PAGES 59-60

4 rivets attach top to each front rail

Braces on top and bottom steps and horizontals

Full set of rear horizontals spaced one per foot

HolsterTop® with Lock-In Accessory System secures tools from falling


Back-up plates reinforce all top connectors

Double riveted, slip-resistant Traction-Tred® steps

Heavy duty internal spreaders

Oversized, molded PROGUARD BOOTS™ provide firm slip-resistant footing and protect fiberglass rail

Model 6106



The Lock-In Accessory System lets you customize your ladder top and safely secure your tools.

### SPECIFICATIONS

Model No.	Size	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
6104	4'	19"	28-7/8"	2.6	15.0
6106	6'	22"	41-1/8"	4.5	21.0
6108	8'	25"	53-1/2"	6.8	30.0
6110	10'	28"	65-3/4"	13.0	35.5
6112	12'	31"	78-1/8"	17.3	44.0

### DIMENSIONS

Top:	5-3/4" x 13"	Steps:	3" wide
Front Rails:	3-1/8" wide	Rear Rails:	1-7/8" wide
Flange:	1-3/16" wide		

## 6002 MODEL

★★★ **250lbs.** LOAD CAPACITY **TYPE I** DUTY RATING

**STYLE: Step Stool**

Molded top provides large standing platform

Slip-resistant Traction-Tred® steps

External Pinch-Proof™ spreaders

Braces on bottom steps

©The blue and yellow ladder is an exclusive registered trademark of Werner Co.

### SPECIFICATIONS

Model No.	Size	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
6002	2'	17-1/4"	19-1/2"	1.4	8.5

### DIMENSIONS

Top:	5-5/8" x 12-3/8"	Steps:	3" wide
Front Rails:	3-1/8" wide	Rear Rails:	1-3/4" wide
Front Flange:	1-1/8" wide	Rear Flange:	1-3/16" wide back 5/8" wide front

# 6000 & 6000S SERIES

☆☆☆ **250lbs.** LOAD CAPACITY **TYPE I** DUTY RATING

**STYLE: Stepladder**



**COMPATIBLE**  
SEE PAGES 59-60

HolsterTop® with Lock-In Accessory System secures tools from falling

Sturdy paint can hanger on back side of top

Braces on top step, second step and top horizontal

External Pinch-Proof™ spreaders


Slip-resistant Traction-Tred® steps

Model 6006

Foot pads riveted to the EDGE®\* structure

\*Energy Diffusing Geometry

©The blue and yellow ladder is an exclusive registered trademark of Werner Co.



The Lock-In Accessory System lets you customize your ladder top and safely secure your tools.

EDGE® bracing provides enhanced strength and increased protection against damage

## SPECIFICATIONS

Model No.	Size	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.	Model No. with Pail Shelf	Approx. Shipping Wt. Lbs.
6004	4'	19"	28-7/8"	2.6	13.0	6004S	15.0
6005	5'	20-1/2"	35"	3.5	16.0	6005S	18.0
6006	6'	22"	41-1/8"	4.5	18.0	6006S	20.0
6008	8'	25"	53-1/2"	6.8	25.5	6008S	27.5

## DIMENSIONS

Top:	5-3/4" x 13"	Steps:	3" wide
Front Rails:	3-1/8" wide	Rear Rails:	1-3/4" wide
Front Flange:	1-1/8" wide	Rear Flange:	1-3/16" wide back 5/8" wide front

# T6000 SERIES

☆☆☆ **250lbs. PER SIDE** LOAD CAPACITY **TYPE I** DUTY RATING

**STYLE: Multi-Use Twin Stepladder††**

High performance dual HolsterTop®, paint and tool holder

Back-up aluminum plates reinforce all top connectors

Braces on top steps and bottom three steps

External Pinch-Proof™ spreaders

Slip-resistant Traction-Tred® steps on front and rear sections

Rubber step bumpers to resist damage

Model T6008

EDGE®\* molded brace and foot pad combination provides enhanced bracing strength and increased protection against damage

\* Energy Diffusing Geometry

- Every rivet backed up by metal plate or washer to protect rails
- ©The blue and yellow ladder is an exclusive registered trademark of Werner Co.

## SPECIFICATIONS

Model No.	Size	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
T6004	4'	19"	36-1/8"	4.5	17.5
T6006	6'	22"	50-1/8"	7.9	24.5
T6008	8'	25"	64-1/8"	11.9	35.0

†† Designed for one or two person jobs. Note: When used as a double stepladder, the maximum load per side, including person and materials, shall not exceed the duty rating of ladder.

## DIMENSIONS

Top:	8-1/2" x 13"	Steps:	3" wide
Rails:	3-1/8" wide	Flange:	1-1/8" wide



## PT6000/PT6000-4C SERIES

★★★ **250lbs.** LOAD CAPACITY  
PER SIDE

**TYPE I**  
DUTY RATING

**STYLE: Stockr's Ladder®††**



- Easy to handle and folds to a 12" width for storage
- Unique combination of one person, platform ladder or two person ladder††
- External Pinch-Proof™ spreaders on 8' model
- Requires less floor space than heavy steel rolling ladders

### SPECIFICATIONS

Model No.	Height (Size) to Platform	Rail Length	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.	Model No. with Casters	Approx. Shipping Wt. Lbs.
PT6002	2'	4'	20"	36-1/2"	6.4	21.0	PT6002-4C	27.0
PT6003	3'	5'	22"	44"	8.5	24.5	PT6003-4C	31.0
PT6004	4'	6'	23"	51"	11.1	28.0	PT6004-4C	35.0
PT6006	6'	8'	26"	65-1/2"	16.7	39.0	PT6006-4C	47.0
PT6008	8'	10'	29"	80"	23.4	52.0	PT6008-4C	64.5

†† Designed for one or two person jobs. Note: When used as a double stepladder, the maximum load per side, including person and materials, shall not exceed the duty rating of ladder.

### DIMENSIONS

Platform:	12-3/4" x 22"	Steps:	3" wide
Rails:	3-1/8" wide	Flange:	1-1/8" wide

## 5900 & 5900S SERIES

★★ **225lbs.** LOAD CAPACITY

**TYPE II**  
DUTY RATING

**STYLE: Stepladder**



**COMPATIBLE**  
SEE PAGES 59-60



\* Energy Diffusing Geometry

- Optional yellow molded pail shelf kit, model no. 76-9 or PK76-9 available for 5900 series

### SPECIFICATIONS

Model No.	Size	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.	Model No. with Pail Shelf	Approx. Shipping Wt. Lbs.
5904	4'	19"	28-7/8"	2.6	11.5	N/A	N/A
5906	6'	22"	41-1/8"	4.5	16.0	5906S	16.5
5908	8'	25"	53-1/2"	6.8	22.5	5908S	23.0

### DIMENSIONS

Top:	5-3/8" x 13"	Steps:	3" wide
Front Rails:	3-1/8" wide	Rear Rails:	1-3/4" wide
Front Flange:	1-1/8" wide	Rear Flange:	1-3/16" wide

# FIBERGLASS STEPLADDER COMPARISON CHART



Features and Benefits	7400 SERIES	T7400 SERIES	P7400 SERIES	7300 SERIES	6200 SERIES	T6200 SERIES	P6200 SERIES	6100 SERIES	6000 SERIES	T6000 SERIES	5900 SERIES
	TYPE IAA	TYPE IAA/IA	TYPE IAA/IA	TYPE IAA	TYPE IA	TYPE IA	TYPE IA	TYPE IA	TYPE I	TYPE I	TYPE II
Slip-resistant Traction-Tred® steps	★	★	★	★	★	★	★	★	★	★	★
Slip-resistant foot pad	★	★	★	★	★	★	★	★	★	★	★
LOCKTOP™					★	★					
Aluminum drill HolsterTop®	★			★							
HolsterTop®								★	★	★	★
Aluminum top		★									
Lock-In Accessory System					★			★	★		★
Designed for one or two person jobs		★								★	
Slip-resistant Traction-Tred® steps all knee braced	★	★	★	★	★	★	★				
Molded braces	★	★	★	★	★	★	★		★	★	★
Rail shields	★	★	★	★	★	★	★				
Oversized Foot Pads				★	★	★	★				
Internal spreaders	★	★		★	★	★		★			
External spreaders									★	★	★
Full set of rear horizontals	★		★	★	★		★	★			
Platform for comfortable work area			★				★				
Shoulder bolt and nut on top hinge	★	★	★	★		★	★			★	
Back-up plates to reinforce top connectors	★	★	★	★	★	★	★	★	★	★	★
Every rivet backed up by metal plate or washer to protect fiberglass	★	★	★	★	★	★	★	★	★	★	★
4 rivets attach top to each front rail	★	★	★	★	★	★	★	★			



# PODIUM



*Work facing any direction.*

- **4X WORK ZONE**

Allows you to work facing any direction so you can accomplish more without having to reposition your ladder.

- Ideal for working at fixed heights and easier to maneuver than scaffolds or lifts.
- Feel like you're standing on the ground with the extra-large platform, 36" high extended guard rail and LOCKTOP™ wrap around ladder top.
- Available in Type IAA (375lb capacity) and Type IA (300lb capacity) Duty Ratings
- Available with factory-installed casters for improved mobility



Extended guard rail securely wraps around work zone and holds an arsenal of tools



Extra-large standing platform for long standing comfort

# PD7300SERIES

★★★★★ **375lbs.** LOAD CAPACITY **TYPE IAA** DUTY RATING

**STYLE: Podium Ladder**



**COMPATIBLE**  
SEE PAGES 59-60



Extended guard rail holds an arsenal of tools

4 rivets attach top to each rail

Extra Large Platform with toe guard

Full set of rear horizontals spaced one per foot

Double riveted, slip-resistant Traction-Tred® steps

All steps are knee-braced

Model PD7304



PD7300-4C series features durable caster assemblies with stainless steel springs & heavy duty step braces

EDGE360™ bracing system protects from every angle

- Ideal for working at fixed heights, easier to maneuver than scaffolds or lifts
- Customize your ladder top with the Lock-In Accessory System
- EDGE360™ features Intergrated Rail Shields, Energy Diffusing Geometry, and Oversized Foot Pads
- Every rivet backed up by metal plate or washer to protect rails
- Internal aluminum spreaders on 6' and 8' models

## SPECIFICATIONS

Model No.	Height (Size) to Platform	Max. Reach	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.	Model No. with Casters	Approx. Shipping Wt. Lbs.
PD7303	3'	9'	26"	37"	9.2	21.0	PD7303-4C	28.3
PD7304	4'	10'	27-1/2"	43"	11.3	26.5	PD7304-4C	33.8
PD7306	6'	12'	31"	56"	16.4	38.5	PD7306-4C	45.8
PD7308	8'	14'	34-1/2"	68"	22.3	45.5	PD7308-4C	52.8

## DIMENSIONS

Platform:	16" x 19.5"	Steps:	3" wide
Front Rails:	3-1/8" wide	Rear Rails:	1-7/8" wide
Front Flange:	1-3/16" wide	Rear Flange:	1-3/16" wide

# PD6200SERIES

★★★★★ **300lbs.** LOAD CAPACITY **TYPE IA** DUTY RATING

**STYLE: Podium Ladder**



**COMPATIBLE**  
SEE PAGES 59-60



Extended guard rail holds an arsenal of tools

4 rivets attach top to each rail

Podium step with toe guard

Full set of rear horizontals spaced one per foot

Double riveted, slip-resistant Traction-Tred® steps

All steps are knee-braced

Model PD6204



PD6200-4C series features durable caster assemblies with stainless steel springs & heavy duty step braces

EDGE360™ bracing system protects from every angle

- Ideal for working at fixed heights, easier to maneuver than scaffolds or lifts
- Customize your ladder top with the Lock-In Accessory System
- EDGE360™ features Intergrated Rail Shields, Energy Diffusing Geometry, and Oversized Foot Pads
- Every rivet backed up by metal plate or washer to protect rails
- Internal aluminum spreaders on 8' and 10' models

## SPECIFICATIONS

Model No.	Height (Size) to Platform	Max. Reach	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.	Model No. with Casters	Approx. Shipping Wt. Lbs.
PD6203	3'	9'	26"	37"	9.2	21.0	PD6203-4C	28.3
PD6204	4'	10'	27-1/2"	43"	11.3	26.5	PD6204-4C	33.8
PD6206	6'	12'	31"	56"	16.4	32.5	PD6206-4C	39.8
PD6208	8'	14'	34-1/2"	68"	22.3	44.5	PD6208-4C	51.8
PD6210	10'	16'	38"	80"	29.1	55.5	PD6210-4C	62.8

## DIMENSIONS

Platform:	16" x 19.5"	Steps:	3" wide
Front Rails:	3-1/8" wide	Rear Rails:	1-7/8" wide
Front Flange:	1-3/16" wide	Rear Flange:	1-3/16" wide



## D7100-2LV SERIES

★★★★★ **375 lbs.** LOAD CAPACITY **TYPE IAA** DUTY RATING

**STYLE: D-Rung Extension Ladder with Integrated Leveling**



**Exclusive Alflo® rung joint means Twist-Proof® performance**

External guides at top of base section securely interlock rails


Slip-resistant Traction-Tred® D-rungs

Rugged gravity spring locks operate smoothly

Internal guides on bottom of fly section increase ease of operation

Factory installed LevelLok® Leveler enables ladder to adapt to uneven terrain.

With simple foot action, Leveler extends up to 10" in 3/16" increments



- Ideal for utility and telecommunication industries

LevelLok® is a registered trademark of the LevelLok Corporation.

**SPECIFICATIONS** NOTE: Type IAA duty rating is for extension ladders up to 32 feet

Model No.	Total Length of Sections	Max. Working Length	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
D7120-2LV	20'	17'	8.6	58.0
D7124-2LV	24'	21'	10.3	66.5
D7128-2LV	28'	25'	12.0	75.0
D7132-2LV	32'	29'	13.7	90.5

★★★★★ **300 lbs.** LOAD CAPACITY **TYPE IA** DUTY RATING

D7136-2LV	36'	32'	20.2	121.0
D7140-2LV	40'	35'	22.5	134.5

**DIMENSIONS**

	Rails:	Flange:	Rungs:	Fly Width:	Base Width:
20' to 32'	3-5/16"	1-3/16"	1-5/8"	16-1/8" outside rails	19" outside rails, 22-3/4" outside shoes
36' & 40'	4"	1-3/4"	1-3/4"	16-3/4" outside rails	22" outside rails, 25-3/4" outside shoes

## D7100-2 SERIES

★★★★★ **375 lbs.** LOAD CAPACITY **TYPE IAA** DUTY RATING

**STYLE: D-Rung Extension Ladder**



**Exclusive Alflo® rung joint means Twist-Proof® performance**

External guides at top of base section securely interlock rails

Heavy duty pulley with rope

Interlocking side rails

Base and fly separate easily to use base section as single ladder

Internal guides on bottom of fly section increase ease of operation

Durable rail shield and shoe bracket protects rail from damage

Mar-resistant molded end caps

Pre-pierced holes for easy field installation of accessories

Plate and rung assembly are riveted at four points to each side rail to allow for rung replacement

Slip-resistant Traction-Tred® D-rungs

Rugged gravity spring locks operate smoothly

Rope clamp ties rope to rung

Model D7120-2

Shoe with slip-resistant pad and spur plate

**SPECIFICATIONS** NOTE: Type IAA duty rating is for extension ladders up to 32 feet

Model No.	Total Length of Sections	Max. Working Length	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
D7116-2†	16'	13'	7.0	41.0
D7120-2	20'	17'	8.7	50.0
D7124-2	24'	21'	10.3	58.5
D7128-2	28'	25'	12.0	67.0
D7132-2	32'	29'	13.7	82.5

★★★★★ **300 lbs.** LOAD CAPACITY **TYPE IA** DUTY RATING

D7136-2	36'	32'	23.8	113.0
D7140-2	40'	35'	26.7	126.5

† Note: D7116-2 is not equipped with rope and pulley

**DIMENSIONS**

	Rails:	Flange:	Rungs:	Fly Width:	Base Width:
16' to 32'	3-5/16"	1-3/16"	1-5/8"	16-1/8" outside rails	19" outside shoes
36' and 40'	4"	1-3/4"	1-3/4"	16-3/4" outside rails	22" outside shoes




# 7100-2/7100-1SERIES

★★★★★ **375lbs.** LOAD CAPACITY **TYPE IAA** DUTY RATING

**STYLE: Round Rung Extension/Straight Ladder**



**Exclusive Alflo® rung joint means Twist-Proof® performance**



### SPECIFICATIONS

Model No.	Total Length of Sections	Max. Working Length	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.	Straight Ladder Model No.	Total Length	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
7116-2‡	16'	13'	7.0	38.5	7108-1	8'	4.5	20.0
7120-2	20'	17'	8.7	47.0	7110-1	10'	5.5	24.0
7124-2	24'	21'	10.3	55.0	7112-1	12'	6.5	28.0
7128-2	28'	25'	12.0	63.0	7114-1	14'	7.6	32.0
7132-2	32'	29'	13.7	78.0	7116-1	16'	8.6	40.0

★★★★★ **300lbs.** LOAD CAPACITY **TYPE IA** DUTY RATING

--	--	--	--	--	7118-1	18'	12.5	52.0
--	--	--	--	--	7120-1	20'	13.9	58.0

‡ Note: 7116-2 is not equipped with rope and pulley

### DIMENSIONS

	Rails:	Flange:	Rungs:	Width (outside rails):	Width (outside shoes):
7100-2: ALL 7100-1: 8' to 16'	3-5/16"	1-3/16"	1-1/4"	17-3/4" outside rails	19" outside shoes
7118-1, 7120-1	4"	1-3/4"	1-1/4"	16-13/16" outside rails	18-1/16" outside shoes

# D8200-2EQSERIES

★★★★★ **300lbs.** LOAD CAPACITY **TYPE IA** DUTY RATING

**STYLE: Extension Ladder with Integrated Leveling**



**Exclusive Alflo® rung joint means Twist-Proof® performance**

**THE Equalizer®**  
ELIMINATES UNEVEN GROUND



Model D8224-2EQ

Dual action feet for use on hard or penetrable surfaces

®The blue and yellow ladder is an exclusive registered trademark of Werner Co.

### SPECIFICATIONS

Model No.	Total Length of Sections	Max. Working Length	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
D8220-2EQ	20'	17'	10.0	54.0
D8224-2EQ	24'	21'	11.9	62.0
D8228-2EQ	28'	25'	13.8	70.0

### DIMENSIONS

Rails:	3-5/16" wide	Fly Width:	16" outside rails
Flange:	1-3/16" wide	Base Width:	17-3/4" outside rails, 21-7/16" outside of feet
Rungs:	1-5/8"		



# LIGHTWEIGHT PERFORMANCE SERIES

## STYLE: D-Rung Lightweight Extension Ladder



**Exclusive Alflo® rung joint means Twist-Proof® performance**

External guides at top of base section securely interlock rails.

Interlocking side rails

Base and fly separate easily to use base section as single ladder

Internal guides on bottom of fly section securely interlock rails

Rope clamp ties rope to rung

Mar-resistant molded end caps

Pre-pierced holes for easy field installation of accessories

Heavy duty pulley with rope

Rugged gravity spring locks operate smoothly

Slip-resistant Traction-Tred® D-rungs

Durable rail shield bracket and shoe with Shu-Lok®, slip-resistant pad and spur plate



**SAME PERFORMANCE**  
as D7100-2 & D6200-2 series,  
**LIGHTER WEIGHT**



New Fiberglass Technology allows ladder to be up to **12% lighter!**

Model D7224-2

Model D6424-2

## D7200-2 SERIES

★★★★★ **375lbs.** LOAD CAPACITY **TYPE IAA** DUTY RATING

### SPECIFICATIONS

Model No.	Total Length of Sections	Max. Working Length	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
D7216-2†	16'	13'	7.0	36.0
D7220-2	20'	17'	8.7	44.0
D7224-2	24'	21'	10.3	51.0
D7228-2	28'	25'	12.0	58.0

† Note: D7216-2 is not equipped with rope and pulley

### DIMENSIONS

Rails:	3-5/16" wide	Fly Width:	16-1/8" outside rails
Flange:	1-3/16" wide	Base Width:	19" outside shoes
Rungs:	1-5/8"		

## D6400-2 SERIES

★★★★ **300lbs.** LOAD CAPACITY **TYPE IA** DUTY RATING

### SPECIFICATIONS

Model No.	Total Length of Sections	Max. Working Length	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
D6416-2†	16'	13'	7.0	32.0
D6420-2	20'	17'	8.7	40.0
D6424-2	24'	21'	10.3	46.0
D6428-2	28'	25'	12.0	53.0

† Note: D6416-2 is not equipped with rope and pulley

### DIMENSIONS

Rails:	3-5/16" wide	Fly Width:	16" outside rails
Flange:	1-3/16" wide	Base Width:	19" outside shoes
Rungs:	1-5/8"		


# D6200-2/D6200-1 SERIES

★★★★ **300lbs.** LOAD CAPACITY TYPE IA DUTY RATING

**STYLE: D-Rung Extension/Straight Ladder**



**Exclusive Alflo® rung joint means Twist-Proof® performance**



## SPECIFICATIONS

Model No.	Total Length of Sections	Max. Working Length	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.	Single Ladder Model No.	Total Length	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
D6216-2†	16'	13'	7.0	36.5	D6208-1	8'	4.7	19.5
D6220-2	20'	17'	8.7	44.5	D6210-1	10'	5.8	23.0
D6224-2	24'	21'	10.3	52.0	D6212-1	12'	6.9	27.0
D6228-2	28'	25'	12.0	59.5	D6214-1	14'	8.0	31.0
D6232-2	32'	29'	13.7	71.5	D6216-1	16'	9.1	37.0
D6236-2	36'	32'	15.3	80.5	--	--	--	--
D6240-2	40'	35'	17.0	88.5	D6220-1	20'	11.5	45.5

† Note: D6216-2 is not equipped with rope and pulley

## DIMENSIONS

Rails:	3-5/16" wide	Fly Width:	16" outside rails
Flange:	1-3/16" wide	Base Width:	19" outside shoes
Rungs:	1-5/8"		


# D6200-3 SERIES

★★★★ **300lbs.** LOAD CAPACITY TYPE IA DUTY RATING

**STYLE: D-Rung Compact Extension Ladder**



**Exclusive Alflo® rung joint means Twist-Proof® performance**



‡ Note: D6216-3 is not equipped with rope and pulley

## SPECIFICATIONS

Model No.	Total Length of Sections	Total Length in Storage Position 2 vs. 3 piece*	Max. Working Length	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
D6216-3	18'	8' / 6'	13'	8.5	40.5
D6220-3	23'	10' / 8'	17'	11.1	54.0
D6224-3	27'	12' / 9'	21'	12.4	61.0
D6228-3	31'	14' / 11'	26'	15.0	74.5
D6232-3	35'	16' / 12'	29'	13.7	81.0

\* Total Length of ladder in storage position, comparison of Standard 2 - piece vs. New 3 - piece extension ladder.

## DIMENSIONS

Rails:	3-5/16" wide	Fly Width:	16" outside rails
Flange:	1-3/16" wide	Base Width:	19" outside shoes
Rungs:	1-5/8"		



## D6000-2SERIES


☆☆☆ **250lbs.** LOAD CAPACITY

**TYPE I**  
DUTY RATING

**STYLE: D-Rung Extension Ladder**



**Exclusive Alflo® rung joint means Twist-Proof® performance**



## D5900-2SERIES


☆☆ **225lbs.** LOAD CAPACITY

**TYPE II**  
DUTY RATING

**STYLE: D-Rung Extension Ladder**



**Exclusive Alflo® rung joint means Twist-Proof® performance**



©The blue and yellow ladder is an exclusive registered trademark of Werner Co.

### SPECIFICATIONS

Model No.	Total Length of Sections	Max. Working Length	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
D6016-2‡	16'	13'	7.0	32.5
D6020-2	20'	17'	8.7	39.0
D6024-2	24'	21'	10.3	46.0
D6028-2	28'	25'	12.0	55.5

‡ Note: D6016-2 is not equipped with rope and pulley

### DIMENSIONS

Rails:	3-3/8" wide	Fly Width:	15-3/4" outside rails
Flange:	1-3/16" wide	Base Width:	18-1/8" outside shoes
Rungs:	1-1/2"		

### SPECIFICATIONS

Model No.	Total Length of Sections	Max. Working Length	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
D5916-2‡	16'	13'	5.9	27.0
D5920-2	20'	17'	7.4	33.0
D5924-2	24'	21'	8.9	39.0


















‡ Note: D5916-2 is not equipped with rope and pulley

### DIMENSIONS

Rails:	3-5/16" wide	Fly Width:	15-1/8" outside rails
Flange:	1-3/16" wide	Base Width:	17-3/4" outside shoes
Rungs:	1-1/2"		

# FIBERGLASS EXTENSION LADDER COMPARISON CHART



Features and Benefits	D7200-2 SERIES	D7100-2LV SERIES	D7100-2 SERIES	7100 SERIES	D8200-2EQ SERIES	D6400-2 SERIES	D6200 SERIES	D6000-2 SERIES	D5900-2 SERIES
	TYPE IAA/IA	TYPE IAA/IA	TYPE IAA/IA	TYPE IAA	TYPE IA	TYPE IA	TYPE IA	TYPE I	TYPE II
 Guides at top of base section	★	★	★	★	★	★	★	★	
 Guides on bottom of fly section	★	★	★	★	★	★	★	★	★
 Pulley and rope systems	★	★	★	★	★	★	★	★	★
 Rail shield and shoe bracket protects rail	★	★	★	★	★	★	★	★	
 Shoe with slip-resistant pad and spur plate	★	★	★	★	★	★	★	★	★
 Rugged gravity spring locks	★	★	★	★	★	★	★	★	★
 Rope clamp ties rope to rung	★	★	★	★	★	★	★	★	★
 Alflo® rung joint for Twist-Proof® performance	★	★	★	★	★	★	★	★	★
Electrically non-conductive side rails	★	★	★	★	★	★	★	★	★
 Mar-resistant molded end caps	★	★	★	★	★	★	★	★	★
Base section may be used as a single ladder	★	★	★	★	★	★	★	★	★
 Pre-pierced holes for easy field installation of accessories	★	★	★	★	★	★	★		
 Plate and rung assembly to allow for rung replacement	★	★	★	★					
 Direct rung to rail connections					★	★	★	★	★
 Interlocking side rails	★	★	★	★	★	★	★	★	★
 Slip-resistant D-rungs	★	★	★		★	★	★	★	★
 Slip-resistant round rungs				★					
 Molded rung braces						★	★	★	★
 Integrated leveling		★			★				


## 7800SERIES

★★★★★ **375lbs.** LOAD CAPACITY TYPE IAA DUTY RATING

**STYLE: Combination Step/Extension Ladder††**



**Exclusive Alflo® rung joint means Twist-Proof® performance**



### SPECIFICATIONS

Model No.	Stepladder Size	Width at Flared Base (outside rails)	Stepladder Spread to Outside of Shoes	Length of Ladder in Closed Position	Extended Ladder Working Length	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
7806	6'	23-1/4"	46-1/2"	72-3/4"	9-1/2'	8.6	33.5
7807	7'	24-1/4"	53-1/2"	84-3/4"	11-1/2'	10.3	37.0
7808	8'	25-1/4"	60-1/2"	96-3/4"	13-1/2'	12.1	40.5

††Designed for one or two person jobs. Note: When used as a double stepladder, the maximum load per side, including person and materials, shall not exceed the duty rating of ladder.

### DIMENSIONS

	Parallel Section	Flared Section
Overlap	3'	--
Rails:	3-1/8" wide	3-1/8" wide
Flange:	1-3/16" wide	1-3/16" wide
Ladder Width:	14-1/2" outside rails	14-1/2" outside rails at top
Ladder in Closed Position:	--	7-7/8" deep

## M7100-1SERIES

★★★★★ **375lbs.** LOAD CAPACITY TYPE IAA DUTY RATING

**STYLE: Manhole Ladder**



**Exclusive Alflo® rung joint means Twist-Proof® performance**



### SPECIFICATIONS

Model No.	Total Length	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
M7108-1	8'	3.0	20.0
M7110-1	10'	3.7	24.0
M7112-1	12'	4.4	28.0
M7114-1	14'	5.2	32.0
M7116-1	16'	5.9	39.5

### DIMENSIONS

Rails:	3-5/16" wide	Rungs:	1-1/4"
Flange:	1-3/16" wide	Ladder Width:	12-3/8" outside shoes

# S7900SERIES

★★★★★ **375lbs.** LOAD CAPACITY  
**3 SECTIONS**


★★★★★ **300lbs.** LOAD CAPACITY  
**4 SECTIONS** **TYPE IA**  
 DUTY RATING

**STYLE: Interchangeable Tapered Sectional Ladder**



**Exclusive Alflo® rung joint means Twist-Proof® performance**

- Maximum number of sections to be used – 4



## SPECIFICATIONS

Model No.	Description	Top of Section	Bottom of Section	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
S7906-1	6' tapered base with swivel shoes	15-3/4"	19-3/4"	2.3	17.0
S7906-2	6' intermediate	15-3/4"	18-3/4"	3.5	15.5
S7906-3	6' top with molded end cap	16-3/16"	18-3/4"	3.4	13.0
S7901 (Accessory)	End cap for middle or base sections	N/A	N/A	0.1	1.0 ea.

## ASSEMBLY DESCRIPTION

Quantity of Sections	Model No.	Total Assembled Size
1	S7906-1 base	6' 2"
1	S7906-1 base	15' 11"
1	S7906-2 middle	
1	S7906-3 top	
1	S7906-1 base	20' 11"
2	S7906-2 middle	
1	S7906-3 top	


## DIMENSIONS

Rails:	3-5/16" wide
Flange:	1-3/16" wide
Rungs:	1-1/4" diameter

# 9500-2/9500-1SERIES

★★★★★ **300lbs.** LOAD CAPACITY  
**TYPE IA**  
 DUTY RATING

**STYLE: All-Fiberglass Extension/Straight Ladder**



## SPECIFICATIONS

Model No.	Total Length of Sections	Max. Working Length	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.	Single Ladder Model No.	Total Length	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
9516-2	16'	13'	8.3	41.0	9508-1	8'	5.5	18.0
9520-2	20'	17'	10.2	49.0	9510-1	10'	6.8	22.0
9524-2	24'	21'	12.2	56.0	9512-1	12'	8.0	26.0
9528-2	28'	25'	14.1	64.0	9514-1	14'	9.4	30.0
9532-2	32'	29'	16.0	72.0	9516-1	16'	10.7	34.0
					9518-1	18'	11.2	38.0
					9520-1	20'	12.5	42.0

## DIMENSIONS


Rails:	3-1/4" wide	Fly Width:	15-1/2" outside rails
Flange:	1-3/16" wide	Base Width:	19" outside shoes
Rungs:	1-1/4"		



## SPF00-1/TPF00-1 SERIES

★★★★ **300lbs.** LOAD CAPACITY **TYPE IA** DUTY RATING

**STYLE: Posting Ladder**



### SPECIFICATIONS

Model No.	Total Length	Length for Shipping	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
<b>Straight Posting Ladders (not shown above)</b>				
SPF14-1	14'	15'	6.0	38.0
SPF16-1	16'	17'	6.8	43.0
SPF18-1	18'	19'	7.6	49.0
SPF20-1	20'	21'	8.4	58.0
<b>Tapered Posting Ladders</b>				
TPF14-1	14'	15'	6.0	37.0
TPF16-1	16'	17'	6.8	42.0
TPF18-1	18'	19'	7.6	48.0
TPF20-1	20'	21'	8.4	57.0

### DIMENSIONS

Rails:	3-5/16" wide	Steps:	2-7/8" wide
Flange:	1-3/16" wide	Base Width:	14-5/8"

## S7700 SERIES

★★★ **250lbs.** LOAD CAPACITY **TYPE I** DUTY RATING

**STYLE: Interchangeable Parallel Sectional Ladder**




**Exclusive Alflo® rung joint means Twist-Proof® performance**

- Maximum number of sections to be used – 3

Slip-resistant Traction-Tred® round rungs

Sections joined by heavy duty extruded fittings and secured by a cam driven tension clamp



### SPECIFICATIONS

Model No.	Description	Top of Section	Bottom of Section	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
S7706-1	For manhole use - 6' length	12" wide	12" wide	2.1	15.5
<b>End Caps and Shoes</b>					
S7701	End cap (2 required)	N/A	N/A	0.1	1.5 ea.
S7702-1	Shoe with black EPDM pad (2 required)	N/A	N/A	0.1	1.5 ea.
S7702-2	Shoe with gray EPDM pad (2 required) Buna N Pad - Oil resistant	N/A	N/A	0.1	1.5 ea.

### ASSEMBLY DESCRIPTION

Max. No. of Sections	Approx. Max. Assembled Length
(3) assembled 6' sections with (1) pair of end caps and (1) pair of shoes	19'

### DIMENSIONS


Rails:	3-5/16" wide
Flange:	1-3/16" wide
Rungs:	1-1/4" diameter



# 400SERIES

★★★★★ **375lbs.** LOAD CAPACITY **TYPE IAA** DUTY RATING

**STYLE: Stepladder**



• Optional black molded pail shelf kit, model no. PK76-3

**SPECIFICATIONS** NOTE: Type IAA duty rating is for stepladders up to 12 ft.

Model No.	Size	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
404	4'	21-1/4"	30-1/8"	4.8	16.0
406	6'	24-3/4"	42-7/16"	8.1	24.0
408	8'	28-1/4"	54-3/4"	12.2	33.5
410	10'	31-3/4"	67"	17.0	43.5
412	12'	35-1/4"	79-3/8"	22.5	54.5

★★★★★ **300lbs.** LOAD CAPACITY **TYPE IA** DUTY RATING

414	14'	38-5/8"	91-11/16"	28.2	65.0
416	16'	42-1/8"	104"	34.7	77.5

**DIMENSIONS**

Top:	7" x 14"	Steps:	3" wide
Front Rails:	3-1/8" wide	Rear Rails:	1-3/4" wide
Front Flange:	1-1/8" wide	Rear Flange:	1" wide

# T400SERIES

★★★★★ **375lbs.** LOAD CAPACITY **PER SIDE** **TYPE IAA** DUTY RATING

**STYLE: Multi-Use Twin Stepladder††**



**SPECIFICATIONS**

Model No.	Size	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
T404	4'	21-1/4"	36-1/4"	5.0	21.5
T406	6'	24-3/4"	50-1/4"	8.8	31.0
T408	8'	28-1/4"	64-1/4"	13.3	42.0
T410	10'	31-3/4"	78-1/4"	18.7	55.0
T412	12'	35-1/4"	92-1/4"	25.0	69.0

†† Designed for one or two person jobs. Note: When used as a double stepladder, the maximum load per side, including person and materials, shall not exceed the duty rating of ladder.

**DIMENSIONS**

Top:	8-1/4" x 14"	Steps:	3" wide
Rails:	3-1/8" wide	Flange:	1-1/8" wide



**P400SERIES**

★★★★★ **375lbs.** LOAD CAPACITY **TYPE IAA** DUTY RATING

**STYLE: Platform Ladder**



Model P404

- Internal spreaders on 8' and above

**SPECIFICATIONS** NOTE: Type IAA duty rating is for platforms ranging in size from 4' to 8'

Model No.	Height (Size) to Platform	Rail Length	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
P404	4'	6'	24-3/4"	42-1/16"	7.1	25.0
P406	6'	8'	28-1/4"	54-3/4"	10.1	33.5
P408	8'	10'	31-3/4"	79-1/2"	20.3	45.5

★★★★★ **300lbs.** LOAD CAPACITY **TYPE IA** DUTY RATING

P410	10'	12'	35-1/4"	79-3/8"	20.3	54.5
P412	12'	14'	38-3/4"	91-11/16"	25.2	66.0
P414	14'	16'	42-1/4"	104"	31.1	79.5

**DIMENSIONS**

Platform:	12-5/8" x 15"	Steps:	3" wide
Front Rails:	3-1/8" wide	Rear Rails:	1-3/4" wide
Front Flange:	1-1/8" wide	Rear Flange:	1" wide

**370SERIES**

★★★★★ **300lbs.** LOAD CAPACITY **TYPE IA** DUTY RATING

**STYLE: Stepladder**



Model 376

- External Pinch-Proof™ spreaders on 3', 7', 8' and 10' models

**SPECIFICATIONS**

Model No.	Size	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
373	3'	17-3/4"	23-3/8"	1.5	9.0
374	4'	19-1/2"	29-1/2"	2.1	11.0
375	5'	21-1/4"	35-3/4"	2.8	13.5
376	6'	23"	41-7/8"	3.5	15.5
378	8'	26-1/2"	54-1/4"	5.1	22.5
310	10'	30"	66-1/2"	7.0	31.0

**DIMENSIONS**

Top:	5-1/8" x 12-1/8"	Steps:	3" wide
Front Rails:	3" wide	Rear Rails:	1-1/4" wide
Front Flange:	7/8" wide	Rear Flange:	1" wide

# T370SERIES

★★★★ **300lbs.** LOAD CAPACITY **TYPE IA**  
**PER SIDE** DUTY RATING

**STYLE: Multi-Use Twin Stepladder††**



- External Pinch-Proof™ spreaders on 4' model

## SPECIFICATIONS

Model No.	Size	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
T374	4'	21-1/4"	36"	3.5	14.5
T376	6'	24-3/4"	50"	5.7	21.5
T378	8'	28-1/4"	64"	8.2	31.0
T310	10'	31-3/4"	78"	11.1	43.0

†† Designed for one or two person jobs. Note: When used as a double stepladder, the maximum load per side, including person and materials, shall not exceed the duty rating of ladder.

## DIMENSIONS

Top:	8-1/4" x 14"	Steps:	3" wide
Rails:	3" wide	Flange:	7/8" wide

# P370SERIES

★★★★ **300lbs.** LOAD CAPACITY **TYPE IA**  
**DUTY RATING**

**STYLE: Platform Ladder**



- External Pinch-Proof™ spreaders on 8' model

## SPECIFICATIONS

Model No.	Height (Size) to Platform	Rail Length	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
P372	2'	4'	21-1/4"	30"	3.0	12.0
P373	3'	5'	23"	36-1/4"	3.9	14.5
P374	4'	6'	24-3/4"	42-3/4"	4.9	17.0
P376	6'	8'	28-1/4"	54-3/4"	7.1	23.0
P378	8'	10'	31-3/4"	67"	8.4	32.0

## DIMENSIONS

Platform:	12-5/8" x 18"	Steps:	3" wide
Front Rails:	3" wide	Rear Rails:	1-1/4" wide
Front Flange:	7/8" wide	Rear Flange:	1" wide



# PT370 SERIES

★★★★ **300 lbs.** LOAD CAPACITY **PER SIDE** TYPE IA DUTY RATING

STYLE: Stockr's Ladder®††



- Available with 4 casters to allow for easy 360° mobility
- Easy to handle and folds to a 10" width for storage
- Unique combination of one person, two person†† and platform ladder use
- Internal Pinch-Proof™ aluminum spreaders on 8' and 10' models

### SPECIFICATIONS

Model No.	Height (Size) to Platform	Rail Length	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.	Model No. with Casters	Approx. Shipping Wt. Lbs.
PT372	2'	4'	21-1/4"	36"	5.1	21.0	PT372-4C	27.5
PT374	4'	6'	24-3/4"	50-1/2"	8.9	27.0	PT374-4C	33.5
PT376	6'	8'	28-1/4"	65-1/4"	13.5	36.0	PT376-4C	42.5
PT378	8'	10'	31-3/4"	81-1/2"	19.0	46.5	PT378-4C	54.0
PT310	10'	12'	34-1/4"	96"	24.5	58.5	PT310-4C	66.5

†† Designed for one or two person jobs. Note: When used as a double stepladder, the maximum load per side, including person and materials, shall not exceed the duty rating of ladder.

### DIMENSIONS

Platform:	12-3/4" x 22"	Steps:	3" wide
Rails:	3" wide	Flange:	3/4" wide

# SH378 MODEL

★★★★ **300 lbs.** LOAD CAPACITY TYPE IA DUTY RATING

STYLE: Shelf Ladder



### SPECIFICATIONS

Model No.	Size	Approx. Width	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
SH378	8'	28-1/4"	3.9	15.5

### DIMENSIONS

Top:	7" x 14"	Steps:	3" wide
Rails:	3" wide	Flange:	7/8" wide

## SSA00SERIES

★★★★★ **375lbs.** LOAD CAPACITY **TYPE IAA** DUTY RATING

**STYLE: Step Stand**



### SPECIFICATIONS

Model No.	Size	Max. Standing Height	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
SSA02	2'	20"	17"	21"	2.6	16.0
SSA03	3'	30"	18-3/4"	27-1/2"	4.0	21.0

### DIMENSIONS

Top:	9" x 14"	Steps:	6" wide
Front Rails:	6" wide	Rear Rails:	1-7/8" wide
Front Flange:	1-1/8" wide	Rear Flange:	1-3/16" wide

## TW370-30SERIES

★★★★★ **300lbs.** LOAD CAPACITY **PER SIDE** **TYPE IA** DUTY RATING

**STYLE: Portable Work Stand<sup>††</sup>**



- Extra wide for versatile use as work stand, stage or material support
- Lightweight and portable

### SPECIFICATIONS

Model No.	Size	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
TW372-30	2'	33"	22"	4.0	12.5
TW373-30	3'	34-3/4"	29"	5.6	17.5
TW374-30	4'	36-1/2"	36"	7.8	24.0

<sup>††</sup>Designed for one or two person jobs. Note: When used as a double stepladder, the maximum load per side, including person and materials, shall not exceed the duty rating of ladder.

### DIMENSIONS

Top:	8" x 30"	Steps:	3" wide
Rails:	3" wide	Flange:	7/8" wide

## 150BMODEL

★★★★★ **300lbs.** LOAD CAPACITY **TYPE IA** DUTY RATING

**STYLE: Step Stool**



### SPECIFICATIONS

Model No.	Size	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
150B	2'	17"	19"	1.9	5.5


### DIMENSIONS

Top:	6" x 12-3/8"	Steps:	3" wide
Front Rails:	3" wide	Rear Rails:	1-1/8" wide
Front Flange:	3/4" wide	Rear Flange:	1" wide

## T372MODEL

★★★★★ **300lbs.** LOAD CAPACITY **PER SIDE** **TYPE IA** DUTY RATING

**STYLE: Twin Step Stool<sup>††</sup>**



- Folds to 7-1/4" width for easy storage

Note: Planks or platforms shall be secured to the step stools. The ends of each plank or platform shall extend beyond the outside edge of each step stool by a minimum of 4 inches and a maximum of 10 inches.

### SPECIFICATIONS

Model No.	Size	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
T372	2'	21-1/4"	23-3/8"	2.3	9.0

<sup>††</sup>Designed for one or two person jobs. Note: When used as a double stepladder, the maximum load per side, including person and materials, shall not exceed the duty rating of ladder.

### DIMENSIONS

Rails:	3" wide	Flange:	7/8" wide
Steps:	3" wide		



### 360 SERIES

☆☆☆ **250lbs.** LOAD CAPACITY **TYPE I** DUTY RATING

**STYLE: Stepladder**



Model 366

### 350 SERIES

☆☆ **225lbs.** LOAD CAPACITY **TYPE II** DUTY RATING

**STYLE: Stepladder**



Model 356

#### SPECIFICATIONS

Model No.	Size	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
363	3'	17"	23-1/4"	1.7	8.0
364	4'	18-1/2"	29-1/4"	2.4	10.5
365	5'	20"	35-1/2"	3.1	12.5
366	6'	21-1/2"	41-5/8"	3.9	14.5
368	8'	24-1/2"	54"	5.7	21.5

#### DIMENSIONS

Top:	5" x 12-3/8"	Steps:	3" wide
Front Rails:	3" wide	Rear Rails:	1-1/8" wide
Front Flange:	3/4" wide	Rear Flange:	1" wide

#### SPECIFICATIONS

Model No.	Size	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
354	4'	18-1/2"	29-1/4"	2.4	10.0
355	5'	20"	35-1/2"	3.1	12.0
356	6'	21-1/2"	41-5/8"	3.9	13.5

#### DIMENSIONS


Top:	4-5/8" x 12-1/2"	Steps:	3" wide
Front Rails:	3" wide	Rear Rails:	1-1/8" wide
Front Flange:	3/4" wide	Rear Flange:	1" wide

## 260SERIES

★ **200lbs.** LOAD CAPACITY

**TYPE III**  
DUTY RATING

### STYLE: Platform Ladder



Model 265

- Compact for convenient storage – folds to 3-1/2"

### SPECIFICATIONS

Model No.	Height (Size) to Platform	Rail Length	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
264	22-1/2"	4-1/2'	20"	25-1/2"	2.0	11.5
265	33-1/2"	5-1/2'	21-1/2"	33-1/4"	2.6	15.0

### DIMENSIONS

Platform:	14-1/2" x 12"	Steps:	3" wide
Front Tubular Rails:	1-1/8" diameter	Rear Tubular Rails:	1" diameter

## 244MODEL

★ **200lbs.** LOAD CAPACITY

**TYPE III**  
DUTY RATING

### STYLE: Utility Ladder



- Lightweight – easy action open-close
- Compact for convenient storage – folds to 3"

### SPECIFICATIONS

Model No.	Rail Length	Approx. Width	Approx. Spread	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
244	3-1/2'	18-1/2"	22-1/2"	1.4	9.0













### DIMENSIONS

Front Tubular Rails:	1-1/8" diameter	Steps:	6" wide
Rear Tubular Rails:	1" diameter	Height to 2nd Step:	23"





# ALUMINUM STEPLADDER COMPARISON CHART

Features and Benefits	400 SERIES	T400 SERIES	P400 SERIES	370 SERIES	T370 SERIES	P370 SERIES	PT370 SERIES	360 SERIES	350 SERIES
	TYPE IAA/IA	TYPE IAA	TYPE IAA/IA	TYPE IA	TYPE IA	TYPE IA	TYPE IA	TYPE I	TYPE II
 Slip-resistant foot pad	★	★	★	★	★	★	★	★	★
 Slip-resistant Traction-Tred® steps	★	★	★	★	★	★	★	★	★
 Dual drill HolsterTop®	★								
 External spreaders	4', 5', 8' models	4', 6' models		3', 8', 10' models				★	★
Designed for one or two person jobs		★			★		★		
 Knee-braced top & bottom steps	★	★	★	★	★	★	★	★	★
 Aluminum top	★	★	★		★	★			
Full set of rear horizontals	★		★	★		★			
 Spill-Proof® pail shelf with rag rack				★				★	★
 Tool-Tra-Top®	★			★				★	★
 Safety guard rail			★			★	★		
 Platform for comfortable work area			★			★	★		
 Paint can hanger on top				★				★	★
 H-spreader for one-handed carry & close				★					



# 500-1 SERIES

★★★★★ **375lbs.** LOAD CAPACITY **TYPE IAA** DUTY RATING

**STYLE: Round Rung Straight Ladder**



**Exclusive Alflo® rung joint means Twist-Proof® performance**



Extra heavy duty I-beam rails

Traction-Tred® deeply serrated aluminum round rungs

Model 508-1

**SPECIFICATIONS** NOTE: Type IAA duty rating is for single ladders up to 16 ft.

Model No.	Total Length	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
508-1	8'	2.9	16.5
510-1	10'	3.6	20.0
512-1	12'	4.3	24.0
514-1	14'	5.0	27.5
516-1	16'	5.7	37.0

★★★★★ **300lbs.** LOAD CAPACITY **TYPE IA** DUTY RATING

518-1	18'	6.4	41.0
520-1	20'	7.1	45.5
524-1	24'	14.0	60.5

**DIMENSIONS**

	Rails:	Flange:	Round Rungs:	Base Width:
8' to 14'	3" wide	1-3/16"	1-1/4"	16-7/8"
16' to 20'	3" wide	1-1/4"	1-1/4"	16-7/8"
24'	4" wide	1-3/8"	1-1/4"	20-5/8"


# D500-2 SERIES

★★★★★ **375lbs.** LOAD CAPACITY **TYPE IAA** DUTY RATING

**STYLE: D-Rung Extension Ladder**



**Exclusive Alflo® rung joint means Twist-Proof® performance**



Mar-resistant end caps notched for easy separation of sections

Extra heavy duty I-beam rails

Interlocking side rails

4-piece pulley with 3/8" rope. 36' to 48' models have heavy duty rope and double pulley system

Slip-resistant Traction-Tred® D-rungs

Base and fly separate easily for use as an extension or two single sections

Rugged spring loaded locks operate smoothly

Internal guides increase ease of operation

Molded slip-resistant shoes for use as a single section

Heavy duty, self-aligning, free-swinging shoe with slip-resistant tread and replaceable steel spur plate

Model D520-2

**SPECIFICATIONS** NOTE: Type IAA duty rating is for extension ladders up to 32 ft.

Model No.	Total Length of Sections	Max. Working Length	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
D520-2	20'	17'	8.8	42.0
D524-2	24'	21'	10.4	49.0
D528-2	28'	25'	12.1	65.5
D532-2	32'	29'	13.8	74.0

★★★★★ **300lbs.** LOAD CAPACITY **TYPE IA** DUTY RATING

D536-2	36'	32'	15.4	90.0
D540-2	40'	35'	17.0	99.5
D544-2	44'	39'	21.4	131.0
D548-2	48'	43'	23.3	142.5

**DIMENSIONS**

Rails:	3-1/4" wide	Rungs:	1-3/4"
Flange:	1-3/16" wide (20' & 24')	Base Section Width:	19-1/8" outside shoes 20-1/8" (44' & 48')
	1-1/4" wide (28' to 48')		






# D1500-2/D1500-1 SERIES

★★★★ **300lbs.** LOAD CAPACITY **TYPE IA** DUTY RATING

**STYLE: D-Rung Extension/Straight Ladder**



**Exclusive Alflo® rung joint means Twist-Proof® performance**



Model D1524-2

## SPECIFICATIONS

Model No.	Total Length of Sections	Max. Working Length	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.	Single Ladder Model No.	Total Length	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
D1516-2†	16'	13'	6.2	30.5	D1508-1	8'	3.6	14.5
D1520-2	20'	17'	7.7	37.0	D1510-1	10'	4.5	17.5
D1524-2	24'	21'	9.2	45.0	D1512-1	12'	5.4	21.5
D1528-2	28'	25'	10.7	56.0	D1514-1	14'	6.2	27.0
D1532-2	32'	29'	12.2	67.0	D1516-1	16'	7.1	32.5
D1536-2	36'	32'	13.7	80.0	D1518-1	18'	8.0	38.5
D1540-2	40'	35'	15.2	89.5	D1520-1	20'	8.9	43.5

† Note: D1516-2 is not equipped with rope and pulley

## DIMENSIONS

Rails:	3" wide	Rungs:	1-3/4"
Flange:	1-1/8" wide	Base Width:	18-1/8" outside rails


# 560-3 MODEL

★★★ **250lbs.** LOAD CAPACITY **TYPE I** DUTY RATING

**STYLE: Round Rung Extension Ladder**



**Exclusive Alflo® rung joint means Twist-Proof® performance**



## SPECIFICATIONS

Model No.	Total Length of Sections	Max. Working Length	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
560-3	60'	47'	26.8	179.0

## DIMENSIONS

Rails:	4" wide	Rungs:	1-1/4"
Flange:	2" wide (base & intermediate sections) 1-3/8" wide (top fly section)	Base Width:	23-1/2"

# D1800-2EQ/D1700-2EQ SERIES

\*\*\* 250lbs. LOAD CAPACITY TYPE I DUTY RATING

STYLE: Extension Ladder with Integrated Leveling



Exclusive Alflo® rung joint means Twist-Proof® performance

Lightweight aluminum

Slip-resistant Traction-Tred® D-rungs

Heavy duty spring-loaded locks operate smoothly


Model D1820-2EQ

THE Equalizer®  
ELIMINATES UNEVEN GROUND



Factory installed adjustable EverLevel® leveling system exceeds OSHA and ANSI requirements

Easily adjustable in 3/8" increments up to 8-1/4"



Convenient built-in bubble level



Dual action foot for use on hard or penetrable surfaces

## SPECIFICATIONS

Model No.	Total Length of Sections	Max. Working Length	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
D1816-2EQ‡	16'	13'	6.5	31.5
D1820-2EQ	20'	17'	8.1	37.5
D1824-2EQ	24'	21'	9.6	45.5
D1828-2EQ	28'	25'	11.2	56.0

\*\*\* 225lbs. LOAD CAPACITY TYPE II DUTY RATING

Model No.	Total Length of Sections	Max. Working Length	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
D1716-2EQ‡	16'	13'	6.5	27.5
D1720-2EQ	20'	17'	8.1	32.5
D1724-2EQ	24'	21'	9.6	39.0
D1728-2EQ	28'	25'	11.2	48.5

‡ Note: D1816-2EQ and D1716EQ are not equipped with rope and pulley

## DIMENSIONS

Rails:	3" wide	Fly Width:	14-1/4" outside rails
Flange:	1-1/16" wide	Base Width:	17-3/8" outside rails
Rungs:	1-3/4"		(20-3/4" to outside of feet)

# D1300-2SERIES

\*\*\* 250lbs. LOAD CAPACITY TYPE I DUTY RATING

STYLE: D-Rung Extension Ladder



Exclusive Alflo® rung joint means Twist-Proof® performance

Smooth operating pulley

Slip-resistant Traction-Tred® D-rungs

Durable shoe rests flat or is held in spur position with Shu-Lok® feature

Mar-resistant end caps

Interlocking side rails

Heavy duty modified I-beam side rails

Heavy duty spring loaded locks operate smoothly

Model D1320-2

## SPECIFICATIONS

Model No.	Total Length of Sections	Max. Working Length	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
D1316-2‡	16'	13'	5.8	26.0
D1320-2	20'	17'	7.2	32.5
D1324-2	24'	21'	8.6	40.0
D1328-2	28'	25'	10.0	50.5
D1332-2	32'	29'	11.5	63.5
D1336-2	36'	32'	13.0	77.5
D1340-2	40'	35'	14.4	85.5

‡ Note: D1316-2 is not equipped with rope and pulley

## DIMENSIONS

Rails:	3" wide	Rungs:	1-3/4"
Flange:	1-1/16" wide	Base Width:	17-3/8" outside rails



## D1200-2SERIES

★★ 225lbs. LOAD CAPACITY

TYPE II DUTY RATING

STYLE: D-Rung Extension Ladder



Exclusive Alflo® rung joint means Twist-Proof® performance



### SPECIFICATIONS

Model No.	Total Length of Sections	Max. Working Length	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
D1216-2†	16'	13'	5.8	22.0
D1220-2	20'	17'	7.2	27.0
D1224-2	24'	21'	8.6	33.5
D1228-2	28'	25'	10.0	43.0
D1232-2	32'	29'	11.5	54.0
D1236-2	36'	32'	13.0	62.5
D1240-2	40'	35'	14.4	73.5

† Note: D1216-2 is not equipped with rope and pulley

### DIMENSIONS

Rails:	3" wide	Rungs:	1-3/4"
Flange:	1" wide	Base Width:	17-3/8" outside rails

## D1200-3SERIES


★★ 225lbs. LOAD CAPACITY

TYPE II DUTY RATING

STYLE: D-Rung Compact Extension Ladder



Exclusive Alflo® rung joint means Twist-Proof® performance



### SPECIFICATIONS

Model No.	Total Length of Sections	Total Length in Storage Position 2 vs. 3 piece*	Max. Working Length	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
D1216-3	18'	8' / 6'	13'	5.9	26.5
D1224-3	27'	12' / 9'	21'	8.7	38.5

\* Total Length of ladder in storage position, comparison of Standard 2 - piece vs. New 3 - piece extension ladder.

### DIMENSIONS

Rails:	3" wide	Fly Width:	14-1/4" outside rails
Flange:	1-1/16" wide	Base Width:	17-3/8" outside rails
Rungs:	1-3/4"		(20-3/4" to outside of feet)


# D1100-2SERIES

★ **200lbs.** LOAD CAPACITY **TYPE III** DUTY RATING

**STYLE: D-Rung Extension Ladder**



**Exclusive Alflo® rung joint means Twist-Proof® performance**



## SPECIFICATIONS

Model No.	Total Length of Sections	Max. Working Length	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
D1116-2‡	16'	13'	4.9	18.5
D1120-2	20'	17'	6.2	23.0
D1124-2	24'	21'	7.4	30.0
D1128-2	28'	25'	9.0	38.5

‡ Note: D1116-2 is not equipped with rope and pulley

## DIMENSIONS

Rails:	2-3/4" wide (16' & 20') 3" wide (24' & 28')	Rungs:	1-1/2"
Flange:	15/16" wide	Base Width:	16" outside rails


# D716-2MODEL

★ **200lbs.** LOAD CAPACITY **TYPE III** DUTY RATING

**STYLE: D-Rung Extension Ladder**



**Exclusive Alflo® rung joint means Twist-Proof® performance**



## SPECIFICATIONS

Model No.	Total Length of Sections	Max. Working Length	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
D716-2	16'	13'	4.6	17.5














## DIMENSIONS

Rails:	2-1/2" wide	Rungs:	1-1/4"
Flange:	3/4" wide	Base Width:	15-3/4" outside rails





# ALUMINUM EXTENSION LADDER COMPARISON CHART

Features and Benefits	D500-2 SERIES	D1500 SERIES	D1800-2EQ SERIES	D1300-2 SERIES	D1700-2EQ SERIES	D1200-2 SERIES	D1100-2 SERIES	D716-2 MODEL
	TYPE IAA/IA	TYPE IA	TYPE I	TYPE I	TYPE II	TYPE II	TYPE III	TYPE III
 Rope clamp ties rope to rung	★	★	★	★	★	★	★	
 Heavy duty shoe with slip-resistant tread and spur plate	★							
Removable sections for use as a single ladder	★	★	★	★	★	★	★	
 External guide brackets		★						
 Pivoting shoe							★	★
 Slip-resistant shoe with Shu-lok® feature and spur plate		★	★	★	★	★		
 Interlocking side rails	★		★	★	★	★	★	
 Rope and pulley system	★	★	★	★	★	★	★	
 Spring loaded locks	★	★	★	★	★	★	★	
 Modified I-beam rails	★	★	★	★	★	★	★	★
 Alflo® rung joint for Twist-Proof® performance	★	★	★	★	★	★	★	★
 Mar-resistant end caps	★	★	★	★	★	★	★	★
 Slip-resistant Traction-Tred® D-rungs	★	★	★	★	★	★	★	★
 Integrated Leveling			★		★			

# MT SERIES

★★★★ **300lbs.** LOAD CAPACITY **TYPE IA**  
**PER SIDE** DUTY RATING

**STYLE: Telescoping MultiLadder<sup>††</sup>**



- Telescoping design for maximum versatility

## SPECIFICATIONS

Model No.	Stepladder Height	Extension Height	Stair Height	Scaffold Length	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
MT-13	3' to 5'	7' to 11'	3' to 5'	1' to 2'	5.9	31.5
MT-17	4' to 7'	9' to 15'	4' to 7'	1' to 3'	6.9	39.5
MT-22	5' to 9'	11' to 19'	5' to 9'	1' to 4'	10.8	47.0
MT-26	6' to 11'	13' to 23'	6' to 11'	1' to 5'	12.3	62.6

<sup>††</sup>Designed for one or two person jobs. Note: When used as a double stepladder, the maximum load per side, including person and materials, shall not exceed the duty rating of ladder.

## DIMENSIONS

Rails:	2-5/8" wide	Rungs:	1" wide
Flange:	1" wide	Ladder Width:	16" wide

# M1A SERIES

★★★★ **300lbs.** LOAD CAPACITY **TYPE IA**  
**PER SIDE** DUTY RATING

**STYLE: Folding MultiLadder<sup>††</sup>**



- Shippable by ground parcel services
- Set-up of some positions requires additional equipment, not included.

## SPECIFICATIONS

Model No.	Closed Height	Scaffold Height	Stepladder Height	Straight Ladder Length	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
M1A-6-12B	40-5/8"	3'	6'	12'	4.0	33.5
M1A-8-16B	52-5/8"	4'	8'	16'	5.2	39.5

<sup>††</sup>Designed for one or two person jobs. Note: When used as a double stepladder, the maximum load per side, including person and materials, shall not exceed the duty rating of ladder.

## DIMENSIONS

Rails:	2-1/2" wide	Rungs:	1-1/4" multi-directional round type
Flange:	1" wide	Ladder Width:	15" outside rails

# AH SERIES

★★★★★ **375lbs.** LOAD CAPACITY

**STYLE: Aluminum Folding Attic Ladder**  
**STANDARD / EXTRA WIDE OPENINGS**



Step-by-Step Installation Made Easy  
**Online Video**  
werneratticladders.com

- Lightweight – easy to open, close and install
- Attractive – will not splinter, decay or rust

### SPECIFICATIONS

Model No.	Rough Opening Width x Length	Floor to Ceiling Height Range	Approx. Ladder Width	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
AH2210	22-1/2" x 54"	7'8" to 10'3"	14-1/8"	6.8	48.5
AH2510	25" x 54"	7'8" to 10'3"	17-1/8"	7.6	52.0
AH2512	25" x 66"	10'5" to 12'	17-1/8"	9.2	58.5

### DIMENSIONS

Rails:	2-3/8" wide	Steps:	3" wide
Flange:	1-1/2" wide		


# AA MODEL

★★★ **250lbs.** LOAD CAPACITY

**STYLE: Compact Aluminum Attic Ladder**  
**BUILT FOR SMALL OPENINGS**



Step-by-Step Installation Made Easy  
**Online Video**  
werneratticladders.com



### SPECIFICATIONS

Model No.	Rough Opening Width x Length	Floor to Floor Height Range	Approx. Ladder Width	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
AA1510	18" x 24" Minimum	7" to 9'10"	12-1/8"	2.55	15.5

### DIMENSIONS


Rails:	5/8" x 2-1/8" wide	Steps:	1-3/16" wide
--------	--------------------	--------	--------------



# WH SERIES

**350 lbs.** LOAD CAPACITY

**STYLE: Wood Folding Heavy Duty Attic Ladder**  
**STANDARD / EXTRA WIDE OPENINGS**



- Easy to open and close
- Fully assembled and ready to install

### SPECIFICATIONS

Model No.	Rough Opening Width x Length	Floor to Ceiling Height Range	Approx. Ladder Width	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
WH2208	22-1/2" x 54"	7' to 8'9"	14-1/4"	10.55	59.5
WH2210	22-1/2" x 54"	8'9" to 10'3"	14-1/4"	10.55	64.5
WH2508	25" x 54"	7' to 8'9"	16-3/4"	11.96	62.5
WH2510	25" x 54"	8'9" to 10'3"	16-3/4"	11.96	67.5
WH3008	30-1/2" x 54"	7' to 8'9"	22 1/4"	14.30	73.5
WH3010	30-1/2" x 54"	8'9" to 10'3"	22 1/4"	14.30	76.5


### NOMINAL DIMENSIONS

	Actual Lumber Size	Rough Lumber Size
Rails:	3/4" x 4-1/2"	1" x 5"
Grooved Steps:	3/4" x 4-1/2"	1" x 5"

# WSERIES

★★★ **250 lbs.** LOAD CAPACITY

**STYLE: Wood Folding Attic Ladder**  
**STANDARD / EXTRA WIDE OPENINGS**



- Easy to open and close
- Fully assembled and ready to install

### SPECIFICATIONS

Model No.	Rough Opening Width x Length	Floor to Ceiling Height Range	Approx. Ladder Width	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
W2208	22 1/2" x 54"	7' to 8'9"	14-1/4"	8.61	48.6
W2210	22 1/2" x 54"	8'9" to 10'4"	14-1/4"	8.61	51.3
W2508	25" x 54"	7' to 8'9"	16-3/4"	9.76	51.2
W2510	25" x 54"	8'9" to 10'4"	16-3/4"	9.76	53.9

### NOMINAL DIMENSIONS

	Actual Lumber Size	Rough Lumber Size
Rails:	3/4" x 3-1/2"	1" x 4"
Grooved Steps:	3/4" x 3-1/2"	1" x 4"

# ATTIC LADDER COMPARISON CHART

<b>Product Advantages</b>	<b>AH SERIES</b>	<b>AA SERIES</b>	<b>WH SERIES</b>	<b>W SERIES</b>
Material	Aluminum	Aluminum	Wood	Wood
Style	Folding	Sliding	Folding	Folding
Size	8 ft. 10 ft. 12 ft.	7' - 9' 10"	8 ft. 10 ft.	8 ft. 10 ft.
Load Capacity	375 lbs.	250 lbs.	350 lbs.	250 lbs.
Ceiling Height Range	7' to 12'	7' to 9'10" (floor to floor)	7' to 10' 3"	7' to 10' 4"
Locking Device	Gas Strut	N/A	Spring	Spring
Opening Device	Rope	Push/Pull Rod	Rope	Rope
Door Material	Plywood	Not Included (Door hardware included)	Plywood	Plywood
Frame Material	Pine	N/A	Pine	Pine
Full Width Door Hinge	Yes	N/A	Yes	Yes
Metal-to-Metal Rail Hinge	Yes	N/A	Yes	Yes
Requires Cutting Rail	Yes	No	Yes	Yes
Separate Foot Attachment	Yes	No	No	No
Number of People for Installation	Two	One	Two	Two
Step Depth	3"	1-3/16"	4-1/2"	3-1/2"
Finished Rails with Eased Edges	2-3/8" wide	2-1/8" wide	4-1/2" wide	3-1/2" wide
Approximate Shipping Weight	48-58 lbs.	15.5 lbs.	59-76 lbs.	48-54 lbs.

**STYLE: Work Platform**



Extra-large platform with increased tread for extra stability

Model AP-30



Large platform provides a non-skid area for standing

Platform legs lock securely in place when in use and fold underneath platform for compact storage

Model AP-20

Non-marring feet provide slip-resistance and protect floor from damage



Model AP-30



Model AP-20

- Merchandised in closed, upright position
- AP-20 packaged in quantities of 6

**AP-20-MP6 MODEL**

★★ **225lbs.** LOAD CAPACITY **TYPE II** DUTY RATING

**SPECIFICATIONS**

Model No.	Height	Width	Depth	Approx. Cu. Ft.	Approx. Shipping Wt. Lbs.
AP-20*	20-9/16"	50-1/4"	15-5/8"	2.1	12.8
AP-20-MP6 ‡	41"	16-5/8"	35-3/4"	14.1	75.0

\* Note: Dimensions of individual unit ‡ Note: Dimensions for packaged unit of 6

**DIMENSIONS**

Top: 39-1/2" x 12"	Highest Standing Level: 20-9/16"
--------------------	----------------------------------

**AP-30 MODEL**

★★★★ **300lbs.** LOAD CAPACITY **TYPE IA** DUTY RATING

**SPECIFICATIONS**

Model No.	Height	Width	Depth	Approx. Cu. Ft.	Approx. Shipping Wt. Lbs.
AP-30	20-9/16"	50-1/4"	15-5/8"	2.1	12.8

**DIMENSIONS**

Top: 48" x 16"	Highest Standing Level: 20-9/16"
----------------	----------------------------------



Multi-use platform




Work comfortably along walls and windows. Ideal for painting.

## PS-48 MODEL

**500 lbs.** LOAD CAPACITY\*

**STYLE: Portable Scaffold**

**Multiple Working Heights**



Mar-resistant wheels  
High grade wheels prevent marring by locking securely into place



Multi-use S-Hooks make transportation easy and are ToolLasso® ready



Extra wide 10" plank for secure standing and comfort

- Versatile; can be used as push cart, storage shelf or work bench

\*250 lbs. per plank (500 lbs. combined)

### SPECIFICATIONS

Model No.	Height	Width	Depth	Approx. Cu. Ft Per Packaged Unit	Approx. Shipping Wt. Lbs.
PS-48	50-1/8"	46-1/8"	25-1/2"	3.4	60.0

### PLANK DIMENSIONS

	Length	Width
Narrow Plank	46"	6"
Wide Plank	46"	10"

## SRS-72 MODEL

**1000 lbs.** LOAD CAPACITY\*

**STYLE: 6' Steel Rolling Scaffold**

Sections stack easily when casters are removed (2 high maximum)

Platform height adjustable in 2" increments for unique working heights and uneven surfaces



Deck pins secure plywood to scaffold frame

Protected locking pins prevent accidental release

Locking casters swivel for convenient 360° mobility

- Easy one-person assembly- No tools required for quick setup and tear down.

\*1000 lbs. load capacity distributed evenly

### DIMENSIONS

Model No.	Approx. Width	Approx. Length	Approx. Height	Approx. Shipping Wt. Lbs.
SRS-72	29-1/2"	73-3/4"	74-7/8"	143.5

### COMPONENT DIMENSIONS

Component	Quantity Included	Approx. Width	Approx. Length	Approx. Height
Frames	2	29"	68-3/4"	1-1/2"
Arm Braces	2	1-1/2"	73-7/8"	17-7/8"
Plywood Deck	1	28-1/2"	66-3/4"	1-1/2"
Locking Casters	4	5-1/8"	9-7/8"	--


### ACCESSORIES (AVAILABLE SEPARATELY)

Model No.	Description	Approx. Width	Approx. Length	Approx. Height	Approx. Shipping Wt. Lbs.
SRO-72-4	Outriggers (4-pc master carton)	18"	20-3/4"	--	37.5
SRG-72	Guard Rail and Toeboard Kit	28-7/8"	69-5/8"	42"	70.5
SRC-72-4	Castors (4-pc master carton)	5-1/8"	1-1/8"	9-7/8"	20.0
SRD-72	Plywood Deck	28-1/2"	66-3/4"	2"	32.5

Note: Outriggers and Guard Rails are required when working height reaches 10'

## PA200 SERIES – ALUMINUM EXTENSION PLANK

- 1 person, 250 lb. Load Capacity.
- For use on stepladders, telescoping multiladders, extension trestle ladders and extension and single ladders equipped with ladder jacks.



### SPECIFICATIONS

Model No.	Closed Position	Open Position	Approx. Width	Inner Rails	Outer Flanged Rails	Approx. Cu. Ft. Per Unit	Approx. Shipping Wt. Lbs.
PA206	6'	9'	14"	1-1/8" x 2"	1-7/8" x 2"	1.5	31.0
PA208	8'	13'	14"	1-1/8" x 2"	1-7/8" x 2"	2.0	40.5
PA210	10'	17'	14"	1-1/8" x 2"	1-7/8" x 2"	2.5	56.5

Note: When assembled as scaffold or staging, these planks must be used in conjunction with suitable guard rail protection in compliance with applicable governmental codes, ordinances, regulations and safe practice.

## 5600 SERIES- 2-PIECE EXTRUDED ALUMA-BOARD™

### SPECIFICATIONS

Model No.	Duty Rating/Sq. Ft.	Width	Side Rail Length	Side Rail Depth	Approx. Shipping Wt. Lbs.
5607-19	75 lbs.	19-1/16"	7'	2"	30.0



Model 5607-19

FOR USE WITH STEEL SCAFFOLDS

## 5500 SERIES - ALUMINUM DECKED ALUMA-PLANK®

### SPECIFICATIONS

Model No.	Duty Rating/Sq. Ft.	Width	Side Rail Length	Side Rail Depth	Approx. Shipping Wt. Lbs.
5507-19	75 lbs.	19-1/16"	7'	3"	25.0
5508-19	75 lbs.	19-1/16"	8'	4"	34.0
5510-19	75 lbs.	19-1/16"	10'	4"	43.0



Model 5507-19

FOR USE WITH STEEL SCAFFOLDS

## 5300 SERIES - PLYWOOD DECKED ALUMA-PLANK®

### SPECIFICATIONS

Model No.	Duty Rating/Sq. Ft.	Width	Side Rail Length	Side Rail Depth	Approx. Shipping Wt. Lbs.
5307-19	75 lbs.	19-1/16"	7'	3-1/2"	27.0
5308-19	75 lbs.	19-1/16"	8'	4-1/2"	38.0
5310-19	75 lbs.	19-1/16"	10'	4-1/2"	47.0
5307-24	75 lbs.	24"	7'	4"	32.0
5310-24	75 lbs.	24"	10'	4-1/2"	53.0




Model 5310-19

FOR USE WITH STEEL SCAFFOLDS

# ALUMINUM PUMP JACK SYSTEM

- Versatile, dependable and easy to operate
- Field replaceable components
- Compatible and interchangeable with the leading competitor



Note: When working 10 ft. and above, OSHA requires fall protection. Refer to product labels.

<p>① Foldable Support Brace (PJ-SBF)</p> <p>(Rigid Support Brace available)</p>	<p>② Nestable Stage (WNS 2512)</p> <p>(other sizes available)</p>	<p>③ Safety Net (PJ-SN)</p>	<p>④ Work Bench (PJ-WB)</p>	<p>⑤ Pump Jack (PJ-100)</p>	<p>⑥ End Rail Kit (narrow) (PJ-ERN)</p> <p>PJ-ERW kit for wide span available</p>	<p>⑦ 24' Aluminum Pole (PJ-24P)</p> <p>Also available: 6' (PJ-6P) 12' (PJ-12P) 18' (PJ-18P)</p>
---	---	-----------------------------	-----------------------------	-----------------------------	---	---

- **Pump Jack**
- **Work Bench**
- **Poles and Braces**
- **End Rail Kits**
- **Safety Net**



## Nestable Stages



- Continuous work platform reduces trip hazard
- 2 Person – 500 lbs. Rated


### PUMP JACK COMPONENTS

Model No.	Description	Approx. Shipping Wt. Lbs.
PJ-100	Pump jack	30.0
PJ-PF-4	Pole foot	3.0
PJ-6P	6' aluminum pole	14.0
PJ-12P	12' aluminum pole	28.0
PJ-18P	18' aluminum pole	42.0
PJ-24P	24' aluminum pole	56.0
PJ-PC	Pole connector	12.0
PJ-SBF	Foldable support brace	9.0
PJ-SBR	Rigid support brace	14.0
PJ-WB	Work bench	15.0
PJ-ERN	End rail kit (narrow)	15.0
PJ-ERW	End rail kit (wide)	17.0
PJ-SN	Safety net	14.0

### NESTABLE STAGES

2-person - 500 lbs. rated

Model No.	Nestable Stage Description	Approx. Shipping Wt. Lbs.
WNS-2412	14" x 12'	46.0
WNS-2416	14" x 16'	63.0
WNS-2420	14" x 20'	86.0
WNS-2424	14" x 24'	115.0
WNS-2512	20" x 12'	54.0
WNS-2516	20" x 16'	75.0
WNS-2520	20" x 20'	103.0
WNS-2524	20" x 24'	122.0
WNS-2612	24" x 12'	62.0
WNS-2616	24" x 16'	81.0
WNS-2620	24" x 20'	116.0
WNS-2624	24" x 24'	139.0



- Exclusive Pole-Trak™ system with rugged hand crank and safety brake
- Slip-resistant foot lever with oversized boot strap
- Accommodates up to a 24" wide plank
- Economical and easy to operate
- Meets ANSI and OSHA standards

- **Pump Jack**
- **Work Bench with Guard Rail Holder**
- **Pole Anchor**
- **Foldable Brace**


① Foldable Support Brace (SPJ-SBF) 	② Steel Work Bench/ Guard Rail Holder (SPJ-WB) 	③ Steel Pump Jack (SPJ-100) 
④ Steel Guard Rail Holder (SPJ-GRH) 	⑤ Pole Anchor for Steel Pump Jack (SPJ-PA-4) 	

### COMPONENTS SHOWN

Description	Model Number	Product Weight (lbs)
① Foldable Support Brace	SPJ-SBF	7.0
② Steel Work Bench/ Guard Rail Holder	SPJ-WB	11.0
③ Steel Pump Jack	SPJ-100	23.0
④ Steel Guard Rail Holder	SPJ-GRH	5.5
⑤ Pole Anchor for Steel Pump Jack (Shipped in 4-packs)	SPJ-PA-4	5.5 (4-pk weight: 23.0)

# ALUMINUM TASK-MASTER® STAGES

- Twist-Proof® Stage Design
- Ideal for ladder jack applications, swing stages or catwalks



## STAGE PLATFORMS 2-person - 500 lbs. rated

Model No.	Width	Side Rail Length	Side Rail Depth	Side Rail Flange	Approx. Shipping Wt. Lbs.
2508	20"	8'	4"	1-3/8"	33.0
2512	20"	12'	4"	1-3/8"	48.0
2516	20"	16'	5"	1-3/8"	70.0
*2520	20"	20'	6"	1-3/8"	102.0
*2524	20"	24'	6"	1-3/8"	121.0
*2528	20"	28'	6"	2"	157.0
*2532	20"	32'	6"	2"	179.0
2608	24"	8'	4"	1-3/8"	38.0
2612	24"	12'	4"	1-3/8"	56.0
2616	24"	16'	5"	1-3/8"	81.0
*2620	24"	20'	6"	1-3/8"	115.0
*2624	24"	24'	6"	1-3/8"	138.0
*2628	24"	28'	6"	2"	168.0
*2632	24"	32'	6"	2"	191.0
2708	28"	8'	4"	1-3/8"	41.0
2712	28"	12'	4"	1-3/8"	60.0
2716	28"	16'	5"	1-3/8"	87.0
*2720	28"	20'	6"	1-3/8"	124.0
*2724	28"	24'	6"	1-3/8"	147.0
*2728	28"	28'	6"	2"	187.0
*2732	28"	32'	6"	2"	213.0

## DECORATOR PLANKS 1-person - 250 lbs. rated

Model No.	Width	Side Rail Length	Side Rail Depth	Side Rail Flange	Approx. Shipping Wt. Lbs.
2008	12"	8'	4"	1-3/8"	25.0
2012	12"	12'	4"	1-3/8"	36.0
2016	12"	16'	4"	1-3/8"	48.0
2020	12"	20'	5"	1-3/8"	65.0
2024	12"	24'	5"	1-3/8"	78.0

## SCAFFOLD PLANKS 2-person - 500 lbs. rated

Model No.	Width	Side Rail Length	Side Rail Depth	Side Rail Flange	Approx. Shipping Wt. Lbs.
2316	12"	16'	4"	1-3/8"	48.0
2320	12"	20'	6"	1-3/8"	79.0
2324	12"	24'	6" Heavy Duty	1-3/8"	112.0
2328	12"	28'	6" Heavy Duty	1-3/8"	131.0
2330	12"	30'	6" Heavy Duty	1-3/8"	140.0
2332	12"	32'	6" Heavy Duty	1-3/8"	149.0
2408	14"	8'	4"	1-3/8"	27.0
2412	14"	12'	4"	1-3/8"	40.0
2416	14"	16'	5"	1-3/8"	58.0
2420	14"	20'	6"	1-3/8"	85.0
2424	14"	24'	6"	2"	109.0
2428	14"	28'	6"	2"	127.0
2432	14"	32'	6" Heavy Duty	2"	182.0


## 3-person - 750 lbs. rated

3112	24"	12'	4"	2"	64.0
3116	24"	16'	5"	2"	92.0
*3120	24"	20'	5"	2"	115.0
*3124	24"	24'	6"	2"	145.0
*3128	24"	28'	6" Heavy Duty	2"	204.0
*3132	24"	32'	6" Heavy Duty	2"	236.0
*3136	24"	36'	6" Heavy Duty	2"	323.0
*3139	24"	39'	6" Heavy Duty	2"	365.0
3208	28"	8'	4"	2"	48.0
3212	28"	12'	4"	2"	71.0
3216	28"	16'	5"	2"	103.0
*3220	28"	20'	5"	2"	128.0
*3224	28"	24'	6"	2"	161.0
*3228	28"	28'	6" Heavy Duty	2"	220.0
*3232	28"	32'	6" Heavy Duty	2"	251.0
*3236†	28"	36'	6" Heavy Duty	2"	344.0
*3239†	28"	39'	6" Heavy Duty	2"	388.0

\*Includes set of double rungs at the end of stage.

†Includes reinforcing channel





## SQUARE MODULAR GUARD RAIL SYSTEM

### System Sizing: How do I size a guard rail system?

The following steps show how to size a single-sided, three-sided, and four-sided guard rail system:

- Step 1: Determine the stage length and width.
- Step 2: Determine whether guardrail system is one-, two-, three-, or four -sided.
- Step 3: Read across the row to determine component requirements.
- Step 4: If ordering a three- or four-sided system, order two ERT-N for 12" and 14" wide stages, and two ERT-W for all stages 20" wide or greater.

*Note: If ordering a two sided system, double the single sided component requirement.*

Model No.	Description	Approx. Shipping Wt. Lbs.
ERT-N	End rail and end toe board assembly - narrow	4.5
ERT-W	End rail and end toe board assembly - wide	7.0
SSP-47	Stanchion post assembly	5.0
SGR-09	1-1/2" square guard rail cut length - 108"	6.0
SGR-13	1-1/2" square guard rail cut length - 156"	8.5
STB-09	3-1/2" toe board cut length - 108"	4.5
STB-13	3-1/2" toe board cut length - 156"	6.5

Stage Length	Single-sided					Three-sided					Four-sided						
	SSP-47	SGR-09	SGR-13	STB-09	STB-13	SSP-47	SGR-09	SGR-13	STB-09	STB-13	ERT-N/ ERT-W*	SSP-47	SGR-09	SGR-13	STB-09	STB-13	ERT-N/ ERT-W*
8'	2	2	0	1	0	4	2	0	1	0	2	4	4	0	2	0	2
12'	3	0	2	0	1	5	0	2	0	1	2	6	0	4	0	2	2
16'	3	4	0	2	0	5	4	0	2	0	2	6	8	0	4	0	2
20'	4	2	2	1	1	6	2	2	1	1	2	8	4	4	2	2	2
24'	5	4	2	2	1	7	4	2	2	1	2	10	8	4	4	2	2
28'	6	2	4	1	2	8	2	4	1	2	2	12	4	8	2	4	2
32'	6	2	4	1	2	8	2	4	1	2	2	12	4	8	2	4	2
36'	6	10	0	5	0	8	10	0	5	0	2	12	20	0	10	0	2
39'	7	4	4	2	2	9	4	4	2	2	2	14	8	8	4	4	2

\*ERT-N is for 12" and 14" wide stages; ERT-W is for 20" wide and greater stages



# ALUMINUM SCAFFOLDING

**Werner aluminum scaffolding is best suited for construction and building maintenance applications, especially in high-traffic areas where mobility and appearance are important.**

#### **CONSTRUCTION:**

- Drywall
- Insulation
- Drop ceilings
- Ductwork

#### **BUILDING MAINTENANCE:**

- Window and façade cleaning
- Changing light bulbs
- Painting
- Wallpapering

**Aluminum scaffolding has benefits that steel scaffolding does not.**

- More corrosion resistant
- Convenient - 30-50% lighter
- Easier and quicker to install
- Better on-site appearance

**Werner offers scaffolding as towers, sections and individual components.**

- Towers and sections for the one-time purchaser with limited scaffold knowledge
- Components for the regular purchaser with extensive knowledge on configuring a scaffold tower

**Scaffolding can be used on inclines and stairs.**

- For use on an incline, a scaffold tower must be secured to prevent movement.
- Scaffolding can be used on a stairway provided the horizontal braces from one end frame to the other are at the same level and adequate braces are used.

- Easy and convenient to order.
- Takes the guesswork out of what is required to meet Code.
- Ideal for schools, hospitals and building maintenance.

Includes guard rails, toeboards and planks with access door that allows end users to climb from inside. 23' towers include additional fixed board (no access door). Outriggers included on all models except 4201-12, 4202-12 and 4203-12. These models meet the ANSI code as noted on Page 50 - "Notice".

## Narrow Span Towers

Platform Length	Total Width (W)	Total Length (L)
6'	9' 6"	9' 6"
8'	9' 6"	11' 6"
10'	9' 6"	13' 6"




**12' Platform Height**

Model No.	Platform Length	Platform Width	Platform Height	Total Tower Height	Approx. Shipping Wt. Lbs.
4101-12	6'	29"	12'	15' 5"	359.0
4102-12	8'	29"	12'	15' 5"	389.0
4103-12	10'	29"	12'	15' 5"	410.5



**18' Platform Height**

Model No.	Platform Length	Platform Width	Platform Height	Total Tower Height	Approx. Shipping Wt. Lbs.
4101-18	6'	29"	17' 6"	20' 11"	405.0
4102-18	8'	29"	17' 6"	20' 11"	439.0
4103-18	10'	29"	17' 6"	20' 11"	462.5



**23' Platform Height**

Model No.	Platform Length	Platform Width	Platform Height	Total Tower Height	Approx. Shipping Wt. Lbs.
4101-23	6'	29"	23'	26' 4"	451.0
4102-23	8'	29"	23'	26' 4"	489.0
4103-23	10'	29"	23'	26' 4"	514.5

**Load Capacity: 25 lbs. per sq. ft. or 500 lbs. maximum per deck & scaffold.**


## Wide Span Towers



**12' Platform Height\***

Model No.	Platform Length	Platform Width	Platform Height	Total Tower Height	Approx. Shipping Wt. Lbs.
4201-12	6'	4-1/2'	12'	15' 5"	299.5
4202-12	8'	4-1/2'	12'	15' 5"	338.0
4203-12	10'	4-1/2'	12'	15' 5"	366.0


\*Outriggers not included with 12' high platform wide span towers (Per ANSI code, does not require outriggers).



**18' Platform Height**

Model No.	Platform Length	Platform Width	Platform Height	Total Tower Height	Approx. Shipping Wt. Lbs.
4201-18	6'	4-1/2'	17' 6"	20' 11"	561.5
4202-18	8'	4-1/2'	17' 6"	20' 11"	610.0
4203-18	10'	4-1/2'	17' 6"	20' 11"	643.0

Platform Length	Total Width (W)	Total Length (L)
6'	10' 10"	10' 10"
8'	10' 10"	12' 10"
10'	10' 10"	14' 7"



**23' Platform Height**

Model No.	Platform Length	Platform Width	Platform Height	Total Tower Height	Approx. Shipping Wt. Lbs.
4201-23	6'	4-1/2'	23'	26' 4"	695.0
4202-23	8'	4-1/2'	23'	26' 4"	778.0
4203-23	10'	4-1/2'	23'	26' 4"	862.0

Platform Length	Total Width (W)	Total Length (L)
6'	10' 10"	10' 10"
8'	10' 10"	12' 10"
10'	10' 10"	14' 7"


**Load Capacity: 25 lbs. per sq. ft. or 500 lbs. per deck and 1,000 lbs. maximum per scaffold.**

# SCAFFOLD SECTIONS

- Easy and convenient to order.
- Enables user to easily add to an existing scaffold tower.
- Ideal for painting and remodeling contractors.

## NARROW SPAN SCAFFOLD SECTIONS


Load Capacity: 25 lbs. per sq. ft. or 500 lbs. maximum per deck and scaffold



Model No.	Width	Length	Approx. Shipping Wt. Lbs.
<b>6' 6" to 7' 6" High Adjustable Base Sections</b>			
4101	29"	6'	121.0
4102	29"	8'	133.0
4103	29"	10'	145.0
<b>6-3/4' High Upper Sections</b>			
4127	29"	6'	60.0
4128	29"	8'	65.0
4129	29"	10'	68.0
<b>5-1/2' High Upper Sections</b>			
4104	29"	6'	53.0
4105	29"	8'	58.0
4106	29"	10'	62.0
<b>4' High Upper Sections</b>			
4107	29"	6'	47.0
4108	29"	8'	51.0
4109	29"	10'	55.0
<b>3-1/2' High Guard Rails</b>			
4110	29"	6'	44.0
4111	29"	8'	48.0
4112	29"	10'	52.0

## SNAP-UP® NARROW SPAN FOLDING SCAFFOLDS

Load Capacity: 25 lbs. per sq. ft. or 500 lbs. maximum per deck and scaffold




- Adjustable 6' 6" to 7' 6" high clearance

Model No.	Width	Length	Approx. Shipping Wt. Lbs.
SNB-6U	29"	6'	127.0
SNB-8U	29"	8'	139.0

## WIDE SPAN SCAFFOLD SECTIONS


Load Capacity: 25 lbs. per sq. ft. or 500 lbs. maximum per deck and 1000 lbs. maximum per scaffold



Model No.	Width	Length	Approx. Shipping Wt. Lbs.
<b>6' 6" to 7' 6" High Base Sections</b>			
4201	4-1/2'	6'	167.0
4202	4-1/2'	8'	188.0
4203	4-1/2'	10'	208.0
<b>5-1/2' High Upper Sections</b>			
4204	4-1/2'	6'	71.0
4205	4-1/2'	8'	76.0
4206	4-1/2'	10'	81.0
<b>4' High Upper Sections</b>			
4207	4-1/2'	6'	62.0
4208	4-1/2'	8'	68.0
4209	4-1/2'	10'	73.0
<b>3-1/2' High Guard Rails</b>			
4210	4-1/2'	6'	55.0
4211	4-1/2'	8'	60.0
4212	4-1/2'	10'	65.0

## SNAP-UP® WIDE SPAN FOLDING SCAFFOLDS

Load Capacity: 25 lbs. per sq. ft. or 500 lbs. maximum per deck and 1000 lbs. maximum per scaffold



- Adjustable 6' 6" to 7' 6" high clearance

Model No.	Width	Length	Approx. Shipping Wt. Lbs.
SWB-6U	4-1/2'	6'	163.0
SWB-8U	4-1/2'	8'	181.0

- Provides most flexibility during installation.
- Enables end user to easily convert to different length or height scaffold towers.
- All components available separately.
- Ideal for rental yards and theatrical and entertainment applications.

## FRAMES

Model No.	Description	Approx. Shipping Wt. Lbs.
<b>For Narrow Span, 29" Wide</b>		
FNB-80	Base end frame	35.0
FNU-81	6-3/4' H upper end frame	19.0
FNU-65	5-1/2' H upper end frame	15.0
FNU-49	4' H upper end frame	12.0
FNG-42	Guard rail end frame	11.5
<b>For Wide Span, 4-1/2' Wide</b>		
FWB-80	Base end frame	39.5
FWU-81	6-3/4' H wide span upper end frame	22.0
FWU-65	5-1/2' H upper end frame	19.0
FWU-49	4' H upper end frame	14.5
FWG-42	Guard rail end frame	14.5


## SCAFFOLD BOARDS

Model No.	Description	Approx. Shipping Wt. Lbs.
P22W-6	6' scaffold board	28.5
P22W-8	8' scaffold board	36.0
P22W-10	10' scaffold board	42.5
PD22W-6	22" wood deck with access door - 6' board	33.0
PD22W-8	22" wood deck with access door - 8' board	41.0
PD22W-10	22" wood deck with access door - 10' board	49.0

## BRACES

Model No.	Description	Approx. Shipping Wt. Lbs.
BD-6	6' diagonal brace	4.0
BD-8	8' diagonal brace	5.0
BD-10	10' diagonal brace	5.5
BH-6	6' horizontal brace	4.0
BH-8	8' horizontal brace	5.0
BH-10	10' horizontal brace	5.5
BN-6	6' narrow span horizontal-diagonal brace	4.0
BN-8	8' narrow span horizontal-diagonal brace	5.0
BN-10	10' narrow span horizontal-diagonal brace	6.0
BW-6	6' wide span horizontal-diagonal brace	5.0
BW-8	8' wide span horizontal-diagonal brace	5.5
BW-10	10' wide span horizontal-diagonal brace	6.0

## OUTRIGGERS for Wide and Narrow Span Scaffolds




**Note:** Braces and Frames are ordered separately

Model No.	Description	Approx. Shipping Wt. Lbs.
BOR-N	Narrow span outrigger brace	4.0
BOR-W	Wide span outrigger brace	5.0
FRO	Rolling outrigger frame (with every frame, a brace is needed)	18.0
<b>Knee-Type Outriggers</b>		
OR-ADU	Adjustable 1' to 5' 6" wide for narrow or wide span scaffolds	11.0


## TOE BOARD SYSTEMS

OSHA requires toe boards on scaffolds over 10' high




Model No.	Size	Approx. Shipping Wt. Lbs.
<b>Aluminum Toe Board Assemblies for 4100 Series</b>		
TN4A-6U	4" x 6'	18.0
TN4A-8U	4" x 8'	21.0
TN4A-10U	4" x 10'	25.0
<b>Aluminum Toe Board Assemblies for 4200 Series</b>		
TW4A-6U	4" x 6'	21.0
TW4A-8U	4" x 8'	25.0
TW4A-10U	4" x 10'	28.0

## ACCESSORY KITS



**Kit No. 41-1  
ONE SWIVEL  
BASE  
PLATE**



**Kit No. 43-1  
GUARD RAIL HOLDER  
A Werner Exclusive**

Includes four steel guard rail holders. With a set of guard rail holders, you can easily turn a horizontal brace into a guard rail.

**NOTE:** Guard Rail Holder fits Intermediate Scaffold Section Models: 4104-4109, 4127-4129, 4204-4209. They are not designed for Werner Co. Guard Rail Upper Section Models: 4110, 4111, 4112, 4210, 4211, 4212.

Kit No.	Description	Approx. Shipping Wt. Lbs.
41-1	One swivel base plate for stairway and span type scaffolds	8.0
43-1	Guard Rail Holder fits intermediate scaffold section models: 4104-4109, 4127-4129, 4204-4209.	1.2

**NOTICE – ALL SCAFFOLDS:** Maximum scaffold platform height is equal to 4x the smaller base section dimension of the scaffold or installed outrigger in most states except California which requires 3x. Check state and local codes.

## SCAFFOLD/OUTRIGGER COMPONENT COMPARISON CHART

Scaffold Towers		Narrow Span (29" wide) Towers									Wide Span (4-1/2" wide) Towers									
Platform Length		6' Long			8' Long			10' Long			6' Long			8' Long			10' Long			
Component Model No.	Description	4101-12	4101-18	4101-23	4102-12	4102-18	4102-23	4103-12	4103-18	4103-23	4201-12	4201-18	4201-23	4202-12	4202-18	4202-23	4203-12	4203-18	4203-23	
<b>FNB-80</b>	Adjustable Base Section	2	2	2	2	2	2	2	2	2										
<b>FNU-65</b>	5-1/2' Upper Section	2	4	6	2	4	6	2	4	6										
<b>FNG-42</b>	Guard Rail	2	2	2	2	2	2	2	2	2										
<b>FWB-80</b>	Adjustable Base Section										2	2	2	2	2	2	2	2	2	2
<b>FWU-65</b>	5-1/2' Upper Section										2	4	6	2	4	6	2	4	6	6
<b>FWG-42</b>	Guard Rail										2	2	2	2	2	2	2	2	2	2
<b>PD22W-6, -8, -10*</b>	Access Door Plank	1	1	2	1	1	2	1	1	2	1	1	2	1	1	2	1	1	2	2
<b>P22W-6, -8, -10*</b>	Wood Deck										1	1	2	1	1	2	1	1	2	2
<b>BH-6, -8, -10*</b>	Horizontal Brace	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12	8	10	12	12
<b>BD-6, -8, -10*</b>	Diagonal Brace	5	7	9	5	7	9	5	7	9	9	13	17	9	13	17	9	13	17	17
<b>BN-6, -8, -10*</b>	Horizontal-Diagonal	2	2	4	2	2	4	2	2	4										
<b>BW-6, -8, -10*</b>	Horizontal-Diagonal										2	2	4	2	2	4	2	2	4	4
<b>FRO</b>	Outrigger	4	4	4	4	4	4	4	4	4		4	4		4	4		4	4	4
<b>BOR-N, -W</b>	Outrigger Brace	4	4	4	4	4	4	4	4	4		4	4		4	4		4	4	4
<b>TN4A-6U, -8U, -10U</b>	Toe Board	1	1	2	1	1	2	1	1	2										
<b>TW4A-6U, -8U, -10U</b>	Toe Board										1	1	2	1	1	2	1	1	2	2


\*-6, -8, -10 refers to platform length. Add suffix to model number for corresponding platform length.

## ALUMINUM FOLDING ARCHED RAMPS MODEL R522

**1500 lbs. Load Capacity Per Pair**  
(750 lbs. evenly distributed load capacity per ramp)  
Shipping Weight: 35.0 lbs.

### ARCHED FOR BOTH HIGH AND LOW CLEARANCE VEHICLES

- Folds and locks for easy transporting
- Center rail and transition plate for smooth loading
- Multi-purpose - Ideal for all wheel sizes
- Easily hook together for small wheelbases
- Includes 2 ramps - No assembly required




## ALUMINUM ARCHED RAMPS MODEL R402

**1400 lbs. Load Capacity Per Pair**  
(700 lbs. evenly distributed load capacity per ramp)  
Shipping Weight: 22.0 lbs.

### ARCHED FOR BOTH HIGH AND LOW CLEARANCE VEHICLES

- Multi-purpose
- Easily hook together for small wheelbases
- Includes 2 ramps - No assembly required



# RAMPS

## ALUMINUM STRAIGHT RAMPS MODEL R301

**1300 lbs. Load Capacity Per Pair**  
(650 lbs. evenly distributed load capacity per ramp)  
Shipping Weight: 20.0 lbs.

### STRAIGHT FOR HIGH CLEARANCE VEHICLES

- Great for off-road vehicles
- Easily hook together for small wheelbases
- Includes 2 ramps - No assembly required



## STEEL STRAIGHT RAMP KIT MODEL R102

**Up to 1400 lbs. Load Capacity Per Pair\***  
(700 lbs. evenly distributed load capacity per ramp)  
Shipping Weight: 6.0 lbs.

\*depending on material, grade and length of board

### STRAIGHT FOR HIGH CLEARANCE VEHICLES

- Works with two 2x8, 2x10 or 2x12 planks (not included).
- Ideal for many uses. Use as a single ramp or a pair.
- Great for off-road vehicles.
- Safety straps secure ramps to vehicle.
- Includes hardware for 2 ramps.





## STEEL REMOVABLE PICKUP TRUCK RACK


250 lbs. Load Capacity

MODEL TR401-S (black)

Shipping Weight: 50.0 lbs.



Cargo positioners & vinyl strips help protect cargo in transit



Expands from 24" to 36"

Black powder coated steel

Corrosion resistant hardware includes silicone sealant for added protection against rust



Designed for work or play.



Cargo positioners & vinyl strips help protect cargo in transit.



Easily removes when not in use.

Some assembly required

### KEY FEATURES (all racks)

- **Exclusive Vinyl Protector Strips:** Werner is the first in the industry to offer these as a standard feature to help protect your equipment against transit damage.
- **Universal Design:** Werner Van & Truck Racks fit all vans with rain gutters and most pickup trucks with 6-1/2' to 8' long beds.

### STANDARD FEATURES

- All Werner Van & Truck Racks are made of welded 14 gauge square tubular steel for added strength.
- Double layer of glossy powder coated finish and corrosion resistant hardware are standard for added durability.

## STEEL VAN RACK 600 lbs. Load Capacity MODEL VR401-W (white)


Shipping Weight: 40.0 lbs.



Includes predrilled uprights.



Cargo positioners & vinyl strips help protect cargo in transit.



White powder coated steel

Cargo positioners & vinyl strips help protect cargo in transit



3rd Bar Option Available

Standard - Model No. VR403-W (white)

Model No. VR404-W (white)

Shipping Weight: 21.0 lbs.

Some assembly required

### Van Rack Compatibility Chart

Van Year	Make	Model	Type	VR401-W	VR403-W	VR404-W
Up to 1997	Chevy	1500-3500	All	✓	✓	
1998 & Up	Chevy/GMC	Express/Savanna	All	✓		✓
1998 & Up	Chevy/GMC	Express/Savanna	Standard	✓		✓
1982 & Up	Ford	E-150, 250, 350	Standard	✓		✓
1982 & Up	Ford	Super	Long	✓		✓
Up to 1999	Dodge	B-150, 250, 350	Standard	✓	✓	
2000 to 2003	Dodge	B-150, 250, 350	Standard			
Up to 1999	Dodge	Maxie Van	Long	✓	✓	
2000 to 2003	Dodge	Maxie Van	Long			
2004 & Up	Dodge	Sprinter (Passenger & Cargo Models)	Standard Roof	✓	✓	
2004 & Up	Dodge	Sprinter (Passenger & Cargo Models)	High Roof & Mega Roof			
All	All	Gutterless/Mini	All			

## MERCHANDISING MODULAR LADDER DISPLAYS & FIXTURES

### 55 END CAP DISPLAY

### 37 DISPLAY RACK



- Modular design for flexible retail footprint
- Easier access and organized ladder display
- Merchandises ladders and accessories
- Werner Performance System® signage included

#### SPECIFICATIONS

Model No.	No. of Ladders in Fixture	Overall dimensions	Method of Shipping	Approx. Shipping Wt. Lbs.
37 Display Rack	7	24-3/4" x 48" x 45-1/2"	UPS or Fed Ex	65.0
55 End Cap	14	50-1/2" x 49-1/2" x 85"	LTL	138.0

**HOW TO ORDER** *FACTORY INSTALLED ACCESSORY KITS*

Please follow these steps and refer to the chart below for purchasing a ladder accessory that is factory installed. Certain combinations of factory installed accessories to the same ladder are also available. Lead time for factory installed accessories may vary depending on availability. If you have a question or need assistance, please call customer service at 1-888-523-3371.

Step 1: Locate the ladder's model number and add an X on to the end of the model number.

Step 2: Use the chart provided and find the accessory you want attached. Add the 4 digit designator to the end of the ladder model number after the X.

Example: Ladder Model Number: D6220-2  
Add the X to signify factory installation: D6220-2X  
Accessory to install: APK80  
Locate accessory on chart and find that "0004" designates this accessory being added.

**MODEL TO ORDER: D6220-2X0004**

Attached Accessories	Description	4-Digit Designator
A61	Combination Spur-Hoop Shoe	0038
A71	Padded Fixed V-Rung	0005
A72	Adjustable Pole Strap	0008
A74	Cable Hooks	0003
A78	Fly Section Shoe	0058
A81	Adjustable Pole Lashes	0089
A83	Rubber Padded Shoe	0049
A86	Spur Shoe	0007
A92	Cable Hook and V-Rung Assembly	0002
APK70	LevelLok® Ladder Leveler with 2 base units	0086
APK80	Level-Master Automatic Ladder Levelers	0004

See price list for added cost.

Werner's illustrations are representative and may not include all styles.

All accessories, attachments, and replacement parts are designed and tested for Werner Co. products only.

# CUSTOMIZE YOUR LADDER TOP



Paint**Cup** & PaintCup**Liner**




Job**Bucket**



Utility**Bucket**



Job**Caddy**



Utility**Hook**



Tool**Lasso**<sup>®</sup>



## AC27-P

### Paint Cup



- Great for trim painting and cut-in applications
- Built-in magnet to secure a paint brush
- Holds 1 quart of paint
- Can be used with disposable Paint Cup Liner AC27-L

Model No.	Fits on
AC27-P	OBEL00, OBPT00, OBCN00, 6200, 6100, 6000, AC24

Approx. Shipping Dimensions	Approx. Shipping Wt. Lbs.
9-1/8" x 13-3/4" x 10-7/8"	4.0

*Shipping quantity (6) units per carton*

## AC27-L

### Paint Cup Liner



- Disposable liner makes clean up easy
- Each AC-27L unit includes 4 liners

Model No.	Fits on
AC27-L	AC27-P

Approx. Shipping Dimensions	Approx. Shipping Wt. Lbs.
5-1/8" x 13-3/8" x 10"	2.2

*Shipping quantity (10) units per carton (40) liners per carton*

## AC50-JB-3

### Job Bucket



- Increase ladder storage and maximize your work space
- Great for all trades: electrical, maintenance, plumbing, construction
- Integrated tape measure and screwdriver holders
- Top grooves hold round pipes in place
- 600 cubic inches of storage, 25 lbs. load capacity

Model No.	Fits on
AC50-JB-3	OBEL00, OBPT00, OBCN00, 6200, 6100, 6000

Approx. Shipping Dimensions	Approx. Shipping Wt. Lbs.
15-1/4" x 11-7/8" x 16-1/4"	6.6

*Shipping quantity (3) units per carton*

# TAKE LESS TRIPS UP THE LADDER



## AC52-UB

### Utility Bucket



- Expand your work surface
- Great for jobsite or household use
- Integrated Lock-In Socket for adding Paint Cup, ToolLasso® or Utility Hook
- Ideal for wet or dry applications
- Holds up to one gallon of liquid, 25 lbs. capacity

Model No.	Fits on
AC52-UB	OBEL00, OBPT00, OBCN00, 6200, 6100, 6000

Approx. Shipping Dimensions	Approx. Shipping Wt. Lbs.
13-1/2" x 10-3/4" x 10-3/4"	4.5

*Shipping quantity  
(3) units per carton*

## AC54-JC

### Job Caddy



- Holds large or odd shaped items like fluorescent bulbs or ceiling fan blades
- 4 storage compartments keep small parts separated
- Screwdriver, pliers, putty knife & towel holders
- End hook built in for increased convenience
- Integrated Lock-In Socket for adding Paint Cup, ToolLasso® or Utility Hook

Model No.	Fits on
AC54-JC	OBEL00, OBPT00, OBCN00, 6200, 6100, 6000

Approx. Shipping Dimensions	Approx. Shipping Wt. Lbs.
15-1/2" x 8-3/8" x 10-3/8"	6.7

*Shipping quantity  
(3) units per carton*

## AC56-UH

### Utility Hook



- Keep cords from getting tangled in your ladder
- Organize cords and keep them within reach
- Holds extension cords, air hoses, garden hoses, strands of lights, paint sprayers and other tools or project materials

Model No.	Fits on
AC56-UH	OBEL00, OBPT00, OBCN00, 6200, 6100, 6000

Approx. Shipping Dimensions	Approx. Shipping Wt. Lbs.
9-3/4" x 13-1/2" x 8"	2.8

*Shipping quantity  
(10) units per carton*

## AC58-TL

### ToolLasso®



- Secures tools from falling
- Wraps around the grip of power tools, hand tools and caulk guns
- Locks into HolsterTop® to keep tools safe and ready to use
- Compatible with the ToolLasso® belt clip
- AC58-TL includes 1 belt clip and 2 ToolLassos

Model No.	Fits on
AC58-TL	OBEL00, OBPT00, OBCN00, 6200, 6100, 6000, AC24, PS-48

Approx. Shipping Dimensions	Approx. Shipping Wt. Lbs.
10-7/8" x 12-1/4" x 9-3/4"	4.0

*Shipping quantity  
(12) units per carton*

# STEPLADDER ACCESSORIES

## AC11

### Stepladder Hanger



Hanger can be mounted on a wall to hold stepladders. Industrial strength coated steel wire construction.


#### User Installed Only

Kit No.	Approx. Shipping Weight
AC11	1.8 lbs. each

Shipping quantity  
(6) units per carton

## 22

### Fiberglass Rail Shields



Designed to reinforce. Shields may also be used to repair ladder if rail cracks occur no higher than 3/4" below bottom rivet of bottom step or horizontal and all holes in the rail are intact. Rail shield(s) come with mounting hardware. (1 front and 1 rear kit per stepladder; 2 front kits needed for trestle ladder)

#### User Installed Only

Kit No.	Fits on Front Rail of Fiberglass Series	Approx. Shipping Wt.
22-2F	6000, T6000, 6200, 7300 T6200, 7400 (MK 13 & up) T7400 (MK 11 & up) P7400 (MK 13 & up) PT7400 (MK 4 & up) E7400 (MK 7 & up)	1.5 lbs.
22-3F	7400 (up through MK 12) T7400 (up through MK 10) P7400 (up through MK 12) PT7400 (up through MK 3) E7400 (up through MK 6)	1.5 lbs.
Kit No.	Fits on Rear Rail of Fiberglass Series	Approx. Shipping Wt.
22-2R	6200, 7300, 7400, P7400	1.0 lb.

## PK76

### Universal Auto-Closing Pail Shelf



Spill-Proof®, rugged construction, easy to keep clean, automatically closes with stepladder, built-in rag rack. Pail shelf comes with mounting hardware and instructions.

#### User Installed Only

Kit No.	Fits on	Approx. Shipping Wt.
PK76-3	Fiberglass Stepladders & Aluminum 400 Series Stepladders	2.5 lbs.

Shipping quantity  
(4) units per carton

### Universal Pail Shelf



Two piece, Spill-Proof®, rugged construction, aluminum arms, built-in rag rack. Pail shelf comes with mounting hardware and instructions.

#### User Installed Only

Kit No.	Fits on	Approx. Shipping Wt.
PK76-9	Fiberglass Stepladders & Aluminum 400 Series Stepladders	1.6 lbs.

Shipping quantity  
(6) units per carton

## 76

### Molded Plastic Pail Shelf



Spill-Proof®, rugged construction, easy to keep clean, automatically closes with stepladder. Pail shelf comes with mounting hardware and instructions.

#### User Installed Only

Kit No.	Fits on Fiberglass Series	Approx. Shipping Wt.
76-2	6000 6200	2.5 lbs.

Shipping quantity  
(2) units per carton

## AC24

### Multipurpose Project Tray



Project Tray conveniently holds tools, paints and supplies. Made for Werner multiladders and stepladders. Attaches easily; works at multiple heights; includes ToolLasso®.

#### User Installed Only

Kit No.	Fits on	Approx. Shipping Wt.
AC24	MT Series M1 Series Type IA (300 lbs.) & Type IAA (375 lbs.) Stepladders	2.8 lbs.

## 21

### Grating Shoes



#### User Installed Only

Kit No.	Fits on Series	Approx. Shipping Wt.
21-20	6200, P6200, 7300, 7400, P7400, OB Series	1.5 lbs.
21-22	T6200, T7400, PT7400	1.5 lbs.

## 40

### Casters/Bracket Kits



Heavy duty aluminum bracket with 4" castor allows 360° mobility of ladder. Soft rubber wheels are easy on floors; designed to roll over door thresholds. Casters may be used on all 4 legs; order 2 kits for this purpose. Two (2) casters/brackets come with mounting hardware and instructions.

Order models below as a "-4C" for factory installation.

#### User Installed Only

Kit No.	Fits on Series	Approx. Shipping Wt.
40-2HD	PT370 PT6000 PT7400 (MK 4 & up)	5.0 lbs.
40-4HD	PT7400 (up through MK 3)	5.0 lbs.

Note: Fits only ladder originally equipped with casters.

## LADDER JACKS

Recommended for use with 300 lbs. Type IA and 375 lbs. Type IAA extension ladders (OSHA and ANSI allow use with 250 lbs. Type I extension ladders also)

**User Installed Only**



2-Rung Model AC10-14-02  
Short Body  
Accepts Stages to 14" width



2-Rung Model AC10-20-02  
Long Body  
Accepts Stages to 20" width




3-Rung Model AC10-20-03  
Long Body  
Accepts Stages to 20" width

- Lightweight, sturdy, easy to use
- Designed for quick field adjustments
- Mounts on either side of extension ladder

Kit No.	Approx. Shipping Wt.
AC10-14-02	15.0 lbs.
AC10-20-02	18.0 lbs.
AC10-20-03	20.0 lbs.

Shipping quantity  
2 per unit;  
(1) unit per carton



**PLATFORM CLAMP SYSTEM**  
Clamp secures platform to ladder jacks and ties supporting ladders together to help secure entire ladder jack system

## AC18MT

**Platform**



Slip-resistant surface. Aluminum construction. Kicks out of way for easy climbing. 300 lbs. load capacity.

**User Installed Only**

Kit No.	Fits on All	Approx. Shipping Wt.
AC18MT	MT Series	4.5 lbs.

## ROOF BRACKETS

FRB4510-10



**User Installed Only**

**ARB10-10**  
**Adjustable Roof Bracket**

Carton Dimensions	Approx. Shipping Wt.
4-5/8" x 19-1/2" x 14-1/4"	25.0 lbs.

Shipping quantity  
(10) units per carton

**FRB4510-10**  
**Fixed Roof Bracket**

Accommodates a 12/12, 45-degree roof pitch

Carton Dimensions	Approx. Shipping Wt.
9-3/8" x 18-1/4" x 9-1/4"	22.0 lbs.

Shipping quantity  
(10) units per carton

## AC19

**Extension Ladder Covers**



Helps prevent damage to support surfaces. Designed to 'snap' over extension ladder rail end caps. Resists paints, stains, thinners and solvents.

**User Installed Only**

Kit No.	Fits on	Approx. Shipping Wt.
AC19-2	ALL Single and Extension Fiberglass and Aluminum Ladders (except 500, D500, D7136-2, D7140-2)	1.2 lbs. each

Shipping quantity  
1 pair per unit;  
(6) units per carton

## AC20

**Paint Can Hook**



Includes 2 steel hooks with can openers. Holds one gallon can. 3/16" diameter.

**User Installed Only**

Kit No.	Fits on	Approx. Shipping Wt.
AC20	ALL Extension Ladders	0.4 lbs. each

Shipping quantity  
2 per unit;  
(12) units per carton

## AC22

**Paint Can/ Bucket Hanger**



Holds one gallon can. Easy on and off. Right or left hand use. Plated steel.

**User Installed Only**

Kit No.	Fits on	Approx. Shipping Wt.
AC22	ALL Extension Ladders	0.5 lbs. each

Shipping quantity  
(6) units per carton

## AC78

**Quickclick™ Stabilizer**



Span: 44", Standoff: 10"  
Requires no tools. Spring-loaded locking latch makes it easier and quicker to install/remove than any other stabilizer on the market. Mar-resistant rubber end caps protect work surface. Stabilizer comes with instructions. Paint can hook included.

**User Installed Only**

Kit No.	For use on Singles and Extensions with	Approx. Shipping Wt.
AC78	1-1/4" round rungs 1-1/2" flat rungs 1-3/4" flat rungs 1-5/8" flat rungs	6.4 lbs.

**Not for use on Werner MultiLadders, Type III Aluminum or Type II Fiberglass extension ladders**

Shipping quantity  
(1) unit per carton

**AC96**

**Aluminum Stabilizer**



Span: 47", Standoff :10"  
For use on aluminum ladders of all duty ratings. Attaches in minutes. Mar-resistant rubber caps protect work surface. Paint can hook included. Comes with mounting hardware and instructions.

**User Installed Only**

Kit No.	Fits on	Ladder Size	Approx. Shipping Wt.
AC96	Aluminum Series Extension Ladders with rails up to 3" x 1-3/16"	ALL	4.5 lbs.
	D716	16'	
	D1100	ALL	
	D1200	ALL	
	D1300	ALL	
	D1500	ALL	
	D500	20' - 24'	
	MT	ALL	
	M1	ALL	

**Ideal for stabilizing M1 MultiLadder when in scaffold or stairway positions**

Shipping quantity (6) units per carton

**PK70-1/APK70**

**Leveler with Base Units**



LevelLok® Ladder Leveler with 2 base attachments. Base unit stays attached to the ladder while leveler can be easily removed when not in use. Swivel shoe with ice pick on both ends. Leveler can be used on either side of ladder. Provides 8-1/2" of travel.

*LevelLok® is a registered trademark of the LevelLok Corporation.*

**User or Factory Installed**

Kit No.	Fits on All	Approx. Shipping Wt.
PK70-1 and APK70	MT Series, D7100, D6200, 7100, D1300, D1500, 7800	8.5 lbs.

**PK70-2**

**Leveler Base Units**



LevelLok® Ladder Leveler 2 base attachments. Base units attach to the ladder to be used with LevelLok® Leveler supplied with PK70-1.

*LevelLok® is a registered trademark of the LevelLok Corporation.*

**User Installed Only**

Kit No.	Fits on All	Approx. Shipping Wt.
PK70-2	MT Series, D7100, D6200, 7100, D1300, D1500, 7800	3.2 lbs.

**PK70-3**

**Leveler**



LevelLok® Ladder Leveler attaches to the base units supplied with PK70-1 and PK70-2.

*LevelLok® is a registered trademark of the LevelLok Corporation.*

Approximate Shipping Weight
6.2 lbs.

**PK80/APK80**

**Level-Master® Automatic Ladder Levelers**



Easily attaches to Werner fiberglass and aluminum extension ladders to level ladder on uneven surfaces.

Automatically adjusts up to 8-1/2". Easily levels and locks securely in place. The width of the ladder is increased by approximately 3-3/4". Note: The ladder's duty rating will remain the same after proper installation of leveler. Two (2) ladder levelers (one for each ladder rail) come with mounting hardware and instructions.

**User or Factory Installed**

Kit No.	Fits on Fiberglass Series	Ladder Size
PK80-2 & APK80	D5900, D6000	ALL
	D6200	ALL
	7100	ALL
	D7100	ALL

Kit No.	Fits on Aluminum Series	Ladder Size
PK80-2 & APK80	D1100	ALL
	D1200, D1300	ALL
	D1500, D500	ALL

Note: The original shoes of a D1500 series ladder may replace the steel shoes on a model PK80-2.

Approx. Shipping Weight
9.5 lbs.
Approx. Added Weight to Ladder for Factory Install
6.5 lbs.

Shipping quantity (1) unit per carton

**A61**

**Combination Spur-Hoop Shoe**



Combination aluminum rail shield bracket and spur-hoop shoe assembly.

**Factory Installed Only**

Factory Install No.	Fits on Fiberglass Series	Ladder Size
A61	D6200-2 7100-2 D7100-2	16' - 32' ALL 16' - 32'

Approx. Added Weight to Ladder for Factory Install
3.0 lbs.

**A62**

**Flange Guards**



Black plastic guards prevent damage to ladder rails.

**Factory Installed Only**

Factory Install No.	Fits on Fiberglass Series	Ladder Size
A62	7100-2 7200-2 D7100-2 D7200-2 D8100-2	16' - 32' ALL 16' - 32' ALL ALL

Approx. Added Weight to Ladder for Factory Install
4.0 lbs.



## 64-2

### Shoulder Rest



Foam cushion designed to make carrying ladder more comfortable. Ideally placed at the ladder's balance point

#### User Installed Only

Kit No.	Fits on Fiberglass Series	Ladder Size	Approx. Shipping Wt.
64-2	D6200-2 D6400-2 7100-1 D7100-2 7100-2 D7200-2 D8100-2	ALL ALL 16' - 32' ALL ALL ALL ALL	0.06 lbs.

## 66-1/A66-1

### Reflective Tape



Highly reflective tape to add visibility to ladders. User-installed kit includes two 12" strips.

#### User or Factory Installed

Kit No.	Fits on	Approx. Shipping Wt.
66-1	All Ladders	0.04 lbs.

Factory Install No.	Fits on	Ladder Size
A66-1	All Ladders	ALL

## 71/A71

### Padded Fixed V-Rung



Slip-resistant rubber grip attached to steel v-rung for wood, metal or concrete poles. Pre-pierced holes in fiberglass top rails are provided to accept this accessory. V-rung assembly comes with mounting hardware and instructions.

#### User or Factory Installed


Kit No.	Fits on Fiberglass Series	Ladder Size
71-1	D6200-2 7100-2 D7100-2 7800	ALL ALL 16' - 32' ALL
71-4	D6200-1 7100-1	ALL Up to 16'

Factory Install No.	Fits on Fiberglass Series	Ladder Size
A71	D6200-1 D6200-2 7100-1 7100-2 D7100-2 7800	ALL ALL Up to 16' ALL 16' - 32' ALL

Approx. Shipping Weight	
71-1:	1.5 lbs.
71-4:	2.0 lbs.
Approx. Added Weight to Ladder for Factory Install	
1.4 lbs.	

## 72/A72

### Adjustable Pole Strap



Adjustable strap design for all diameter poles. Slip-resistant rubber grip stitched to strap. Strap assembly comes with mounting hardware and instructions.

#### User or Factory Installed

Kit No.	Fits on Fiberglass Series	Ladder Size	Approx. Shipping Wt.
72-2	D6200-2 7100-2 D7100-2	ALL Up to 16' 16' - 32'	1.3 lbs.
72-1	D6200-1 7100-1	ALL Up to 16'	1.3 lbs.

Factory Install No.	Fits on Fiberglass Series	Ladder Size
A72	D6200-2 7100-1 7100-2 D7100-2	ALL Up to 16' ALL 16' - 32'

## 74/A74

### Cable Hooks



Easily folds within side rails for storage. Cable hooks can be mounted above or below top rung. Consult Werner if using in conjunction with other accessories. Cable hooks come with mounting hardware and instructions.


#### User or Factory Installed

Kit No.	Fits on Fiberglass Series	Ladder Size	Approx. Shipping Wt.
74-1	D6200-2 7100-1 7100-2 D7100-2	ALL Up to 16' ALL 16' - 32'	2.6 lbs.
74-2	D7100-2	36' - 40'	2.6 lbs.

Factory Install No.	Fits on Fiberglass Series	Ladder Size
A74	D7100-2	ALL

## A78

### Fly Section Shoes with Quick Disconnect



Combination aluminum rail shield bracket and hoop shoe with corrugated slip-resistant extruded rubber pad on fly section, allows use as a single or manhole ladder assembly.

#### Factory Installed Only

Factory Install No.	Fits on Fiberglass Series	Ladder Size
A78	D6200-2 7100-2 D7100-2	ALL ALL 16' - 32'

Approx. Added Weight to Ladder for Factory Install	
1.5 lbs.	

**81/A81**

**Adjustable Pole Lashes**



For use with ladders having hoop style end caps only. Adjustable strap design for all diameter poles. Adjustable pole lash comes with mounting hardware and instructions.

**User or Factory Installed**

Kit No.	Fits on Fiberglass Series	Ladder Size	Approx. Shipping Wt.
81-3	D7100-2	36' - 40'	1.5 lbs.

Factory Install No.	Fits on Fiberglass Series	Ladder Size
A81	D6200-2 7100-1 7100-2 D7100-2	ALL ALL ALL ALL

**A82**

**Red Rungs**



Set of 3 painted red rungs for fiberglass extension ladders. Available for rung-plate models only.

**Factory Installed Only**

Factory Install No.	Fits on Fiberglass Series	Ladder Size
A82-1	D7100-2 D7200-2 D8100-2	16' - 32' 16' - 32' ALL
A82-2	D7100-2	ALL
A82-3	D7100-2	36' - 40'

**A83**

**Rubber Padded Shoe**



Aluminum protective rail shield and rubber padded foot. Comes with two (2) padded shoes.

**Factory Installed Only**

Factory Install No.	Fits on Fiberglass Series	Ladder Size
A83	D6200-1 D6200-2 7100-1 7100-2 D7100-2	ALL 16' - 32' Up to 16' ALL 16' - 32'

Approx. Added Weight to Ladder for Factory Install
2.2 lbs.

**86/A86**

**Spur Shoe**



Plated steel spur for use on penetrable surfaces. Two (2) spur shoe assemblies, mounting hardware and instructions included.

**User or Factory Installed**

Kit No.	Fits on Fiberglass Series	Ladder Size
86-1	D6200-2 7100-2, D7100-2 7100-1	16' - 32' 16' - 32' Up to 16'

Factory Install No.	Fits on Fiberglass Series	Ladder Size
A86	D6200-1 D6200-2 7100-1 7100-2 D7100-2	ALL 16' - 32' Up to 16' ALL 16' - 32'

Approx. Shipping Weight
2.5 lbs.
Approx. Added Weight to Ladder for Factory Install
2.0 lbs.

**89**

**Rail Wear Sleeves**




3' long replaceable plastic sleeves help avoid manhole rim damage to ladder rails. Two (2) sleeves, mounting hardware and instructions included.

**User Installed Only**

Kit No.	Fits on Fiberglass Series	Ladder Size	Approx. Shipping Wt.
89-1	M7100-1 7100-1	ALL Up to 16'	2.5 lbs.

**91**

**Adjustable Pole Lash Assembly with Angle Brackets**



This assembly comes with brackets for independent use; wraps around pole. Strap design for all diameter poles. Adjustable pole lash assembly comes with two (2) angle brackets, mounting hardware and instructions.

**User Installed Only**

Kit No.	Fits on Fiberglass Series	Ladder Size	Approx. Shipping Wt.
91-2	D6200-2 7100-2 D7100-2	ALL ALL 16' - 32'	2.0 lbs.

**92/A92**

**Cable Hook and V-Rung Assembly**



Functions as both cable hook and v-rung. For use in applications where the diameter of the pole at the point of support does not exceed 10". Steel v-rung has rubber pad for slip-resistant performance. One (1) cable hook and v-rung assembly, mounting hardware and instructions included.

**User or Factory Installed**

Kit No.	Fits on Fiberglass Series	Ladder Size
92-88	D6200-2 D8200-2EQ	16' - 40' 20' - 28'
92-89	7100-2, D7100-2 D7100-2LV	16' - 32' 20' - 32'
92-91	7100-1	8' - 16'
92-92	D6200-3	16' - 32'

Factory Install No.	Fits on Fiberglass Series	Ladder Size
A92	D6200-2 D6200-3 7100-2 7100-1 D8200-2EQ D7100-2 D7100-2LV	ALL ALL ALL 8' - 16' ALL 16' - 32' 20' - 32'

Approx. Shipping Weight
4.0 lbs.
Approx. Added Weight to Ladder for Factory Install
3.0 lbs.

## 94

### Ladder-Cinch™



Use as a quick tie down. Strap designed for all diameter poles. One (1) Ladder-Cinch™ assembly, storage bag and instructions.

#### User Installed Only

Kit No.	Fits All	Ladder Size	Approx. Shipping Wt.
94-2	Fiberglass Series Extension Ladders	ALL	1.0 lbs.

## 97P

### Adjustable True Grip® Stabilizer and Surface Protectors



Span adjustment : 49", 57" or 65"  
Stand-off distance: 12" or 29-1/2"  
Rectangular stabilizer spans double windows. Quickly converts stand off distance for larger overhangs. Mounts quickly and easily. This comes with one (1) stabilizer, rubber pads, fleece bonnets, mounting hardware and instructions.

- Fits rail up to 3" x 1-3/16"

#### User Installed Only

Kit No.	Fits on Aluminum Series	Ladder Size
97P	D716-2	16'
	D1100	ALL
	D1200	ALL
	D1300	ALL
	D1500	ALL
	D500-2	20' - 24'
	D1700-2EQ	ALL
	D1800-2EQ	ALL

Note: Not to be used on Multi-Ladders

Approx. Shipping Weight
9.5 lbs.

## AC59

### Attic Ladder Installation and Trim Kit



This kit includes temporary support boards, shims and fasteners for installing your attic ladder. Once installed, this kit also included mitered trim boards to improve the attic ladder's appearance.

#### User Installed Only

Kit No.	Fits on	Approx. Shipping Wt.
AC59	ALL Attic Ladders	8.25 lbs. each

## 36-82

### Attic Ladder Assist Pole



3' assist pole allow easy access and smooth opening of attic ladder door.

#### User Installed Only

Kit No.	Fits on	Approx. Shipping Wt.
36-82	ALL Attic Ladders	3.0 lbs. each

SERIES/MODEL	STYLE	PAGE
150B	Aluminum Step Stool	28
21	Grating Shoes	61
22	Fiberglass Rail Shields	61
244	Aluminum Utility Ladder	30
260	Aluminum Platform Ladder	30
2000	1-Person Decorator Plank	47
2300	2-Person Scaffold Plank	47
2400	2-Person Scaffold Plank	47
2500	2-Person Stage Platform	47
2600	2-Person Stage Platform	47
2700	2-Person Stage Platform	47
36-82	Attic Ladder Assist Pole	66
37	Display Rack	57
350	Aluminum Stepladder	29
360	Aluminum Stepladder	29
370	Aluminum Stepladder	25
3100	3-Person Stage Platform	47
3200	3-Person Stage Platform	47
40-1	Swivel Locking Caster	52
41-1	Swivel Base Plate	52
43-1	Guard Rail Holder	52
400	Aluminum Stepladder	24
4100	Narrow Span Scaffold Sections	51
4100-12	Narrow Span Scaffold Tower 12' Platform Height	50
4100-18	Narrow Span Scaffold Tower 18' Platform Height	50
4100-23	Narrow Span Scaffold Tower 23' Platform Height	50
4200	Wide Span Scaffold Sections	51
4200-12	Wide Span Scaffold Tower 12' Platform Height	50
4200-18	Wide Span Scaffold Tower 18' Platform Height	50
4200-23	Wide Span Scaffold Tower 23' Platform Height	50
55	End Cap Display	57
500-1	Aluminum Round Rung Straight Ladder	32
560-3	Aluminum Round Rung Extension Ladder	33
5300	Plywood Decked Aluma-Plank™	44
5500	Aluminum Decked Aluma-Plank™	44
5600	2-Piece Extruded Aluma-Board™	44
5900	Fiberglass Stepladder	11
6000	Fiberglass Stepladder	10
6002	Fiberglass Step Stool	9
6100	Fiberglass Stepladder	9
6200	Fiberglass Stepladder	6
6202	Fiberglass Step Stool	8
64-2	Shoulder Pad	64
66-1/A66-1	Reflective Tape	64
71/A71	Padded Fixed V-Rung	64
72/A72	Adjustable Pole Strap	64
74/A74	Cable Hooks	64
76	Molded Plastic Pail Shelf	61
7100	Fiberglass Round Rung Extension/Straight Ladder	16
7300	Fiberglass Stepladder	5

SERIES/MODEL	STYLE	PAGE
7400	Fiberglass Stepladder	1
7800	Fiberglass Combination Step/Extension Ladder	21
81/A81	Adjustable Pole Lashes	65
86/A86	Spur Shoe	65
89	Rail Wear Sleeves	65
91	Adjustable Pole Lash Assembly with Angle Brackets	65
92/A92	Cable Hook and V-Rung Assembly	65
94	Ladder-Cinch™	66
97P	Adjustable True Grip® Stabilizer and Surface Protectors	66
9500	All-Fiberglass Extension Ladder/Single Ladder	22
A61	Combination Spur-Hoop Shoe	63
A62	Flange Guards	63
A78	Fly Section Shoes with Quick Disconnect	64
A82	Red Rungs	65
A83	Rubber Padded Shoe	65
AA	Aluminum Compact Attic Ladder	39
AC10-14-02	2-Rung Short Body Ladder Jack	62
AC10-20-02	2-Rung Long Body Ladder Jack	62
AC10-20-03	3-Rung Long Body Ladder Jack	62
AC11	Stepladder Hanger	61
AC18MT	Platform	62
AC19	Extension Ladder Covers	62
AC20	Paint Can Hook	62
AC22	Paint Can/Bucket Hanger	62
AC24	Multipurpose Project Tray	61
AC27-L	Lock-In Paint Cup Liner	59
AC27-P	Lock-In Paint Cup	59
AC50-JB-3	Lock-In Job Bucket	59
AC52-UB	Lock-In Utility Bucket	60
AC54-JC	Lock-In Job Caddy	60
AC56-UH	Lock-In Utility Hook	60
AC58-TL	Lock-In ToolLasso®	60
AC59	Attic Ladder Installation and Trim Kit	66
AC78	Quickclick™ Stabilizer	62
AC96	Aluminum Stabilizer	63
AH	Aluminum Universal Attic Ladder	39
AP	Aluminum Work Platforms	42
ARB10-10	Adjustable Roof Bracket	62
BD	Scaffold Diagonal Brace	52
BH	Scaffold Horizontal Brace	52
BN	Scaffold Narrow Span Horizontal-Diagonal Brace	52
BOR	Scaffold Outrigger Brace	52
BW	Scaffold Wide Span Horizontal-Diagonal Brace	52
D1100	Aluminum D-Rung Extension Ladder	36
D1200-2	Aluminum D-Rung Extension Ladder	35
D1200-3	Aluminum D-Rung Compact Extension Ladder	35
D1300	Aluminum D-Rung Extension Ladder	34
D1500	Aluminum D-Rung Extension Ladder/Straight Ladder	33
D1700-2EQ	Aluminum Extension Ladder with Integrated Leveling	34
D1800-2EQ	Aluminum Extension Ladder with Integrated Leveling	34

SERIES/MODEL	STYLE	PAGE
D500-2	Aluminum Flat Rung Extension Ladder	32
D5900	Fiberglass D-Rung Extension Ladder	19
D6000	Fiberglass D-Rung Extension Ladder	19
D6200-2	Fiberglass D-Rung Extension Ladder/Straight Ladder	18
D6200-3	Fiberglass D-Rung Compact Extension Ladder	18
D6400-2	Fiberglass D-Rung Lightweight Extension Ladder	17
D716-2	Aluminum D-Rung Extension Ladder	36
D7100-2	Fiberglass D-Rung Extension Ladder	15
D7100-2LV	Fiberglass D-Rung Ext. Ladder w/ Integrated Leveling	15
D7200-2	Fiberglass D-Rung Lightweight Extension Ladder	17
D8200-2EQ	Fiberglass Extension Ladder with Integrated Leveling	16
E7400	Fiberglass Extension Trestle Ladder	3
ERT-N	End Rail and End Toe Board Assembly - Narrow	48
ERT-W	End Rail and End Toe Board Assembly - Wide	48
FNB-80	Scaffold Base End Frame	52
FNU	Scaffold Frames	52
FRB4510-10	Fixed Roof Bracket	62
FRO	Scaffold Rolling Outrigger Frame	52
FTP6200	Fiberglass Tripod Stepladder	7
FWB-80	Scaffold Base End Frame	52
FWG-42	Scaffold Guard Rail End Frame	52
FWU	Scaffold Frames	52
M1	Aluminum Folding MultiLadder	38
M7100	Fiberglass Manhole Ladder	21
MT	Aluminum Telescoping MultiLadder	38
OBCN00	Fiberglass Old Blue® Series Contractor's Jobstation™	4
OBEL00	Fiberglass Old Blue® Series Electrician's Jobstation™	4
OR-ADU	Scaffold Knee-Type Outriggers	52
P22W	Scaffold Board	52
P370	Aluminum Platform Ladder	27
P400	Aluminum Platform Ladder	25
P6200	Fiberglass Platform Ladder	7
P7400	Fiberglass Platform Ladder	2
PA200	Aluminum Extension Plank	44
PD22W	Scaffold Wood Deck with Access Door	52
PD6200	Podium Ladder	14
PD7300	Podium Ladder	14
PJ-6P	Aluminum Pump Jack 6' Aluminum Pole	45
PJ-12P	Aluminum Pump Jack 12' Aluminum Pole	45
PJ-18P	Aluminum Pump Jack 18' Aluminum Pole	45
PJ-24P	Aluminum Pump Jack 24' Aluminum Pole	45
PJ-100	Aluminum Pump Jack	45
PJ-ERN	Aluminum Pump Jack End Rail Kit (narrow)	45
PJ-ERW	Aluminum Pump Jack End Rail Kit (narrow)	45
PJ-PC	Aluminum Pump Jack Pole Connector	45
PJ-PF-4	Aluminum Pump Jack Pole Foot	45
PJ-SBF	Aluminum Pump Jack Foldable Support Brace	45
PJ-SBR	Aluminum Pump Jack Rigid Support Brace	45
PJ-SN	Aluminum Pump Jack Safety Net	45
PJ-WB	Aluminum Pump Jack Work Bench	45

SERIES/MODEL	STYLE	PAGE
PK70-1/APK70	Ladder Leveler with Base Units	63
PK70-2	Ladder Leveler Base Units	63
PK70-3	Ladder Leveler	63
PK76	Universal Pail Shelf	61
PK80/APK80	Level-Master® Automatic Ladder Levelers	63
PS-48	Steel Portable Scaffold	43
PT370	Aluminum Stockr's Ladder®	26
PT6000	Fiberglass Stockr's Ladder®	11
PT7400	Fiberglass Stockr's Ladder®	3
R102	Straight Ramp Kit	55
R301	Straight Ramps	55
R402	Arched Ramps	54
R522	Folding Arched Ramps	54
S7700	Fiberglass Interchangeable Parallel Sectional Ladder	23
S7900	Fiberglass Interchangeable Tapered Sectional Ladder	22
SGR-09	1-1/2" Square Guard Rail Cut Length - 108"	48
SGR-13	1-1/2" Square Guard Rail Cut Length - 156"	48
SH378	Aluminum Shelf Ladder	27
SNB	Snap-Up® Narrow Span Folding Scaffolds	51
SPF00	Fiberglass Posting Ladder	23
SPJ-100	Steel Pump Jack	46
SPJ-GRH	Steel Pump Jack Guard Rail Holder	46
SPJ-PA-4	Steel Pump Jack Pole Anchor	46
SPJ-SBF	Steel Pump Jack Foldable Support Brace	46
SPJ-WB	Steel Pump Jack Work Bench/Guard Rail Holder	46
SRS-72 & Accessories	6' Steel Rolling Scaffold	43
SSA00	Aluminum Step Stand	28
SSF00	Fiberglass Step Stand	8
SSP-47	Stanchion Post Assembly	48
STB-09	3-1/2" Toe Board Cut Length - 108"	48
STB-13	3-1/2" Toe Board Cut Length - 156"	48
SWB	Snap-Up® Wide Span Folding Scaffolds	51
T370	Aluminum Multi-Use Twin Stepladder	26
T372	Aluminum Twin Step Stool	28
T400	Aluminum Multi-Use Twin Stepladder	24
T6000	Fiberglass Multi-Use Twin Stepladder	10
T6200	Fiberglass Twin Stepladder	6
T6202	Fiberglass Twin Step Stool	8
T7400	Fiberglass Multi-Use Twin Stepladder	2
TN4A	Aluminum Toe Board Assemblies for 4100 Series	52
TPF00	Fiberglass Posting Ladder	23
TR401-S	Steel Removable Pickup Truck Rack	56
TW370-30	Aluminum Portable Work Stand	28
TW4A	Aluminum Toe Board Assemblies for 4200 Series	52
TW6200	Fiberglass Portable Work Stand	8
VR401-W	Steel Van Rack	57
W	Wood Folding Attic Ladder	40
WH	Wood Folding Heavy Duty Attic Ladder	40
WNS	Nestable Stage	45