



NOTES:

1. FINISH: Oil Dipped
2. COMPLIANCE: ROHS
3. TEMPERATURE: Up To 400° F
4. BUSHING SERIES: Trantorque Mini
5. APPROXIMATE WEIGHT: 0.100 lbs
6. MATERIAL: Corrosion Resistant Steel
7. TRANSMISSIBLE TORQUE: 1184 Ft-Lb
8. HUB CONTACT PRESSURE: 16084 PSI
9. RECOMMENDED TORQUE TIGHTENING: 585 in/lbs

COMPONENT	KEYLESS BUSHING
-----------	-----------------

GRAINGER
 100 Grainger Parkway, Lake Forest, Illinois 60045-5201
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE 1.807

13J122

Keyless Bushing, Shaft Dia. 0.6250 In

UNIT
INCH
SHEET
1 of 1