



Force Rating	242 lb.	Max. Pressure	90 psi
Bin Weight Capacity	2420 lb.	Max. Temp.	360 °F
Speed @ 87 psi	19,500 VPM	Speed @ 60 psi	17,000 VPM
dB @ 87 psi	76	dB @ 60 psi	-
CFM @ 87 psi	9.9	CFM @ 60 psi	-

NOTES:

1. DUTY: Continuous
2. MUFFLER: Included
3. VIBRATOR TYPE: Ball
4. MOUNTING: Any Position
5. STANDARDS: CE Certified
6. HOUSING MATERIAL: Aluminum

COMPONENT	Pneumatic Vibrator
-----------	--------------------



100 Grainger Parkway, Lake Forest, Illinois 60045-5201
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE 0.840

<h1>1DYN9</h1> <p>PNEUMATIC BALL VIBRATOR, FORCE 242 LB</p>	UNIT
	INCH [MM]
	SHEET
	1 of 1