


Series	H	Shut Off	Yes
Sleeve Material	316 Stainless Steel	Valve Design	Poppet
Connection Type	FNPS	Seal Material	Buna
Coupler Body Size	1/2"	Max. Pressure	3750 psi
Coupler Flow Rate	14.0 gpm	Coupler Finish	Plain
Coupler Thread Size	1/2"-14	Locking Mechanism	Ball
Coupler Interchange Type	H	Coupler Body Material	316 Stainless Steel



NOTES:

1. ITEM: Hydraulic Coupler Body
2. FOR USE WITH: Rubber Hose
3. BEARING MATERIAL: 316 Stainless Steel
4. OPERATING TEMP. RANGE: -40° to 200°F
5. QUICK COUPLER TYPE: Hydraulic Coupler Body

GRAINGER

100 Grainger Parkway, Lake Forest, Illinois 60045-5201
1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE

1.36

COMPONENT	Hydraulic Quick Couplers		
20LG81 Coupler Body, 1/2-14, 1/2 In. Body, 316 SS	UNIT		
	INCH		
	SHEET		
			1 of 1