



NOTES:

1. SHAFT SIZE: 1"
2. MIN. RPM: 600
3. MAX. RPM: 1800
4. SHAFT STYLE: Keyed
5. ITEM: Single Vane Pump
6. INLET PORT: 1" NPT
7. SHAFT ROTATION: Right
8. OUTLET PORT : 1/2" NPT
9. MAX. PRESSURE: 2500 psi
10. DISPLACEMENT: .60 cu. in./rev.
11. PORT LOCATION: Inline With Inlet
12. MOUNT TYPE: SAE A 2 Bolt Flange
13. FLOW RATE: 3 gpm @ 1200 rpm and 100 psi
14. APPLICATION: Power Units, Mobile Equipment, Lifts

COMPONENT	Hydraulic Vane Pumps
------------------	----------------------



100 Grainger Parkway, Lake Forest, Illinois 60045-5201
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE 0.32

20V926 Vane Pump, 3 gpm @ 1200 rpm and 100 psi	UNIT
	INCH
	SHEET
	1 of 1