



**NOTES:**

1. WEIGHT: 0.2 Lbs.
2. STIFFNESS: 916
3. MAXIMUM RPM: 7600
4. COMPONENT WR2: 0.0019 bs-ft<sup>2</sup>
5. TORQUE RATING: 312 in-lb.
6. MATERIAL: EPDM Rubber
7. MAX. ANGULAR MISALIGNMENT: 1° in.
8. MAX. PARALLEL MISALIGNMENT: 0.015 in.
9. MAX. ANGULAR GAP MISALIGNMENT: 0.056 in.
10. OPERATING TEMPERATURE: -30°F to +275°F

|  |                        |
|--|------------------------|
| <b>COMPONENT</b>                         | Sleeve Coupling Insert |
| <b>32ZP56</b>                            | <b>UNIT</b>            |
| Sleeve Coupling Insert, 5JE, EPDM Rubber | INCH                   |
|  | <b>SHEET</b>           |
|  | 1 of 1                 |



100 Grainger Parkway, Lake Forest, Illinois 60045-5201  
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000  
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

|              |      |
|--------------|------|
| <b>SCALE</b> | 0.68 |
|--------------|------|