



NOTES:

1. OIL INCLUDED: Yes
2. PORT SIZE: 3/8" NPT
3. NUMBER OF STAGES: 2
4. OVERALL LENGTH: 7-1/2"
5. OVERALL WIDTH: 3-47/64"
6. OVERALL HEIGHT: 3-47/64"
7. ITEM: Hydraulic Hand Pump
8. MAX. HANDLE EFFORT: 99 lb.
9. RESERVOIR MATERIAL: Steel
10. HANDLE MATERIAL: Aluminum
11. RESERVOIR CAPACITY: 346.5 cu. in.
12. PUMP MATERIAL: Anodized Aluminum
13. MAX. PRESSURE 1ST STAGE: 500 psi
14. MAX. PRESSURE 2ND STAGE: 14,500 psi
15. DISPLACEMENT PER STROKE 1ST STAGE: 3.20 cu. in.
16. DISPLACEMENT PER STROKE 2ND STAGE: 0.12 cu. in.

COMPONENT		Hydraulic Hand and Foot Pumps	
<h1>26VZ39</h1>		UNIT	MM
		SHEET	1 of 1
Hand Pump, 2 Speed, 14,500 psi		SCALE	0.27



100 Grainger Parkway, Lake Forest, Illinois 60045-5201
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE 0.27