



**NOTES:**

1. MAX. RPM: 1800
2. APPROX. WEIGHT: 32.00 oz.
3. MAX. TORQUE: 750 in-lbs.
4. MACHINED FROM: Bar Stock
5. BODY MATERIAL: Steel, ASTM A108 / FINISH: Black Oxide
6. FEATURES/APPLICATION:  
 High Axial Load and Torque Capacity, Does Not Mar the Shaft.  
 Where Alignment is Critical, Particularly When No Backlash is Desired and Flexibility is N/A.

<b>COMPONENT</b>	Rigid Coupling, One-Piece
<b>UNIT</b>	INCH
<b>SHEET</b>	1 of 1

**GRAINGER**  
 100 Grainger Parkway, Lake Forest, Illinois 60045-5201  
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000  
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

**SCALE** .96

29NL41

Set Screw Type, Steel, w/ Keyway  
 3" L x 2" OD x 1" Bore