



**NOTES:**

- 1. ITEM : General Purpose Bolt-Hole Caster
- 2. CASTER SUB-TYPE : Swivel
- 3. LOAD RATING : 395 lb.
- 4. WHEEL/TREAD HARDNESS RATING : Soft
- 5. WHEEL/TREAD HARDNESS : 70 Shore A
- 6. WHEEL/TREAD COLOR : Black
- 7. CASTER BRAKE TYPE : Total Lock Brake
- 8. CASTER FRAME MATERIAL : Steel
- 9. FRAME FINISH : Zinc Plated
- 10. WHEEL CORE MATERIAL : Nylon
- 11. OPERATING TEMPERATURE RANGE : -40° to 158°F
- 12. APPLICATION : Tool and Work Boxes
- 13. FEATURES : Kingpin Less Press Steel, Hallow
- 14. STANDARDS : ICWM

COMPONENT		Bolt Hole Casters	
<h1>38LU25</h1>		UNIT	INCH
		SHEET	1 of 1
General Purpose Bolt-Hole Caster, 4"		SCALE	0.44



100 Grainger Parkway, Lake Forest, Illinois 60045-5201  
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000  
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.