



NOTES:

1. LOAD RATING : 550 lb.
2. CASTER SUB-TYPE : Swivel
3. WHEEL BEARING TYPE : Plain
4. ADJUSTMENT STYLE : Nut
5. WHEEL/TREAD MATERIAL : Nylon
6. FRAME FINISH : Powder Coated
7. CASTER MOUNTING TYPE : Bolt Hole
8. SWIVEL RACEWAY TYPE : Single Ball
9. CASTER FRAME MATERIAL : Aluminum
10. STANDARDS : DIN EN, ISO 9001, ICWM
11. ITEM : Leveling Threaded Stem Caster
12. CASTER STEM TYPE : Threaded Bolt Hole
13. FEATURES : Push/Pull Force Reduction

COMPONENT		Leveling Stem Casters	
<h1>454N25</h1>		UNIT	INCH
		SHEET	
		1 of 1	
Leveling Threaded Stem Caster, 550 lb., 2"			



100 Grainger Parkway, Lake Forest, Illinois 60045-5201
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE 0.52