


Screw and Knob Adjust - 3/16" Internal Hex.



**NOTES:**

1. VALVE CAVITY SIZE: C10-2
2. ITEM: Threaded Cartridge Valve
3. CARTRIDGE VALVE ITEM: Cartridge Valve
4. MAX. FLOW - HYDRAULIC VALVES: 20.0 gpm
5. MAX. PRESSURE - HYDRAULIC VALVES: 5000 psi
6. CARTRIDGE VALVE TYPE: Differential Area Relief
7. APPLICATION: Differential area relief valves are best suited for intermittent applications where fast response is critical. They are often used as crossover relief valves to chop pressure spikes.

<b>COMPONENT</b>	Hydraulic Cartridge Valves
------------------	----------------------------



100 Grainger Parkway, Lake Forest, Illinois 60045-5201  
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000  
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

**SCALE** 0.98

<b>4UA87</b>  Valve, Differential Relief, 20 GPM Max	<b>UNIT</b>
	MM (INCH)
	<b>SHEET</b>
	1 of 1