



NOTES:

1. SERIES: B-LOC Series B400
2. MATERIAL: Steel
3. FINISH: Oil Dipped
4. TEMPERATURE: Dependent on Application ° F
5. HUB CONTACT PRESSURE: 16991 psi
6. MAX TRANSMISSIBLE THRUST: 8439 lbs
7. MAX TRANSMISSIBLE TORQUE: 352 ft-lbs
8. RECOMMENDED INSTALL TORQUE: 11 ft-lbs
9. ASSEMBLY HARDWARE: (9) M6 x 18 Locking Screws included in assembly

COMPONENT	KEYLESS BUSHING
-----------	-----------------



100 Grainger Parkway, Lake Forest, Illinois 60045-5201
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE 1.393

Keyless Bushing, Dia. 1 In., 9 Bolt

44A240

UNIT	INCH
SHEET	1 of 1