



**NOTES:**

1. VALVE CAVITY SIZE: C10-4
2. ITEM: Threaded Cartridge Valve
3. CARTRIDGE VALVE ITEM: Cartridge Valve
4. MAX. FLOW - HYDRAULIC VALVES: 7.0 gpm
5. MAX. PRESSURE - HYDRAULIC VALVES: 3600 psi
6. CARTRIDGE VALVE TYPE: Directional Control Valve
7. VALVE WAYS AND POSITIONS: 4-Way/3-Position
8. APPLICATION: 4 Way spool valves are often used for the raise / lower function of a double acting cylinder, or as a forward/reverse function of bi-directional motors. The center position can be used to stop the actuator in mid-stroke, or dump pump flow.

COMPONENT		Hydraulic Cartridge Valves	
<h1>4UA90</h1> <p>Valve, Solenoid, C10-4</p>		UNIT	
		MM (INCH)	
		SHEET	
SCALE	0.68		1 of 1



100 Grainger Parkway, Lake Forest, Illinois 60045-5201  
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000  
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.