



**NOTES:**

1. MAX. TEMP.: 250
2. MOTOR TYPE: Gear
3. FINISH: Black Painted
4. INCLUDES: Mounting Feet
5. ITEM: Forced Air Oil Cooler
6. FAN GUARD MATERIAL: Steel
7. HYDRAULIC MOTOR GPM: 3.6
8. MIN. OIL PRESSURE (PSI): 500
9. MAX. OIL PRESSURE (PSI): 2000
10. COOLANT HP HEAT REMOVED: 25
11. COOLANT MAX. PRESSURE (PSI): 377
12. COOLANT FLOW RANGE (GPM): 8 to 80
13. FAN BLADE MATERIAL: Polypropylene
14. HEAT EXCHANGER MATERIAL: Aluminum
15. HYDRAULIC MOTOR DISPLACEMENT (CU. IN./REV): 0.218

COMPONENT		Hydraulic Motor Oil Coolers	
<h1>4UJC1</h1>		UNIT	
		INCH	
Oil Cooler, w/Hydraulic Motor, 8-80 GPM		SHEET	
			1 of 1



100 Grainger Parkway, Lake Forest, Illinois 60045-5201  
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000  
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE 0.09