



NOTES:

1. DUTY: Continuous
2. FORCE: Sinusoidal
3. INLET PORT: 1/2 NPT
4. GPM @ 1000 PSI: 7.0
5. OUTLET PORT: 1/2 NPT
6. MAX. PRESSURE: 3000 psi
7. FORCE @ 1000 psi: 617 Lb.
8. SPEED @ 1000 psi: 5300 VPM
9. VIBRATOR TYPE: Low Frequency
10. BIN WEIGHT CAPACITY: 4450 Lb.
11. MOUNTING PLATE: Sold Separately

COMPONENT	Hydraulic Vibrator	
<p>4HT16</p> <p>Vibrator, Hydraulic</p>	UNIT	INCH
	SHEET	1 of 1
	SCALE	0.450



100 Grainger Parkway, Lake Forest, Illinois 60045-5201
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE 0.450