



NOTES:

1. SERIES: H
2. MAX. RPM: 969
3. PORT TYPE: Side
4. SHAFT TYPE: Keyed
5. ITEM: Hydraulic Motor
6. PORT THREAD: 1/2-14 NPTF
7. MAX. OIL TEMP. (F): 180
8. MIN. OIL VISCOSITY: 100 SUS
9. CONTINUOUS TORQUE: 650 in.-lb.
10. PRESSURE RATING (PSI): 2400
11. FLANGE MOUNT: 2 Bolt, 3.25" Pilot
12. DISPLACEMENT (CU. IN./REV.): 2.8

COMPONENT General Purpose Hydraulic Motors



100 Grainger Parkway, Lake Forest, Illinois 60045-5201
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE 0.41

5PZG6

Hydraulic Motor, 2.8 cu in/rev, 2 Bolt

UNIT
 INCH
SHEET
 1 of 1