



NOTES:

1. STROKE: 0.38"
2. ITEM: Work Support
3. TYPE: Manifold Mount
4. FUNCTION: Fluid Advanced
5. OIL CAPACITY: 0.04 cu. in.
6. MAX. OIL FLOW: 40 cu. in./min.
7. MAX. SUPPORT FORCE: 1650 lb.
8. PRESSURE RANGE: 700 to 5000 psi
9. INCLUDES: Contact Button, Manifold Seal
10. MATERIAL OF CONSTRUCTION: Steel/Bronze
11. PLUNGER CONTACT SPRING FORCE EXTENDED: 2.0 lb.
12. PLUNGER CONTACT SPRING FORCE RETRACTED: 5.8 lb.

COMPONENT		Hydraulic Work Supports	
<h1>5UWZ0</h1>		UNIT	INCH
		SHEET	1 of 1
		Work Support,Manifold,Fluid Adv,1650 lb	



100 Grainger Parkway, Lake Forest, Illinois 60045-5201
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE 1.35