



NOTES:

1. MATERIAL: Steel
2. RATED TORQUE: 65.7 lb-in
3. END FLOAT TOLERANCE: 0.060"
4. TEMPERATURE RANGE: -25° / + 150°
5. MAX. PARALLEL MISALIGNMENT: 0.005"
6. HORSEPOWER RATING @ 100 RPM: 0.09
7. WEIGHT: Coupling - Aprox. 0.65 lbs.
8. ANGULAR MISALIGNMENT TOLERANCE: 6 Degree
9. USED WITH: Chain Part # 6AGR2, Coupling Cover Part # 6AGP9
10. The Inner diameter dimension can supply finished chain coupling according to JIS, GB, BS and ASA standard series.

COMPONENT		Coupling Coupling Sprocket	
6AGR5		UNIT	INCH
		SHEET	1 of 1
40 Pitch, 16 T, 1-1/8" Bore Sprocket		SCALE	1.00



100 Grainger Parkway, Lake Forest, Illinois 60045-5201
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.